





WIRING DIAGRAM		LOCKNUT LN-SS5		SPECIFICATIONS																																																			
 OUTPUT: AP6X SHORT-CIRCUIT AND OVERLOAD PROTECTED				<table><tr><td>RATED OPERATING DISTANCE</td><td>1.0 mm = .039" (NOMINAL)</td></tr><tr><td>MOUNTING MODE</td><td>FLUSH</td></tr><tr><td>MIN. REPEAT ACCURACY</td><td>≤ 2%</td></tr><tr><td>TEMPERATURE DRIFT</td><td>≤ ± 10%</td></tr><tr><td>HYSTERESIS</td><td>3-15%</td></tr><tr><td>OPERATING TEMPERATURE</td><td>-25°C to +70°C (-13°F to +158°F)</td></tr><tr><td>RATED OPERATIONAL VOLTAGE</td><td>10-30 VDC</td></tr><tr><td>RESIDUAL RIPPLE</td><td>≤ 10%</td></tr><tr><td>DC RATED OPERATIONAL CURRENT</td><td>≤ 100 mA</td></tr><tr><td>NO-LOAD CURRENT</td><td>≤ 15 mA</td></tr><tr><td>RESIDUAL CURRENT</td><td>≤ 0.1 mA</td></tr><tr><td>RATED INSULATION VOLTAGE</td><td>≤ 0.5 kV</td></tr><tr><td>SHORT-CIRCUIT PROTECTED</td><td>YES</td></tr><tr><td>MAX VOLTAGE DROP</td><td>≤ 1.8 V</td></tr><tr><td>WIRE BREAKAGE PROTECTION</td><td>INCORPORATED</td></tr><tr><td>REVERSE POLARITY PROTECTION</td><td>INCORPORATED</td></tr><tr><td>OUTPUT FUNCTION</td><td>3-WIRE, NORMALLY OPEN, PNP</td></tr><tr><td>MAX. SWITCHING FREQUENCY</td><td>≤ 3.0 kHz</td></tr><tr><td>HOUSING MATERIAL</td><td>METAL, A4 1.4404 (AISI 316L)</td></tr><tr><td>ACTIVE FACE MATERIAL</td><td>PLASTIC, PA12-GF20</td></tr><tr><td>CABLE</td><td>ø3.0, LifYY-11Y, TPU</td></tr><tr><td>SHOCK RESISTANCE</td><td>30 g, 11 ms</td></tr><tr><td>VIBRATION RESISTANCE</td><td>55 Hz, 1 mm AMPLITUDE (IN ALL 3 PLANES)</td></tr><tr><td>DEGREE OF PROTECTION</td><td>IP67</td></tr><tr><td>SWITCHING STATUS INDICATION</td><td>LED: YELLOW</td></tr></table>		RATED OPERATING DISTANCE	1.0 mm = .039" (NOMINAL)	MOUNTING MODE	FLUSH	MIN. REPEAT ACCURACY	≤ 2%	TEMPERATURE DRIFT	≤ ± 10%	HYSTERESIS	3-15%	OPERATING TEMPERATURE	-25°C to +70°C (-13°F to +158°F)	RATED OPERATIONAL VOLTAGE	10-30 VDC	RESIDUAL RIPPLE	≤ 10%	DC RATED OPERATIONAL CURRENT	≤ 100 mA	NO-LOAD CURRENT	≤ 15 mA	RESIDUAL CURRENT	≤ 0.1 mA	RATED INSULATION VOLTAGE	≤ 0.5 kV	SHORT-CIRCUIT PROTECTED	YES	MAX VOLTAGE DROP	≤ 1.8 V	WIRE BREAKAGE PROTECTION	INCORPORATED	REVERSE POLARITY PROTECTION	INCORPORATED	OUTPUT FUNCTION	3-WIRE, NORMALLY OPEN, PNP	MAX. SWITCHING FREQUENCY	≤ 3.0 kHz	HOUSING MATERIAL	METAL, A4 1.4404 (AISI 316L)	ACTIVE FACE MATERIAL	PLASTIC, PA12-GF20	CABLE	ø3.0, LifYY-11Y, TPU	SHOCK RESISTANCE	30 g, 11 ms	VIBRATION RESISTANCE	55 Hz, 1 mm AMPLITUDE (IN ALL 3 PLANES)	DEGREE OF PROTECTION	IP67	SWITCHING STATUS INDICATION	LED: YELLOW
RATED OPERATING DISTANCE	1.0 mm = .039" (NOMINAL)																																																						
MOUNTING MODE	FLUSH																																																						
MIN. REPEAT ACCURACY	≤ 2%																																																						
TEMPERATURE DRIFT	≤ ± 10%																																																						
HYSTERESIS	3-15%																																																						
OPERATING TEMPERATURE	-25°C to +70°C (-13°F to +158°F)																																																						
RATED OPERATIONAL VOLTAGE	10-30 VDC																																																						
RESIDUAL RIPPLE	≤ 10%																																																						
DC RATED OPERATIONAL CURRENT	≤ 100 mA																																																						
NO-LOAD CURRENT	≤ 15 mA																																																						
RESIDUAL CURRENT	≤ 0.1 mA																																																						
RATED INSULATION VOLTAGE	≤ 0.5 kV																																																						
SHORT-CIRCUIT PROTECTED	YES																																																						
MAX VOLTAGE DROP	≤ 1.8 V																																																						
WIRE BREAKAGE PROTECTION	INCORPORATED																																																						
REVERSE POLARITY PROTECTION	INCORPORATED																																																						
OUTPUT FUNCTION	3-WIRE, NORMALLY OPEN, PNP																																																						
MAX. SWITCHING FREQUENCY	≤ 3.0 kHz																																																						
HOUSING MATERIAL	METAL, A4 1.4404 (AISI 316L)																																																						
ACTIVE FACE MATERIAL	PLASTIC, PA12-GF20																																																						
CABLE	ø3.0, LifYY-11Y, TPU																																																						
SHOCK RESISTANCE	30 g, 11 ms																																																						
VIBRATION RESISTANCE	55 Hz, 1 mm AMPLITUDE (IN ALL 3 PLANES)																																																						
DEGREE OF PROTECTION	IP67																																																						
SWITCHING STATUS INDICATION	LED: YELLOW																																																						
																																																							
SOURCE DRAWING - FOR REFERENCE ONLY																																																							
RELATED DOCUMENTS		3RD ANGLE PROJECTION		THIS DRAWING IS PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.																																																			
1. 2. 3. 4.				3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax turck.com																																																			
MATERIAL		ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY		DRFT RDS DATE 04/17/08 DESCRIPTION BI 1-EG05-AP6X-0.2M-RS 4T																																																			
SEE NOTES				DSGN SCALE 1=1.0																																																			
FINISH		CONTACT TURCK FOR MORE INFORMATION		UNIT OF MEASUREMENT INCH [MILLIMETER]																																																			
SEE NOTES				IDENTIFICATION NO. S4609795																																																			
B DRAWING PROCESSED AS PART OF ECO 33971		CBM 04/06/11 33971		REV B																																																			
REV DESCRIPTION		BY DATE ECO NO.		FILE: S4609795 SHEET 1 OF 1																																																			