

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	00		G	EC 0G3C 0216 05	28 DEC 05	BSV	JLG

D

C

B




A

D


C

B

A



TYP SECTION THRU CAVITY



RECOMMENDED HOLE LAYOUT

- 1 .000015 GOLD ON CONTACT AREA, .000100-.000200 MATTE-TIN LEAD IN AREA A, ALL OVER .000050 MIN NICKEL.
- 2 "AMP" TRADEMARK SHALL BE ON PART
- 3 TOLERANCE NON-CUMULATIVE.
- 4 DIMENSION APPLIES AT BASE OF HOUSING.
- 5 DIMENSION APPLIES TO AREA BELOW BASE OF SHROUD.
- 6 OBSOLETE PART NUMBER
- 7 .000015 GOLD ON CONTACT AREA, .000100-.000200 MATTE-TIN IN AREA A, ALL OVER .000050 MIN NICKEL.

7	3.320	3.030	3.000	2.500	25	52	5-102826-1
1	2.220	1.930	1.900	1.400	14	30	6 102826-3
1	2.720	2.430	2.400	1.900	19	40	6 102826-2
1	3.320	3.030	3.000	2.500	25	52	102826-1
FINISH	F	E	D	C	B	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	17-9-81	Tyco Electronics Corporation Harrisburg, Pa 17105-3608			
DIMENSIONS: INCHES		CHK	29-9-81				
		APVD	8-10-81	NAME			
		PRODUCT SPEC		HEADER ASSY, MOD II, .025 SQ POST, .100 X .100 C/L, DOUBLE ROW			
MATERIAL HSG : 20% FLAME RETARDANT GLASS FILLED NYLON COLOR : BLACK POST : PHOS-BRZ		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± 0° 30'		APPLICATION SPEC		SIZE CAGE CODE DRAWING NO	
FINISH		WEIGHT		A2 00779		C=102826	
POSTS : SEE TABLE		CUSTOMER DRAWING		SCALE 3:1		SHEET 1 OF 1	
						REV G	