




C	ZINC DIECAST BODY AND HEAD WITH STEEL COVER, BODY AND COVER FINISHED IN RED EPOXY PAINT HEAD FINISHED IN BLACK EPOXY PAINT
D	RED GLASS FILLED POLYESTER HOUSING AND COVER, ZINC DIECAST HEAD FINISHED IN BLACK EPOXY PAINT
E	ZINC DIECAST BODY AND HEAD WITH STEEL COVER, BODY AND COVER FINISHED IN RED EPOXY PAINT, HEAD FINISHED IN BLACK EPOXY PAINT 3 - CONDUIT

A	1/2" NPT X 1/4 CONDUIT THREAD ADAPTER REQUIRED FOR GSD AND GSE PRODUCT
	1/2" NPT X 1/4 CONDUIT THREAD GSA PRODUCT
	PG 13.5 CONDUIT THREAD NO ADAPTER REQUIRED
	M20 X 1.5 CONDUIT THREAD ADAPTER REQUIRED WITH GSD PRODUCT ONLY
B	PF 1/2 CONDUIT THREAD ADAPTER REQUIRED WITH GSD PRODUCT ONLY

AVAILABLE IN GSC, GSD, AND GSE		AVAILABLE IN GSE ONLY	
01	SNAP-ACTION CONTACTS	40	SLOW-ACTION CONTACTS (BREAK BEFORE MAKE)
07	SNAP-ACTION CONTACTS (GOLD PLATED CONTACTS)	41	SLOW-ACTION CONTACTS (BREAK BEFORE MAKE) (GOLD PLATED CONTACTS)
03	SLOW-ACTION CONTACTS (BREAK BEFORE MAKE)	42	SLOW-ACTION CONTACTS (BREAK BEFORE MAKE)
33	SLOW-ACTION CONTACTS (BREAK BEFORE MAKE) (GOLD PLATED CONTACTS)	43	SLOW-ACTION CONTACTS (BREAK BEFORE MAKE) (GOLD PLATED CONTACTS)
06	SLOW-ACTION CONTACTS (2 NORMALLY CLOSED)	44	SLOW-ACTION CONTACTS (BREAK BEFORE MAKE)
36	SLOW-ACTION CONTACTS (2 NORMALLY CLOSED) (GOLD PLATED CONTACTS)	45	SLOW-ACTION CONTACTS (BREAK BEFORE MAKE) (GOLD PLATED CONTACTS)
46	SLOW-ACTION CONTACTS (BREAK BEFORE MAKE)	47	SLOW-ACTION CONTACTS (BREAK BEFORE MAKE) (GOLD PLATED CONTACTS)



NOTES:

1 - MAXIMUM OPERATING TORQUE - 12 Nm / 11 in-lb

2 - MAXIMUM DISCONNECT TORQUE - 16 Nm / 15 in-lb

3 - MAXIMUM TIGHTENING TORQUE FOR FIXING SCREW - 0.5Nm/4.4in-lb (GSC & GSE PRODUCTS)

4 - 0.339Nm/3 in-lb (GSD PRODUCTS)


5 - IP66/IP67 NEMA 1,4X(INDOOR USE ONLY),12,13 FOR GSD PRODUCTS

ELECTRICAL RATING - I _{th} = 10A					ENVIRONMENTAL	APPROVALS
SILVER CONTACTS				GOLD PLATED CONTACTS		
AC FOR SWITCH CODES 01, 07, 03, 33	AC FOR SWITCH CODES 06, 36	AC FOR SWITCH CODES 40,41,42,43,44,45,46,47	DC			
A600 AC15 U _e I _e	A500 AC15 U _e I _e	A300 AC15 U _e I _e	Q300 DC13 U _e I _e	1V 10uA MIN 50V 100mA MAX	IP66 NEMA 1, 4, 12, 13 TEMP RANGE: -40°C TO +85°C -40°F TO +185°F STORAGE: -40°C TO +85°C -40°F TO +185°F SHOCK: 50G PER IEC 68-2-27 VIBRATION: 100G PER IEC 68-2-6	  IEC 947-5-1 EN50047
VOLTS AMPS 120 6 240 3 380 1.9 480 1.5 500 1.4 600 1.2	VOLTS AMPS 120 6 240 3 380 1.9 480 1.5 500 1.4	VOLTS AMPS 120 6 240 3	VOLTS AMPS 125 0.55 250 0.27			

CONTACT CLOSED

CONTACT OPEN

** POSITIVE OPENING TO IEC 947-5-1

THIRD ANGLE PROJECTION			
			
SCALE	FULL		
DO NOT SCALE PRINT			
TOLERANCES			
APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE :			
NO PLACES ONE PLACE TWO PLACES THREE PLACES ANGLES	DIM. FRA. 1/16 0.015 0.157-006	DIM. IN. 1/8 0.005 0.010-006	TOL. FRA. 0.001/0.03 0.001/0.015 0.010-006
SI METRIC ☒		US CUSTOMARY ☐	
DESIGN UNITS		TBD	
WEIGHT		TBD	