





REV.	DATE	DESCRIPTION
NC	06/11/00	INITIAL RELEASE
A	07/01/04	UPDATE DRAWING FORMAT



RECOMMENDED
CABLE STRIPPING DIM'S

NOTES:

1. CRIMPRED FERRULE HEX CRIMP SIZE .187"

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS	DATE	Amphenol Connex BNC R/A CRIMP PLUG (AT&T 735A CABLE)								
8						DRAWN	G.R.S.					07/01/04				
7						CHECKED										
6						ISSUED			PART DESCRIPTION							
5	NUT	BRASS	NICKEL	1		SHEET	1 OF 1	PART NO.								
4	FERRULE	COPPER	NICKEL	1				112962								
3	CONTACT PIN	BRASS	GOLD	1				DWG. NO. 112962.DWG								
2	INSULATOR	TEFLON	NATURAL	1		CAD FILE		C:/112/112962.DWG	REV. A	SIZE A	SCALE NA					
1	BODY	BRASS	NICKEL	1												
	DESCRIPTION	MATERIAL	FINISH	QTY												

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[112962](#)