

MICRO SWITCH

FREEPORT ILLINOIS, U.S.A
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929

SWITCH - BASIC

CATALOG LISTING

BE-2R059-A41

BE-2R059-A41
PAGE 1 OF 1

M

DRAWING
NUMBER

2

X

4

ISSUE

RELEASE NO. PR-6352

CHECK

CHECK

CHECK

CHECK

CHECK


CHECK

CHECK

CHECK

CHECK

CHECK



NOTE -

① - MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .139 MAX DIA ON $1.000 \pm .002$ CENTERS

2 - PLASTIC MATERIAL USED:


CASE ---- DUREZ 16274 OR EQUIVALENT (NORMALIZED)

COVER ---- GE 12983 OR EQUIVALENT (NORMALIZED)

PLUNGER -- GE EF-4530 OR EQUIVALENT

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS

OPERATING FORCE ---- 24 OZ MAX

RELEASE FORCE ---- 10 OZ MIN

DIFFERENTIAL TRAVEL ---- .0075 MAX

OVERTRAVEL ---- .015 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

25A-125, 250, 480VAC
1HP-125VAC; 2HP-250 or 480VAC
PILOT DUTY 750VA-480VAC, MAX
60/75°C (Cu)



SCALE FULL

DO NOT SCALE PRINT

TOLERANCES

APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE ±

DIM.	TOL.	DIM.	TOL.
mm	mm/in	in	mm/in
NO PLACES	X	1/64	
ONE PLACE	X,X	0.4/016	X,X
TWO PLACES	X,XX	0.15/006	X,XX
THREE PLACES	X,XXX		X,XXX
ANGLES			

SI METRIC

US CUSTOMARY

DESIGN UNITS

WEIGHT

RASTER

FO-52848-A

DRAWN

K P K123 FEB 77

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[BE-2R059-A41](#)