

THIS DRAWING IS UNPUBLISHED

RELEASED FOR PUBLICATION

2008

© COPYRIGHT 2008

Tyco Electronics AMP GmbH

ALL RIGHTS RESERVED.

LOC
IRDIST
-

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	D10	OBSOLETE 964339-6 AND UPDATE PACK 964339-3	02AUG2018	SV	PKS
	D11	ADDED FRONT VIEW AND DIMENSIONS	03JUNE2019	MB	PKS
	D12	3-964339-2 REMOVED FROM GENERAL SALES	29JAN2020	JA	PKS

- 1 SLOT ACCEPTS:
SINGLE MAGNET WIRE Ø0.40...0.63
DOUBLE MAGNET WIRE SAME DIAMETERS Ø0.40...0.56mm
Kontakt geeignet fuer
Lackdraht. Einzeldraht Ø0.40...0.63mm
Lackdraht. zwei Draehle gleichen Durchmessers Ø0.40-0.56mm
- 2 POKE IN TAB TERMINAL 3.4x0.5mm
Poke in Flachstecker 3.4x0.5mm
- 3 AREA WILL BE CUT BY TERMINATION
Bereich wird beim Kontaktieren abgelrennt
- 4 CAVITY ACCORDING TO TE SPEC. 411-18512
Kontakt Kammer nach TE Spec. 411-18512
- 5 IDENTIFICATION NO. FOR MAGNET WIRE RANGE (10)
Kennziffer fuer Lackdrahtbereich (10)
- 6 OVER THE MARKED LENGTH:
UNDER GOLD FILM
SELECTIVE PALLADIUM OVER NICKEL
Ueber die gekennzeichnete Laenge:
Unter Goldschicht
selekt. Palladium ueber Nickel
- 7 WORKING TEMPERATURE 150°C
Einsatztemp. 150°C

- 8 REELED WITH PAPER INTERLAYER 0-737976-1
ON PLASTIC REEL 1-725652-0
Reeling mit Papierzwischenlage 0-737976-1
auf Kunststoffspulen 1-725652-0
- 9 REELED WITH PAPER INTERLAYER 782504-5
ON PLASTIC REEL 973053-3
Reeling mit Papierzwischenlage 782504-5
auf Kunststoffspulen 973053-3
- 10 REELED WITH PAPER INTERLAYER 1-782504-1
ON PLASTIC REEL 725652-4
Reeling mit Papierzwischenlage 1-782504-1
auf Kunststoffspulen 725652-4
- 11 REELED WITH PAPER INTERLAYER 1-782504-1
ON CARDBOARD REEL 973053-1
Reeling mit Papierzwischenlage 1-782504-1
auf Pappbandspute 973053-1

	2-964339-7	10	A	-	CuNiSi	FLASH GOLD OVER NICKEL	
	2-964339-2		A	-	CuNiSi	TIN PLATED	-
OBSOLETE	964339-7		B	6 7	CuNiSi		
OBSOLETE	964339-6		1		CuNiSi	NICKEL	
	964339-5	11	D	-	CuNiSi	vorverzinnt	-
	964339-3	11	C	-	CuZn	vorverzinnt	-
	964339-2		B	-	CuNiSi	vorverzinnt	-
	964339-1		B	-	CuNiSi	BLANK	-
	PART NO	REV.	PCS.		MATERIAL	SURFACE COLOUR	ITEM NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN Rudolph 16-03-05

CHK H. Polßer 20-03-95

APVD -

PRODUCT SPEC

108-2012


APPLICATION SPEC

114-2046

WEIGHT

-

Customer Drawing

DIMENSIONS:
mmTOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC	±.7
1 PLC	±.7
2 PLC	±.7
3 PLC	±.7
4 PLC	±.7
ANGLES	±1°
FINISH	

MATERIAL

SEE TABLE

SEE TABLE

TE

TE Connectivity

NAME

MAG MATE LEAF TERMINAL
MARK II

SIZE

A3

CAGE CODE

00779

C-964339

DRAWING NO


SCALE 10:1

SHEET 1 OF 1

RESTRICTED TO

D12

DIRECTION OFF TOP OF REEL



Spec. 107-3 Fig. 272

B-B

