



PRODUCT NUMBER

20020034-XXXXXXLF

20020034-□ □ □ □ B 0 □ L F

PITCH

G: 5.00 mm
H: 5.08 mm

POLES

02: 2 POLES
03: 3 POLES
.....
24: 24 POLES

LF : DENOTED RoHS COMPATIBLE

1 : STANDARD PRODUCT
W/ BOX PACKING

HOUSING CODE

CODE	COLOR	AVAILABILITY
1	GREEN(RAL 6018/T)	STANDARD
2	BLACK	ON REQUEST ONLY
3	GREY(RAL 7004/P)	ON REQUEST ONLY
4	BLUE(RAL 5015/A)	ON REQUEST ONLY

PROPERTY TABLE				
FCI SERIES NAME		35-500	35-508	
PITCH (mm)		5.00	5.08	
VOLTAGE RATING (VAC)		300	300	
CURRENT RATING (A)		10	10	
APPLICABLE WIRE RANGE (AWG)	1-WIRE	12~26	12~26	
	2-WIRE	NA	NA	
WIRE CROSS SECTION (mm ²)	SOLID	1-WIRE	2.5	2.5
		2-WIRE	NA	NA
	STRANDED	1-WIRE	2.5	2.5
		2-WIRE	NA	NA
OPENING CONTACT HOUSING(mm ²)		2.4x3.0	2.2x2.7	
WIRE STRIP LENGTH(mm)		9~10	9~10	
WITHSTANDING VOLTAGE (kV)		1.6	1.6	
OPERATING TEMP. (°C)		-40~+115	-40~+115	
POLES AVAILABLE		02~24	02~24	
SAFETY CERTIFICATE				



NOTES:

1. MATERIALS

- 1-1 HOUSING: THERMALPLASTIC RESIN, UL 94V-0 RATED.
- 1-2 INSULATING LEVER: THERMALPLASTIC RESIN, UL 94V-0 RATED.
- 1-3 WIRE GUARD : STAINLESS STEEL.
- 1-4 TERMINAL: COPPER ALLOY, TIN PLATED.
- 1-5 SCREW: STEEL, ZINC PLATED.
2. PRODUCT SPECIFICATION REFER TO FCI GS-12-625.
3. PRODUCT PACKING SPECIFICATION REFER TO FCI GS-14-1394.
4. FCI, SAFETY CERTIFICATE LOGO AND SERIES NAME TO BE SHOWN ON PRODUCT SURFACE.
5. THE PRODUCTS WHERE THE PART NUMBER END IN "LF" MEET THE EUROPEAN UNION DIRECTIVE AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.


mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection	product family
				tolerances unless otherwise specified			TERMINAL BLOCK
ltr	ecn no	dr	date				title
A	T11-0004	WL	011811				TERMINAL BLOCK
B	T-005306	WL	082311				PLUGGABLE SIGNAL PLUG, UPSIDE CONTACT W/FLANGE
				angles	X.±0.5	MM	
					X.X±0.3	[INCH]	
				X'±1"	X.XX±0.1	scale	
				dr	WENDY CHEN	113010	dwg no
				enrg	JASON HSU	113010	sheet 1 of 3
				chr	JASON HSU	113010	size
				appd	JASON HSU	113010	A4
							type
							CUSTOMER Drawing
sheet index	revision sheet	B	B	B	B	B	
		1	2	3			

PRODUCT NUMBER	SERIES NAME	PITCH
20020034-GXXXXXXLF	35-500	5.00 mm




N = Number of poles
 Dim. L=(N $\times$ 5.0[.197])+0.6[.111]
 Dim. P=(N-1) $\times$ 5.0[.197]
 Dim. T=(N $\times$ 5.0[.197])+10.62[.418]
 Dim. K=(N+1) $\times$ 5.0[.197]

POLES	Dim. L & P	Dim.T & K
2-6p	$\pm 0.15[.006]$	$\pm 0.15[.006]$
7-12p	$\pm 0.20[.008]$	$\pm 0.25[.010]$
13-18p	$\pm 0.25[.010]$	$\pm 0.30[.012]$
19-24p	$\pm 0.30[.012]$	$\pm 0.40[.016]$






SECTION A-A




mat'l. code				surface ASME Y14.5 ✓		tolerance ASME Y14.5		projection 		product family TERMINAL BLOCK			
ltr		ecn no		dr		date		tolerances unless otherwise specified		title			
B								angles		TERMINAL BLOCK			
								X.±0.5		PLUGGABLE SIGNAL PLUG, UPSIDE CONTACT			
								X.X±0.3		W/FLANGE			
								X'±1"					
								X.XX±0.1					
								dr		sheet 2 of 3			
								WENDY CHEN		size			
								engr		A4			
								JASON HSU					
								chr					
								JASON HSU					
								appd					
								JASON HSU					
sheet index		revision sheet											

PRODUCT NUMBER	SERIES NAME	PITCH
20020034-HXXXXXXLF	35-508	5.08 mm




N = Number of poles
 Dim. L = $(N \times 5.08 [.200]) + 0.5 [.020]$
 Dim. P = $(N - 1) \times 5.08 [.200]$
 Dim. T = $(N \times 5.08 [.200]) + 10.16 [.400]$
 Dim. K = $(N + 1) \times 5.08 [.200]$

Poles	Dim.L & P & T & K
2-6p	$\pm 0.20 [.008]$
7-12p	$\pm 0.30 [.012]$
13-16p	$\pm 0.40 [.016]$
17-24p	$\pm 0.50 [.020]$



SECTION A-A



mat'l. code				surface ASME Y14.5 ✓	tolerance ASME Y14.5	projection MM INCH	product family TERMINAL BLOCK
ltr	ecn no	dr	date	tolerances unless otherwise specified			title TERMINAL BLOCK PLUGGABLE SIGNAL PLUG, UPSIDE CONTACT W/FLANGE
B				angles X°±1°	X.±0.5 X.X±0.3 X.XX±0.1	scale	sheet 3 of 3 size A4
		dr	WENDY CHEN	113010			dwg no 20020034
		enr	JASON HSU	113010			
		chr	JASON HSU	113010			
		appd	JASON HSU	113010			
sheet index	revision sheet						type CUSTOMER Drawing