




LOC B	DIST —	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			BA1	ECN-21-126962	19NOV2021	RK	MZ
			BA2	MIN. ADDED TO NOTE 7	22AUG2022	DM	SM



SECTION B-B

- | | |
|--|---|
|  <p>WIRE BARRELS
FACE UP.</p> | <p>REELING
DIRECTION</p> |
| | <p>(C)</p> <p>AS. DIRECTION
'A', BUT
BARRELS DOWN</p> |
| | <p>→</p> <p>(A)</p> |
| | <p>←</p> <p>(B)</p> |

		STAINLESS STEEL	BRASS		5-163081-1
A		STAINLESS STEEL	BRASS	1-163082-6	1-163081-7
A		STAINLESS STEEL	PH. BRONZE		1-163081-5 
B		STAINLESS STEEL	PH. BRONZE		1-163081-4 
A		STAINLESS STEEL	BRASS		1-163081-3
B		STAINLESS STEEL	BRASS		1-163081-2
A		STAINLESS STEEL	BRASS	1-163082-0	1-163081-1
A		STAINLESS STEEL	BRASS	163082-1	163081-8
A		STAINLESS STEEL	BRASS	163082-2	163081-7
B		STAINLESS STEEL	BRASS		163081-2
B		STAINLESS STEEL	BRASS		163081-1
REELING	FINISH	SPRING MATERIAL	PIN BODY	LOOSE PIECE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. BRIGHT 24/10/11 CHK M. GREENER 24/10/11 APVD D. PENNINGTON 11/06/12		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±0.5 1 PLC ±0.15 2 PLC ±0.15 3 PLC ±0.15 4 PLC ± ANGLES ±2°		NAME TYPE III+, SIZE 16, PIN ASS'Y 18-16 AWG, 2.0-2.5mm DIA INSULATION	
		PRODUCT SPEC 108-10042 APPLICATION SPEC 114-10004		SIZE	RESTRICTED TO
MATERIAL		WEIGHT		CAGE CODE	DRAWING NO
SEE TABLE		SEE TABLE		A2 00779	C=163081
CUSTOMER DRAWING				SCALE	REVISION
				NTS	1 OF 1
					BA2