


## REVISIONS

DOC. NO. SPC-F005 \* Effective: 7/8/02 \* DCP No: 1398

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
1902	A	RELEASED	EO	05/08/06	TL	06/15/06	HO	06/15/06


 RoHS  
Compliant


NO	DESCRIPTION	MATERIAL	Q'TY	FINISH
10	CRIMP FERRULE	BRASS	1	NICKEL
9	INSULATION II	POM	1	NONE
8	BODY	BRASS	1	NICKEL
7	WASHER II	IRON	1	NICKEL
6	SPRING WASHER	SK-5	1	NICKEL
5	WASHER I	IRON	1	NICKEL
4	GASKET	RUBBER	1	RED
3	CENTER CONTACT	BRASS + PHOSPHOR BRONZE	1	GOLD
2	INSULATION I	POM	1	WHITE
1	SHELL	ZINC	1	NICKEL

DISCLAIMER:  
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED  
HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE  
BELIEVE TO BE ACCURATE AND RELIABLE. SINCE  
CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE  
USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT  
FOR THE INTENDED USE AND ASSUME ALL RISK AND  
LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:  
.X=±0.2  
.XX=±0.1  
.XXX=±0.05  
ANGLE=±5°

DRAWN BY:  
EKLAS ODISH 05/08/06  
CHECKED BY:  
THOMAS LEE 06/15/06  
APPROVED BY:  
HISHAM ODISH 06/15/06

DRAWING TITLE:  
Coaxial Connector, BNC, Male, 50 Ohms, Crimp Style, RG58/U  
SIZE DWG. NO. ELECTRONIC FILE REV  
A SPC20102 82K9782.DWG A  
SCALE: NTS U.O.M.: mm [Inches] SHEET: 1 OF 1