



LineGard | PGFI Series 15 Amp Plug Series GFCI / ELCI

INTRODUCTION

The LineGard™ 15 Amp Plug Series is a ground fault circuit interrupter designed and manufactured by North Shore Safety, Ltd., a leader in innovated safety products. The PGFP product is rated for 15 amps at 120 VAC and available in either manual (safe start) or automatic reset configuration.

Standard offerings include products geared for maintenance repair organizations (MRO), original equipment manufacturers (OEM) or general portable power applications. MRO products are supplied with heavy-duty 12/3 conductor high flex (indoor/outdoor) safety yellow cable (SJTW type) capable of withstanding heavy trade or industrial use. OEM products are configured with robust 14/3 conductor (indoor/outdoor) black cable (SJTW type) for integration into trade related equipment. All products are industrial/trade grade tough and are backed by a 2 year manufacturer's warranty. Note that any cord or equipment updated with this device becomes OSHA compliant for power usage in a confined space and NEC compliant to NEC 590.6 (a) and (b).

FEATURES

- Bright LED power indicator
- Recessed interface buttons reduce damage and nuisance tripping from rough service
- High strength polycarbonate housing
- Class A cULus 943 listed with load side connector assemblies
- Assemblies without load side connectors are UL recognized for use under UL 943
- NEMA 3R rated (indoor / outdoor use)
- Assembly is rated for 15 amps / 120 VAC
- Available in automatic or manual reset configurations*
- Available with single or tri-tap plug assembly

SPECIFICATIONS

Listing Type	cULus Listed Class A UL 943
Rated Supply Voltage	120VAC
Rated Current	Up to 15 Amps or rating of wiring device and/or cable
Trip Level, Class A	5mA +/- 1mA (UL 943)
Operating Frequency	60 Hz
Reset Type¹	Automatic or Manual
Ground Trip Current	4 mA to 6 mA
Overload Current	90 Amps @ 125VAC
Insulation Voltage	1,500 VRMS for 1 minute
Endurance Operations	3000 operations
1. Manual configuration should be specified if automatic start-up after power restoration of circuit power creates an unsafe condition. 2. Integrated or replacement cable must be indoor/outdoor 3-conductor cable of type ST, SJT, SE, SJE, SO or SJO	

RELATED CODES

Confined Space	OSHA 29 CFR 1926.404 (b)(1)(ii), OSHA 29 CFR 1926.405 (a)(2)(ii)(G)
Construction Sites	(NEC 590.6)
Commercial Garages	(NEC 511.12)
Outdoor Signs	(NEC 600.10)
Fountains & Water Displays	(NEC 680.58)
Spa & Hot Tubs	(NEC 680.40)
Marinas & Boat Yards	(NEC 555.3)

APPLICATION OPPORTUNITIES:

Electrical wet locations
Power generators
Agricultural equipment
Outdoor electrical equipment
Cement cutting equipment
Portable electric heaters
Submersible pumps
Pipeline heaters
Automotive garages
Industrial part washers
Outdoor signage
Vending equipment

DECISION TABLES

1 Product Type		PGFP - M11 0 K Y - ST2			6 Cable Configuration	
2 Reset Type ⁽¹⁾		3 Cable Gauge		4 Cable Type	5 Connector	No designation No cable required (field wireable)
M11	Manual	No designation No cable required (field wireable)		No designation No cable required (field wireable)	No designation No cable required (field wireable)	ST2 Single-tap, 2' yellow cable
A11	Automatic	0 12 gauge, 3 conductor		K SJTW (yellow)	Y cULus 943 Listed	TT2 Tri-tap, 2' yellow cable
		1 14 gauge (15 amp)		J SJ00W (black)	N No connector	ST25 Single-tap, 25' yellow cable
		2 16 gauge (13 amp)				TT25 Tri-tap, 25' yellow cable
		3 18 gauge (10A)				ST50 Single tap, 50' yellow cable
						FL Flying leads, specify cable length in feet

Note: 1. Manual configuration should be specified if automatic power-up, after power restoration of circuit power, could create an unsafe condition.
2. Integrated or replacement cable must be indoor/outdoor 3-conductor cable of type ST, SJT, SE, SJE, S0 or SJO
3. Custom cord sets are available. Please consult Airpax for other options

