


CONDUIT THREAD

20.0
.79

23.0
.91

1 1/2" NPT X 14 CONDUIT THREAD ADAPTER
REQUIRED FOR GSD AND GSE PRODUCT

07	SNAP-ACTION CONTACTS (GOLD PLATED CONTACTS)	40	SLOW-ACTION CONTACTS (BREAK BEFORE MAKE)
		41	SLOW-ACTION CONTACTS (BREAK BEFORE MAKE) (GOLD PLATED CONTACTS)
03	SLOW-ACTION CONTACTS (BREAK BEFORE MAKE)		
	SLOW-ACTION CONTACTS		

44	SLOW-ACTION CONTACTS (BREAK BEFORE MAKE)
45	SLOW-ACTION CONTACTS (BREAK BEFORE MAKE) (GOLD PLATED CONTACTS)

Diagram illustrating the wiring for a 4-position selector switch (44 and 45) with slow-action contacts (Break Before Make). The diagram shows four positions (11, 12, 21, 22, 31, 32, 43, 44) and a common terminal (3Y, 1X).

ENVIRONMENTAL	APPROVALS
NEMA 1, 4, 12, 13  RANGE: -40°C TO +85°C -40°F TO +185°F RANGE: -40°C TO +85°C -40°F TO +185°F : 50G PER IEC 68-2-27 UTION: 100G PER IEC 68-2-6	  IEC 947-5-1 EN50047

CODE 2 , LEVER TO TOP

26° ** 5° 0° 5° 26° **

21-22
13-14

90°

2° 0° 2°

21-22
13-14

90°

WITH SWITCH CODE 01 & 07 BASIC

11° ** 5° 0° 5° 11° **

21-22
13-14

90°

WITH SWITCH CODE 03 & 33 BASIC

11° ** 5° 0° 5° 11° **

21-22
11-12

90°

WITH SWITCH CODE 06 & 36 BASIC

 CONTACT CLOSED
 CONTACT OPEN
****** POSITIVE OPENING TO IEC 947-5-1

CODE 2 , LEVER TO TOP

↔ | ↔

11° ** 5° 0° 5° 11° **

90° 11° 11° 90°

WITH SWITCH CODE 40 & 41 BASIC

↔ | ↔

11° ** 5° 0° 5° 11° **

90° 11° 11° 90°

WITH SWITCH CODE 42 & 43 BASIC

↔ | ↔

11° ** 5° 0° 5° 11° **

90° 11° 11° 90°

WITH SWITCH CODE 44 & 45 BASIC

↔ | ↔

11° ** 5° 0° 5° 11° **


90° 11° 11° 90°

WITH SWITCH CODE 46 & 47 BASIC


ELECTRICAL RATING - I _{th} = 10A					ENVIRONMENTAL		APPROVALS		
SILVER CONTACTS				GOLD PLATED CONTACTS		IP66 NEMA 1, 4, 12, 13  TEMP RANGE: -40°C TO +85°C -40°F TO +185°F STORAGE: -40°C TO +85°C -40°F TO +185°F SHOCK: 50G PER IEC 68-2-27 VIBRATION: 100G PER IEC 68-2-6		  IEC 947-5-1 EN50047	
AC FOR SWITCH CODES 01, 07, 03, 33		AC FOR SWITCH CODES 06, 36, 40, 41, 42, 43, 44, 45, 46, 47		DC					
A600 AC15 Ue Ie		A300 AC15 Ue Ie		Q300 DC13 Ue Ie					
VOLTS AMPS 120 6 240 3 380 1.9 480 1.5 500 1.4 600 1.2		VOLTS AMPS 120 6 240 3		VOLTS AMPS 125 0.55 250 0.27					
					1V 10uA MIN 50V 100mA MAX				

[illegible]


BODY CODES C AND D



ACTUATOR CODE 2




ACTUATOR CODE 1




ACTUATOR CODE 3


BODY CODE E



ACTUATOR CODE 2



ACTUATOR CODE 1



ACTUATOR CODE 3

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.			
FED. MFG. CODE 91929		CATALOG LISTING	
MICRO SWITCH a Honeywell Division		LIMIT SWITCH	
DESIGN UNITS		SI METRIC	
WEIGHT		TBD	

THIRD ANGLE PROJECTION			
SCALE FULL			
DO NOT SCALE PRINT			
TOLERANCES			
APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE 1			
NO PLACES	ONE PLACE	TWO PLACES	THREE PLACES
ANGLES	ANGLES	ANGLES	ANGLES
SI METRIC	US CUSTOMARY	SI METRIC	US CUSTOMARY
DESIGN UNITS	SI METRIC	US CUSTOMARY	US CUSTOMARY
WEIGHT	TBD	WEIGHT	TBD

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Honeywell:

[GSDB03S1](#) [GSDB03S2](#) [GSDB03S3](#) [GSDB03S3-1](#) [GSDB06S1](#) [GSDB06S2](#) [GSDB06S3](#) [GSEA24A1B](#) [GSEA24D](#)
[GSEA44S2](#) [GSDA03S1](#) [GSDA06S1](#) [GSEA06S1](#) [GSDA06S3](#) [GSDC06S3](#) [GSDA06S2](#) [GSDA03S2](#) [GSEB01D](#)
[GSEA44S1](#) [GSDA03S3](#) [GSEA44S3](#) [GSDC01D](#) [GSCA33S1](#) [GSEC46S3](#) [GSEC46S2](#) [GSEA40S2](#) [GSEC46S1](#)