

The RF MOSFET Line

RF Power Field Effect Transistors


N-Channel Enhancement-Mode Lateral MOSFETs

MRF19090R3
MRF19090SR3


Designed for Class AB PCN and PCS base station applications with frequencies from 1.9 to 2.0 GHz. Suitable for CDMA, TDMA, GSM, and multicarrier amplifier applications.

- Typical CDMA Performance: 1990 MHz, 26 Volts
IS-97 CDMA Pilot, Sync, Paging, Traffic Codes 8 Through 13
Output Power — 9 Watts
Power Gain — 10 dB
Adjacent Channel Power —
885 kHz: -47 dBc @ 30 kHz BW
1.25 MHz: -55 dBc @ 12.5 kHz BW
2.25 MHz: -55 dBc @ 1 MHz BW
- Internally Matched, Controlled Q, for Ease of Use
- High Gain, High Efficiency and High Linearity
- Integrated ESD Protection
- Designed for Maximum Gain and Insertion Phase Flatness
- Capable of Handling 10:1 VSWR, @ 26 Vdc, 1.93 GHz, 90 Watts (CW) Output Power
- Excellent Thermal Stability
- Characterized with Series Equivalent Large-Signal Impedance Parameters
- In Tape and Reel. R3 Suffix = 250 Units per 56 mm, 13 inch Reel.

1990 MHz, 90 W, 26 V
LATERAL N-CHANNEL
RF POWER MOSFETs



CASE 465B-03, STYLE 1
NI-880
MRF19090R3



CASE 465C-02, STYLE 1
NI-880S
MRF19090SR3

MAXIMUM RATINGS

Rating	Symbol	Value	Unit
Drain-Source Voltage	V_{DS}	65	Vdc
Gate-Source Voltage	V_{GS}	-0.5, +15	Vdc
Total Device Dissipation @ $T_C = 25^\circ\text{C}$ Derate above 25°C	P_D	270 1.54	Watts $\text{W}/^\circ\text{C}$
Storage Temperature Range	T_{stg}	- 65 to +150	$^\circ\text{C}$
Operating Junction Temperature	T_J	200	$^\circ\text{C}$

THERMAL CHARACTERISTICS

Characteristic	Symbol	Value	Unit
Thermal Resistance, Junction to Case	$R_{\theta JC}$	0.65	$^\circ\text{C}/\text{W}$

ESD PROTECTION CHARACTERISTICS

Test Conditions	Class
Human Body Model	1 (Minimum)
Machine Model	M3 (Minimum)


NOTE - CAUTION - MOS devices are susceptible to damage from electrostatic charge. Reasonable precautions in handling and packaging MOS devices should be observed.

ELECTRICAL CHARACTERISTICS (T_C = 25°C unless otherwise noted)

Characteristic	Symbol	Min	Typ	Max	Unit
OFF CHARACTERISTICS					
Drain-Source Breakdown Voltage (V _{GS} = 0 Vdc, I _D = 100 μA)	V _{(BR)DSS}	65	—	—	Vdc
Zero Gate Voltage Drain Current (V _{DS} = 28 Vdc, V _{GS} = 0 Vdc)	I _{DSS}	—	—	10	μAdc
Gate-Source Leakage Current (V _{GS} = 5 Vdc, V _{DS} = 0 Vdc)	I _{GSS}	—	—	1	μAdc
ON CHARACTERISTICS					
Forward Transconductance (V _{DS} = 10 Vdc, I _D = 3 Adc)	g _{fs}	—	7.2	—	S
Gate Threshold Voltage (V _{DS} = 10 Vdc, I _D = 300 μAdc)	V _{GS(th)}	2.0	—	4.0	Vdc
Gate Quiescent Voltage (V _{DS} = 26 Vdc, I _D = 750 mAdc)	V _{GS(Q)}	2.5	3.8	4.5	Vdc
Drain-Source On-Voltage (V _{GS} = 10 Vdc, I _D = 1 Adc)	V _{DS(on)}	—	0.10	—	Vdc
DYNAMIC CHARACTERISTICS					
Reverse Transfer Capacitance (1) (V _{DS} = 26 Vdc, V _{GS} = 0, f = 1 MHz)	C _{rss}	—	4.2	—	pF
FUNCTIONAL TESTS (In Motorola Test Fixture)					
Two-Tone Common-Source Amplifier Power Gain (V _{DD} = 26 Vdc, P _{out} = 90 W PEP, I _{DQ} = 750 mA, f = 1930 MHz and 1990 MHz, Tone Spacing = 100 kHz)	G _{ps}	10	11.5	—	dB
Two-Tone Drain Efficiency (V _{DD} = 26 Vdc, P _{out} = 90 W PEP, I _{DQ} = 750 mA, f = 1930 MHz and 1990 MHz, Tone Spacing = 100 kHz)	η	33	35	—	%
3rd Order Intermodulation Distortion (V _{DD} = 26 Vdc, P _{out} = 90 W PEP, I _{DQ} = 750 mA, f = 1930 MHz and 1990 MHz, Tone Spacing = 100 kHz)	IMD	—	-30	-28	dBc
Input Return Loss (V _{DD} = 26 Vdc, P _{out} = 90 W PEP, I _{DQ} = 750 mA, f = 1930 MHz and 1990 MHz, Tone Spacing = 100 kHz)	IRL	—	-12	—	dB
P _{out} , 1 dB Compression Point (V _{DD} = 26 Vdc, P _{out} = 90 W CW, f = 1990 MHz)	P1dB	—	90	—	W
Output Mismatch Stress (V _{DD} = 26 Vdc, P _{out} = 90 W CW, I _{DQ} = 750 mA, f = 1930 MHz, VSWR = 10:1, All Phase Angles at Frequency of Tests)	Ψ	No Degradation In Output Power Before and After Test			

(1) Part is internally matched both on input and output.

Freescale Semiconductor, Inc.



B1, B2	2 Ferrite Beads, Round, Ferroxcube #56-590-65-3B
B3, B34	Ferrite Beads, Surface Mount, Ferroxcube
C1, C18	0.4 - 2.5 pF Variable Capacitors, Johanson Gigatrim #27285
C2, C5, C8	10 pF Chip Capacitors, B Case, ATC #100B100CCA500X
C3	12 pF Chip Capacitor, B Case, ATC #100B120CCA500X
C4	0.3 pF Chip Capacitor, B Case, ATC #100B0R3CCA500X
C6, C7	120 pF Chip Capacitors, B Case, ATC #100B12R1CCA500X
C9, C12	0.1 μ F Chip Capacitors, Kemet #CDR33BX104AKWS
C10, C11	1000 pF Chip Capacitors, B Case, ATC #100B102JCA50X
C13, C17	22 μ F, 35 V Tantalum Chip Capacitors, Kemet #T491X226K035AS4394
C14, C16	10 μ F, 35 V Tantalum Chip Capacitors, Kemet #T495X106K035AS4394
C15, C19	1 μ F, 35 V Tantalum Chip Capacitors, Kemet #T495X105K035AS4394

L1, L2	8 Turns, #26 AWG, 0.085" OD, 0.330" Long, Copper Wire
R1, R2	270 Ω , 1/4 W Chip Resistors, Garrett Instruments #RM73B2B271JT
Z1	ZO = 50 Ohms
Z2	ZO = 50 Ohms, Lambda = 0.123
Z3	ZO = 15.24 Ohms, Lambda = 0.0762
Z4	ZO = 10.11 Ohms, Lambda = 0.0392
Z5	ZO = 6.34 Ohms, Lambda = 0.0711
Z6	ZO = 5.02 Ohms, Lambda = 0.0476
Z7	ZO = 5.54 Ohms, Lambda = 0.0972
Z8	ZO = 50.0 Ohms, Lambda = 0.194
Z9	ZO = 50.0 Ohms
Raw PCB Material	0.030" Glass Teflon [®] , $\epsilon_r = 2.55$, 2 oz Copper, 3" x 5" Dimensions

Figure 1. MRF19090 Test Circuit Schematic




Figure 2. MRF19090 Test Circuit Component Layout

Freescale Semiconductor, Inc.

TYPICAL CHARACTERISTICS




Figure 3. Class AB Performance versus Frequency




Figure 4. CDMA Performance ACPR, Gain and Drain Efficiency versus Output Power




Figure 5. Third Order Intermodulation Distortion versus Output Power




Figure 6. Intermodulation Products versus Output Power




Figure 7. Power Gain versus Output Power





Figure 8. Third Order Intermodulation Distortion and Gain versus Supply Voltage



$V_{DD} = 26 \text{ V}$, $I_{DQ} = 750 \text{ mA}$, $P_{out} = 90 \text{ Watts (PEP)}$

f MHz	Z_{source} Ω	Z_{load} Ω
1930	$4.5 - j6.1$	$1.1 - j4.5$
1960	$4.4 - j6.0$	$1.1 - j4.4$
1990	$4.3 - j6.1$	$1.1 - j4.3$

Z_{source} = Test circuit impedance as measured from gate to ground.

Z_{load} = Test circuit impedance as measured from drain to ground.





Figure 9. Series Equivalent Source and Load Impedance

Freescale Semiconductor, Inc.

PACKAGE DIMENSIONS




- NOTES:
1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M-1994.
 2. CONTROLLING DIMENSION: INCH.
 3. DIMENSION H IS MEASURED 0.030 (0.762) AWAY FROM PACKAGE BODY.
 4. RECOMMENDED BOLT CENTER DIMENSION OF 1.16 (29.57) BASED ON M3 SCREW.

DIM	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	1.335	1.345	33.91	34.16
B	0.535	0.545	13.6	13.8
C	0.147	0.200	3.73	5.08
D	0.495	0.505	12.57	12.83
E	0.035	0.045	0.89	1.14
F	0.003	0.006	0.08	0.15
G	1.100	BSC	27.94	BSC
H	0.057	0.067	1.45	1.70
K	0.175	0.205	4.44	5.21
M	0.872	0.888	22.15	22.55
N	0.871	0.889	19.30	22.60
Q	$\varnothing .118$	$\varnothing .138$	$\varnothing 3.00$	$\varnothing 3.51$
R	0.515	0.525	13.10	13.30
S	0.515	0.525	13.10	13.30
aaa	0.007	REF	0.178	REF
bbb	0.010	REF	0.254	REF
ccc	0.015	REF	0.381	REF

- STYLE 1:
1. DRAIN
 2. GATE
 3. SOURCE

CASE 465B-03
ISSUE C
NI-880
MRF19090R3



- NOTES:
1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M-1994.
 2. CONTROLLING DIMENSION: INCH.
 3. DIMENSION H IS MEASURED 0.030 (0.762) AWAY FROM PACKAGE BODY.

DIM	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	0.905	0.915	22.99	23.24
B	0.535	0.545	13.60	13.80
C	0.147	0.200	3.73	5.08
D	0.495	0.505	12.57	12.83
E	0.035	0.045	0.89	1.14
F	0.003	0.006	0.08	0.15
H	0.057	0.067	1.45	1.70
K	0.170	0.210	4.32	5.33
M	0.872	0.888	22.15	22.55
N	0.871	0.889	19.30	22.60
R	0.515	0.525	13.10	13.30
S	0.515	0.525	13.10	13.30
aaa	0.007	REF	0.178	REF
bbb	0.010	REF	0.254	REF
ccc	0.015	REF	0.381	REF

- STYLE 1:
1. DRAIN
 2. GATE
 3. SOURCE

CASE 465C-02
ISSUE A
NI-880S
MRF19090SR3

Information in this document is provided solely to enable system and software implementers to use Motorola products. There are no express or implied copyright licenses granted hereunder to design or fabricate any integrated circuits or integrated circuits based on the information in this document.

Motorola reserves the right to make changes without further notice to any products herein. Motorola makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does Motorola assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation consequential or incidental damages. "Typical" parameters that may be provided in Motorola data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals", must be validated for each customer application by customer's technical experts. Motorola does not convey any license under its patent rights nor the rights of others. Motorola products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the Motorola product could create a situation where personal injury or death may occur. Should Buyer purchase or use Motorola products for any such unintended or unauthorized application, Buyer shall indemnify and hold Motorola and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that Motorola was negligent regarding the design or manufacture of the part.

MOTOROLA and the Stylized M Logo are registered in the US Patent and Trademark Office. All other product or service names are the property of their respective owners. Motorola, Inc. is an Equal Opportunity/Affirmative Action Employer.

© Motorola Inc. 2004

HOW TO REACH US:

USA/EUROPE/LOCATIONS NOT LISTED:
Motorola Literature Distribution
P.O. Box 5405, Denver, Colorado 80217
1-800-521-6274 or 480-768-2130

JAPAN: Motorola Japan Ltd.; SPS, Technical Information Center,
3-20-1, Minami-Azabu, Minato-ku, Tokyo 106-8573, Japan
81-3-3440-3569

ASIA/PACIFIC: Motorola Semiconductors H.K. Ltd.; Silicon Harbour Centre,
2 Dai King Street, Tai Po Industrial Estate, Tai Po, N.T., Hong Kong
852-26668334

HOME PAGE: <http://motorola.com/semiconductors>



◇ **For More Information On This Product,
Go to: www.freescale.com**

MRF19090/D