

**ebm-papst St. Georgen GmbH & Co. KG**

Hermann-Papst-Str. 1

D-78112 St. Georgen

Phone +49 (0) 7724 81-0

Fax +49 (0) 7724 81-1309

info2@de.ebmpapst.com

www.ebmpapst.com

Nominal data

Type	422 JH	
Phase		1~
Nominal voltage	VDC	12
Nominal voltage range	VDC	8 .. 13,8
Speed (rpm)	min ⁻¹	17250
Power consumption	W	6.9
Min. ambient temperature	°C	-20
Max. ambient temperature	°C	70
Air flow	m ³ /h	38
Sound power level	B	6.6
Sound pressure level	dB(A)	54

ml = Max. load · me = Max. efficiency · fa = Free air · cs = Customer specification · ce = Customer equipment
Subject to change



Technical description

Weight	0.045 kg
Dimensions	40 x 40 x 28 mm
Impeller material	Glass-fiber reinforced PA plastic
Housing material	Glass-fiber reinforced PBT plastic
Airflow direction	Exhaust over struts
Direction of rotation	Counterclockwise, viewed toward rotor
Storage	Ball bearing
Service life L10 at 20 °C	60.000 h
Service life L10 at 60 °C	30.000 h
Cable	With leads AWG 28, UL 1061
Approval	VDE, CSA, UL
Option	Possible custom designs: Speed signal Go / No-go alarm External temperature sensor PWM control input Moisture protection Salt spray protection

Technical drawing of the 3D-printed part showing dimensions and tolerances:

- Top view dimensions: $40 \pm 0,15$ (width), $28 \pm 0,25$ (depth), $32 \pm 0,3$ (height), $38,4 \pm 0,25$ (total height).
- Side view dimensions: 310 ± 10 (length), 6 ± 1 (thickness), $3 \pm 0,15$ (filament diameter).
- Bottom view dimensions: $\emptyset 3,7 \pm 0,15$ (hole diameter), $\emptyset 4,5 \pm 0,2$ (hole diameter), $\emptyset 42,5 \pm 0,3$ (hole diameter).

Curves

