


NOTE

1.52610-**23のアクチュエータはハウジング内に押し下げた状態とする。
詳細寸法については図面 526101002 PSD 000 を参照下さい。
ACTUATOR OF PART NO. 52610-**23 SHOULD BE LOCKED.
RE DETAILD DIMENSIONS, SEE 526101002 PSD 000.

2.梱包数量：1000個/リール
NUMBER OF CONNECTORS：1000 PCS/REEL


3.リードテープ長さ LEAD TAPE LENGTH



4.カバーテープの剥離強度については、IEC60286-3に準拠。
COVER TAPE PEEL FORCE IS DEFINED BY IEC60286-3.

5.材料 MATERIAL
キャリアテープ：ポリプロピレン
トップテープ：PET, PE, PEF
リール：ポリスチレン <リサイクル材を含む>
CARRIER TAPE：POLYPROPYLENE
TOP TAPE：PET, PE, PEF
REEL：POLYSTYRENE (PS) < RECYCLE MATERIAL CONTAINED >

6.ELV及びRoHS適合品。
ELV AND RoHS COMPLIANT.







MODEL NO. 52610-**34

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION													
RELEASED EC NO: 106044 DRWN: YMIZUNO02 CHK'D: TKUSUHARA01 APPR: TKUSUHARA01	2016/12/16 2016/12/28 2016/12/28	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE		molex®					
				mm		---							
		ANGULAR TOL ± 3.0 °		DRWN BY		DATE		1.0 FPC CONN ZIF ASSY SMT ST EMBSTP PKG					
		4 PLACES ± 0.2		YMIZUNO02		2016/12/16							
		3 PLACES ± 0.2		CHK'D BY		DATE							
		2 PLACES ± 0.2		YKOBAYASHI02									
		1 PLACE ± 0.2		APPR BY		DATE		PRODUCT CUSTOMER DRAWING					
		0 PLACES ± 0.2		TKUSUHARA01		2016/12/28							
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DRAWING SIZE		THIRD ANGLE PROJECTION		SERIES		MATERIAL NUMBER		CUSTOMER	
				A3				52610		SEE CHART		GENERAL	
						DOCUMENT NUMBER		DOC TYPE		DOC PART		SHEET NUMBER	
				526100002		PSD		000		1 OF 5			

GENERAL TOLERANCES (UNLESS SPECIFIED)		
10 UNDER		±0.2
10 OVER 30 UNDER		±0.25
30 OVER		±0.3

RELEASE STATUS	P1	RELEASE DATE	2016/12/28	05:20:08
----------------	----	--------------	------------	----------



24	29.4	25.4	15.25	11.32	52610-1034	10
			14.25	10.32	52610-0934	9
			13.25	9.32	52610-0834	8
			12.25	8.32	52610-0734	7
			11.25	7.32	52610-0634	6
キャリアテープ幅 CARRIER TAPE WIDTH	D	C	(B)	(A)	MATERIAL NO.	極数 CKT

RELEASE STATUS	P1	RELEASE DATE	2016/12/28	05:20:08
----------------	----	--------------	------------	----------

GENERAL TOLERANCES (UNLESS SPECIFIED)		
10 UNDER		$\pm$ 0.2
10 OVER 30 UNDER		$\pm$ 0.25
30 OVER		$\pm$ 0.3

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

RELEASED

2016/12/16
2016/12/28
2016/12/28

EC NO: 106044
DRWN: YMIZUNO02
CHK'D: TKUSUHARA01
APPR: TKUSUHARA01

A

REV

GENERAL TOLERANCES
(UNLESS SPECIFIED)

ANGULAR TOL $\pm$ 3.0 °

4 PLACES

$\pm$ 0.2

3 PLACES

$\pm$ 0.2

2 PLACES

$\pm$ 0.2

1 PLACE

$\pm$ 0.2

0 PLACES

$\pm$ 0.2

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION UNITS

mm

SCALE

DRWN BY

YMIZUNO02

DATE

2016/12/16

CHK'D BY

YKOBAYASHI02

DATE

APPR BY

TKUSUHARA01

DATE

2016/12/28

DRAWING SIZE

A3

THIRD ANGLE PROJECTION

1.0 FPC CONN ZIF ASSY SMT ST EMBSTP PKG

PRODUCT CUSTOMER DRAWING

SERIES

52610

MATERIAL NUMBER

SEE CHART

CUSTOMER

GENERAL

DOCUMENT NUMBER

526100002

DOC TYPE




PSD

DOC PART

000

SHEET NUMBER

2 OF 5



32	37.4	33.4	20.25	16.32	52610-1534	15
			19.25	15.32	52610-1434	14
			18.25	14.32	52610-1334	13
			17.25	13.32	52610-1234	12
			16.25	12.32	52610-1134	11
キャリアテープ幅 CARRIER TAPE WIDTH	D	C	(B)	(A)	MATERIAL NO.	極数 CKT

GENERAL TOLERANCES (UNLESS SPECIFIED)		
10 UNDER		± 0.2
10 OVER 30 UNDER		± 0.25
30 OVER		± 0.3

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

RELEASED

EC NO: 106044
DRWN: YMIZUNO02
CHK'D: TKUSUHARA01
APPR: TKUSUHARA01

2016/12/16
2016/12/28
2016/12/28

GENERAL TOLERANCES
(UNLESS SPECIFIED)

ANGULAR TOL $\pm 3.0^\circ$

4 PLACES ± 0.2

3 PLACES ± 0.2

2 PLACES ± 0.2

1 PLACE ± 0.2

0 PLACES ± 0.2

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION UNITS
mm

SCALE

DRWN BY
YMIZUNO02

DATE
2016/12/16

CHK'D BY
YKOBAYASHI02

DATE

APPR BY
TKUSUHARA01

DATE
2016/12/28

DRAWING SIZE
A3

THIRD ANGLE PROJECTION

molex®

1.0 FPC CONN ZIF ASSY SMT ST EMBSTP PKG

PRODUCT CUSTOMER DRAWING

SERIES
52610

MATERIAL NUMBER
SEE CHART




CUSTOMER
GENERAL

DOCUMENT NUMBER
526100002

DOC TYPE
PSD

DOC PART
000


SHEET NUMBER
3 OF 5



44	49.4	45.4	31.25	27.32	52610-2634	26
			30.25	26.32	52610-2534	25
			29.25	25.32	52610-2434	24
			28.25	24.32	52610-2334	23
			27.25	23.32	52610-2234	22
			26.25	22.32	52610-2134	21
			25.25	21.32	52610-2034	20
			24.25	20.32	52610-1934	19
			23.25	19.32	52610-1834	18
			22.25	18.32	52610-1734	17
			21.25	17.32	52610-1634	16
キャリアテープ幅 CARRIER TAPE WIDTH	D	C	(B)	(A)	MATERIAL NO.	極数 CKT

GENERAL TOLERANCES (UNLESS SPECIFIED)		
10 UNDER		±0.2
10 OVER 30 UNDER		±0.25
30 OVER		±0.3

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION												
RELEASED EC NO: 106044 DRWN: YMIZUNO02 CHK'D: TKUSUHARA01 APPR: TKUSUHARA01	2016/12/16 2016/12/28 2016/12/28	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE		molex®				
		ANGULAR TOL ± 3.0 °		mm		---						
		4 PLACES	± 0.2	DRWN BY		DATE		1.0 FPC CONN ZIF ASSY SMT ST EMBSTP PKG				
		3 PLACES	± 0.2	YMIZUNO02		2016/12/16						
		2 PLACES	± 0.2	CHK'D BY		DATE		PRODUCT CUSTOMER DRAWING				
		1 PLACE	± 0.2	YKOBAYASHI02								
A	REV	0 PLACES	± 0.2	APPR BY		DATE		SERIES				
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		TKUSUHARA01		2016/12/28		MATERIAL NUMBER				
				DRAWING SIZE		THIRD ANGLE PROJECTION		CUSTOMER				
				A3				GENERAL				
				DOCUMENT NUMBER		DOC TYPE		DOC PART				
				526100002		PSD		000				
								SHEET NUMBER				
								4 OF 5				









56	61.4	57.4	35.25	31.32	52610-3034	30
キャリアテープ幅 CARRIER TAPE WIDTH	D	C	(B)	(A)	MATERIAL NO.	極数 CKT

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

GENERAL TOLERANCES (UNLESS SPECIFIED)		2016/12/16 2016/12/28 2016/12/28		RELEASED EC NO: 106044 DRWN: YMIZUNO02 CHK'D: TKUSUHARA01 APPR: TKUSUHARA01		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE		molex®			
						ANGULAR TOL ± 3.0 °		mm		---					
						4 PLACES ± 0.2		DRWN BY		DATE		1.0 FPC CONN ZIF ASSY SMT ST EMBSTP PKG			
						3 PLACES ± 0.2		YMIZUNO02		2016/12/16					
						2 PLACES ± 0.2		CHK'D BY		DATE		PRODUCT CUSTOMER DRAWING			
1 PLACE ± 0.2		YKOBAYASHI02													
0 PLACES ± 0.2		APPR BY		DATE		TKUSUHARA01 2016/12/28									
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DRAWING SIZE		THIRD ANGLE PROJECTION						SERIES		MATERIAL NUMBER		CUSTOMER	
		A3				52610		SEE CHART		GENERAL					
						DOCUMENT NUMBER		DOC TYPE		DOC PART		SHEET NUMBER			
10 UNDER		±0.2		A		REV		526100002		PSD		000		5 OF 5	
10 OVER 30 UNDER		±0.25													
30 OVER		±0.3													

RELEASE STATUS	P1	RELEASE DATE	2016/12/28	05:20:08
----------------	----	--------------	------------	----------






36.6	34.85	31.2	29	52610-3034	30
34.6	32.85	29.2	27	52610-2834	28
32.6	30.85	27.2	25	52610-2634	26
31.6	29.85	26.2	24	52610-2534	25
30.6	28.85	25.2	23	52610-2434	24
29.6	27.85	24.2	22	52610-2334	23
28.6	26.85	23.2	21	52610-2234	22
27.6	25.85	22.2	20	52610-2134	21
26.6	24.85	21.2	19	52610-2034	20
25.6	23.85	20.2	18	52610-1934	19
24.6	22.85	19.2	17	52610-1834	18
23.6	21.85	18.2	16	52610-1734	17
22.6	20.85	17.2	15	52610-1634	16
21.6	19.85	16.2	14	52610-1534	15
20.6	18.85	15.2	13	52610-1434	14
19.6	17.85	14.2	12	52610-1334	13
18.6	16.85	13.2	11	52610-1234	12
17.6	15.85	12.2	10	52610-1134	11
16.6	14.85	11.2	9	52610-1034	10
15.6	13.85	10.2	8	52610-0934	9
14.6	12.85	9.2	7	52610-0834	8
13.6	11.85	8.2	6	52610-0734	7
12.6	10.85	7.2	5	52610-0634	6
D	(C)	B	(A)	EMBOSSED PACKAGE ORDER NO. オーダー番号	極数 CKT
CONNECTOR SERIES NO. : 52610-**23					

GENERAL TOLERANCES (UNLESS SPECIFIED)		
10 UNDER		±0.2
10 OVER 30 UNDER		±0.25
30 OVER		±0.3

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		CURRENT REV DESC: REVISED		moLEX		
DIMENSION UNITS		SCALE		1.0 FPC CONN ZIF S/T HOUSING ASSY		
mm		---		PRODUCT CUSTOMER DRAWING		
GENERAL TOLERANCES (UNLESS SPECIFIED)		EC NO: 600129		DOCUMENT NUMBER		
ANGULAR TOL ± 3.0 °		DRWN: YCHEN128 2018/04/11		526101002		
4 PLACES ± 0.03		CHK'D: KTAHASHI 2018/04/12		PSD 000 B		
3 PLACES ± 0.03		APPR: NUKITA 2018/04/13		SHEET NUMBER		
2 PLACES ± 0.05		INITIAL REVISION:		1 OF 2		
1 PLACE ± 0.1		DRWN: YMIZUNO02 2016/12/16				
0 PLACES ± 0.2		APPR: TKUSUHARA01 2016/12/28				
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION				
		DRAWING				
		A3-SIZE				
		SERIES				
		52610				
		MATERIAL NUMBER				
		SEE TABLE				
		CUSTOMER				
		GENERAL				


DOCUMENT STATUS	P1	RELEASE DATE	2018/04/13	03:51:06
-----------------	----	--------------	------------	----------





36.6	34.85	31.2	29	52610-30 34	30
34.6	32.85	29.2	27	4 -28 34	28
32.6	30.85	27.2	25	-26 34	26
31.6	29.85	26.2	24	-25 34	25
30.6	28.85	25.2	23	-24 34	24
29.6	27.85	24.2	22	-23 34	23
28.6	26.85	23.2	21	-22 34	22
27.6	25.85	22.2	20	-21 34	21
26.6	24.85	21.2	19	-20 34	20
25.6	23.85	20.2	18	-19 34	19
24.6	22.85	19.2	17	-18 34	18
22.6	20.85	17.2	15	-16 34	16
21.6	19.85	16.2	14	-15 34	15
20.6	18.85	15.2	13	-14 34	14
19.6	17.85	14.2	12	-13 34	13
18.6	16.85	13.2	11	-12 34	12
16.6	14.85	11.2	9	-10 34	10
15.6	13.85	10.2	8	-09 34	9
14.6	12.85	9.2	7	-08 34	8
13.6	11.85	8.2	6	-07 34	7
12.6	10.85	7.2	5	52610-06 34	6
D	(C)	B	(A)	EMBOSSED PACKAGE ORDER No. オーダー番号	極数 CKT.
CONNECTOR SERIES NO. : 52610-***23					

REVISED EC NO: J2014-0096 DRWN: AISHII CHKD: KAKAHASHI APPR: YNOGAWA	DESCRIPTION REV 2013/07/18 2013/07/18 2013/08/19	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION						
		10 UNDER	±0.2	DRAWN BY AISHII	DATE 2013/02/20	TITLE 1.0 FPC CONN ZIF S/T HOUSING ASSY								
		10 OVER 30 UNDER	±0.25	CHECKED BY KAKAHASHI	DATE 2013/02/20									
		30 OVER	±0.3	APPROVED BY KMORIKAWA	DATE 2013/03/15	DOCUMENT NO. SD-52610-050								
		ANGULAR ±3 °		MATERIAL NO. SEE SHEET 2										
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION										



注記 (NOTES):
1. 材質 MATERIAL
ハウジング: ポリアミド (PA), ナチュラル (白色), ガラス充填, UL94V-0
HOUSING: POLYAMIDE, NATURAL (WHITE), GLASS FILLED, UL94V-0
アクチュエータ: ポリフェニレンサルファイド (PPS), ナチュラル (茶色), ガラス充填, UL94V-0
ACTUATOR: POLYPHENYLENE SULFID, NATURAL (BROWN), GLASS FILLED, UL94V-0
ターミナル: リン青銅 (t=0.32)
TERMINAL: PHOSPHOR BRONZE (t=0.32)

2. めっき仕様 PLATING
ターミナル TERMINAL
錫銀ビスマスめっき (1.0 μm以上)
TIN SILVER BISMUTH PLATING (1.0 MICROMETER MINIMUM)
下地: ニッケルめっき (1.0 μm以上)
UNDER PLATING: NICKEL PLATING (1.0 MICROMETER MINIMUM)

3. ソルダータール半田付け面のズレ量は、基準面 F に対し上方向0.05MAX., 下方向0.15MAX.とする。
MISALIGNMENT OF SOLDER TAILS FROM F UPPER DIRECTION: 0.05 MAX. LOWER DIRECTION: 0.15 MAX.

4. 偶数極に適用
APPLY FOR EVEN CIRCUIT.

5. R0.3はFPCの導体部にかからないこと。
R0.3 MUST NOT BE OVERLAPED TO PATTERN OF FPC.

6. エンボステープ梱包時は、アクチュエータがロックした状態とする。
IN THE PACKAGE, ACTUATOR OF PART NO.52610-**23 SHOULD BE LOCKED.

7. ソルダータールの平坦度は0.1mm以下とする。
SOLDERTAIL COPLANARITY IS 0.1MM MAXIMUM.

8. ELV及びRoHS適合品
ELV AND RoHS COMPLIANT

FPCについて ABOUT FPC
打ち抜き方向は導体側から補強板側を推奨します。
導体部については軟烙銅35 μmまたは50 μmを推奨します。
補強フィルム材質はポリイミドを推奨します。ベースフィルムは25 μmを推奨します。
接着剤は熱硬化接着剤を推奨します。
尚、接着剤の接点部への付着は導通不良の原因になりますので、染み出しが無い様、お願い致します。
RECOMMENDED PUNCHING DIRECTION: FROM CONDUCTOR SIDE TO STIFFENER SIDE
RECOMMENDED CONDUCTOR SPEC: SOFT COPPER FOIL
RECOMMENDED CONDUCTOR THICKNESS: 35 MICROMETER OR 50 MICROMETER
RECOMMENDED STIFFENER MATERIAL: POLYIMIDE
RECOMMENDED BASE FILM THICKNESS: 25 MICROMETER
RECOMMENDED ADHESIVE: THERMOSETTING ADHESIVE
NOTE: PLEASE PUT APPROPRIATE AMOUNT OF ADHESIVE ON ADHEREND BECAUSE THERE IS A POSSIBILITY THAT THE EXTRA ADHESIVE CAUSES THE DEFECT IN ELECTRICAL CONTINUITY.

偶数極に適用
APPLY FOR EVEN CIRCUIT.

R0.3はFPCの導体部にかからないこと。
R0.3 MUST NOT BE OVERLAPED TO PATTERN OF FPC.

エンボステープ梱包時は、アクチュエータがロックした状態とする。
IN THE PACKAGE , ACTUATOR OF PART NO.52610-**-23
SHOULD BE LOCKED.

ソルダーテールの平坦度は0.1mm以下とする。
SOLDERTAIL COPLANARITY IS 0.1MM MAXIMUM.

ELV及びRoHS適合品
ELV AND RoHS COMPLIANT


SEE SHEET 1 OF 2 EC NO: J2014-0096 DRAWN: AISHI CHKD: TAKAHASHI APPR: YNOGAWA REV	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION
		10 UNDER	± 0.2	DRAWN BY AISHI	DATE 2013/02/20	TITLE 1.0 FPC CONN ZIF S/T HOUSING ASSY		
		10 OVER 30 UNDER	± 0.25	CHECKED BY TAKAHASHI	DATE 2013/02/20			
		30 OVER	± 0.3	APPROVED BY KMORI KAWA	DATE 2013/03/15			
		ANGULAR ±3 °		MATERIAL NO.				
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SD-52610-050		
		SIZE A3 THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						

NOTES

1. 52610-**23のアクチュエータはハウジング内に押し下げた状態とする。
詳細寸法については図面SD-52610-050をご参照ください。
ACTUATOR OF PART NO. 52610-**23 SHULD BE LOCKED.
RE DETAILED DIMENSIONS, SEE SD-52610-050

2. 梱包数量: 1000個/リール
NUMBER OF CONNECTORS : 1000PCS/REEL


3. リードテープ長さ
LEAD TAPE LENGTH



4. カバーテープの剥離強度については、IEC60286-3に準拠
COVER TAPE PEEL FORCE IS DEFINED BY IEC60286-3.

5. 材料(MATERIAL)
キャリアテープ (CARRIER TAPE): ポリプロピレン (POLYPROPYLENE)
トップテープ (TOP TAPE): PET, PE, PEF
リール(REEL): ポリスチレン(PS)<リサイクル材を含む>
POLYSTYREN(PS) <RECYCLE MATERIAL CONTAINED>

6. ELV及びRoHS適合品
ELV AND RoHS COMPLIANT



RELEASED EC NO: J2013-1003 2013/02/20 DRWNA:ISHII 2013/02/20 CHKD:K TAKAHASHI 2013/02/20 APPR:KMORIKAWA 2013/03/15	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION						
		10 UNDER	± 0.3	DRAWN BY AISHII	DATE 2013/02/20	TITLE EMBOSS TAPE PACKAGED FOR 1.0 FPC CONN ZIF S/T HOUSING ASSY								
		10 OVER 30 UNDER	± 0.25	CHECKED BY KTAKAHASHI	DATE 2013/02/20									
		30 OVER	± 0.2	APPROVED BY KMORIKAWA	DATE 2013/03/15	molex								
		ANGULAR ±3 °		MATERIAL NO.							DOCUMENT NO.			SHEET NO.
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART							SD-52610-051			1 OF 5
	REV 0			SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									

10

9

8

7

6

5

4

3

2

1

F




E

D

C

B

A



24	29.4	25.4	15.25	11.32	52610-1034	10
			14.25	10.32	52610-0934	9
			13.25	9.32	52610-0834	8
			12.25	8.32	52610-0734	7
			11.25	7.32	52610-0634	6
キャリアテープ幅 CARRIER TAPE WIDTH	D	C	(B)	(A)	MATERIAL. NO.	極数 CKT.

SEE SHEET 1 OF 5 EC NO.: J2013-1003 DRW: AISHII 2013/02/20 CHKD: TAKAHASHI 2013/02/20 APPR: KMORIKAWA 2013/03/15	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
		10 UNDER	±0.3	DRAWN BY AISHII	DATE 2013/02/20	TITLE EMBOSS TAPE PACKAGED FOR 1.0 FPC CONN ZIF S/T HOUSING ASSY molex				
		10 OVER 30 UNDER	±0.25	CHECKED BY TAKAHASHI	DATE 2013/02/20					
		30 OVER	±0.2	APPROVED BY KMORIKAWA	DATE 2013/03/15					
		ANGULAR ±3 °		MATERIAL NO.		DOCUMENT NO.		SHEET NO.		
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SD-52610-051		2 OF 5			
	REV 0	SIZE A3 THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION								

9

8

7

6

5

4

3

2

10 9 8 7 6 5 4 3 2 1

F

E

D

C

B

A

F


E

D

C

B

A




32	37.4	33.4	20.25	16.32	52610-1534	15
			19.25	15.32	52610-1434	14
			18.25	14.32	52610-1334	13
			17.25	13.32	52610-1234	12
キャリアテープ幅 CARRIER TAPE WIDTH	D	C	(B)	(A)	MATERIAL. NO.	極数 CKT.

SEE SHEET 1 OF 5 EC NO.: J2013-1003 DRW: AISHII 2013/02/20 CHKD: KTAKAHASHI 2013/02/20 APPR: KMORIKAWA 2013/03/15	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
		10 UNDER	± 0.3	AISHII	2013/02/20	TITLE EMBOSS TAPE PACKAGED FOR 1.0 FPC CONN ZIF S/T HOUSING ASSY				
		10 OVER 30 UNDER	± 0.25	KTAKAHASHI	2013/02/20					
		30 OVER	± 0.2	KMORIKAWA	2013/03/15	molex				
		ANGULAR ±3 °		MATERIAL NO.						
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SD-52610-051			3 OF 5	

0	REV	SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		
---	-----	------------	--	--	--

9 8 7 6 5 4 3 2



DIMENSION STYLE MM ONLY	SCALE ---	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION
----------------------------	--------------	------------------------	---

tb_frame_A3_J_ME_S
Rev G 2012/01/25

