


4

3


2


1

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AA	27		F	REDWN & REV; OG1Z-0010-99	12MAY00	LMH	LHS



1. LOCKING LANCE FOR P/N -1 ONLY



.375	.850	.016	.031	.490	.650	.565	ø.39	.170	.925	1.080	2.25	606296-3
.500	.850	.016	.031	.490	.650	.565	ø.515	.170	.925	1.080	2.25	606296-2
.375	.850	.016	.031	.490	.650	.565	ø.39	.170	.925	1.080	2.25	606296-1
BOLT HOLE SIZE	L	K	J	H	G	F	E	D	C	B	A	PART NUMBER
DIMENSIONS, INCHES												
THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN L.HALL 18APR00		AMP Incorporated Harrisburg, PA 17105-3608 AMP TUBULAR TERMINAL 2/0 (ROUND TONGUE)						
				CHK L.H. SMITH 12MAY00								
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:				APVD B. ANTHONY 12MAY00		NAME				
		0 PLC ±				PRODUCT SPEC		SIZE A3				
		1 PLC ±				APPLICATION SPEC						
		2 PLC ± .02										
		3 PLC ± .005						CAGE CODE 00779				
		4 PLC ± .0005										
		ANGLES ± 3°						DRAWING NO C-606296				
MATERIAL HIGH CONDUCTIVITY WROUGHT COPPER		FINISH ELECTRO TIN PLATE				WEIGHT —		RESTRICTED TO				
CUSTOMER DRAWING						SCALE NTS		SHEET 1		OF 1		REV F