


ACTUATOR HEAD FOR POSITION SWITCH 3SE51/52  
ANGULAR ROLLER LEVER,  
METAL LEVER WITH PLASTIC ROLLER 22MM

**General technical details:**

<b>product designation</b>		actuator head for position switch
<b>Explosion protection category for dust</b>		none
<b>Mechanical operating cycles as operating time</b>		
• typical		15,000,000
<b>Resistance against vibration</b>		0.35 mm / 5g
<b>Resistance against shock</b>		30g / 11 ms
<b>Ambient temperature</b>		
• during operating	°C	-25 ... +85
• during storage	°C	-40 ... +90
<b>Material / of the enclosure</b>		
• of the switch head		metal
<b>Design of the operating mechanism</b>		metal lever, plastic roller
<b>Minimum actuating force / in activation direction</b>	N	10
<b>mounting position</b>		any
<b>Item designation</b>		
• according to DIN 40719 extendable after IEC 204-2 / according to IEC 750		E
• according to DIN EN 61346-2		T

**Certificates/approvals:**

**General Product Approval****Declaration of Conformity**

CCC



CSA



GOST




UL



VDE



EG-Konf.

**Test Certificates****other**[Special Test Certificate](#)[Confirmation](#)[Vibration Test Certificates](#)**Further information:****Information- and Downloadcenter (Catalogs, Brochures,...)**<http://www.siemens.com/industrial-controls/catalogs>**Industry Mall (Online ordering system)**<http://www.siemens.com/industrial-controls/mall>**CAx-Online-Generator**<http://www.siemens.com/cax>**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**<http://support.automation.siemens.com/WW/view/en/3SE5000-0AF01/all>**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3SE5000-0AF01](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3SE5000-0AF01)**last change:**

Jul 1, 2013