

SuperTan[®] Wet Tantalum Capacitors with Hermetic Seal



Vishay ST represents a major breakthrough in wet tantalum capacitor technology. Its unique cathode system provides the highest capacitance per unit volume. The design facilitates a doubling of capacitance, lower ESR and higher ripple current rating compared with conventional wet tantalum products. Moreover, the ST has the capacitance stability of a solid tantalum capacitor and there are no circuit impedance restrictions.

The ST is housed in an all tantalum, hermetically sealed case and is manufactured to withstand hazardous environments. The ST is used widely in the defense and aerospace industries and whenever there is a space problem.


FEATURES

- Very High Capacitance
- 10 to 1800 μ F
- 25 to 125VDC
- - 55°C to + 125°C
- Very Low ESR
- High Ripple Current
- All Tantalum Case
- Hermetically Sealed
- Low DCL

Application Notes

- No continuous reverse voltage permissible.
- Transient reverse voltage surges are acceptable under the following conditions:
The peak reverse voltage does not exceed 1.5V and the peak current times the duration of the reverse transient does not exceed 0.05 ampere seconds. In addition, the repetition frequency of the reverse voltage surge is less than 10Hz.
- The peak of the applied AC ripple and the applied DC voltage must not exceed the DC voltage rating of the capacitor.
- Ripple current ratings by part number at 85°C and 40kHz are included in the table. Ripple current correction factors for other temperatures and frequencies are given on the next page.

DIMENSIONS in inches (millimeters)



CASE CODE	D MAX. INSULATED	D ± 0.016 (0.41)	L + 0.031 (0.79) UNINSULATED	E ± 0.250 (6.35) MAX.
T1	0.219 (5.56)	0.188 (4.78)	0.453 (11.51)	1.500 (38.10)
T2	0.312 (7.92)	0.281 (7.14)	0.641 (16.28)	2.250 (57.15)
L2	0.312 (7.92)	0.281 (7.14)	1.008 (25.60)	2.250 (57.15)
T3	0.406 (10.31)	0.375 (9.52)	0.766 (19.46)	2.250 (57.15)
T4	0.406 (10.31)	0.375 (9.52)	1.062 (26.97)	2.250 (57.15)

NOTES:

- Material at egress is tantalum
- Insulation sleeving will lap over the ends of the capacitor case.
- Tinned nickel leads, solderable and weldable

Approx. Weight T1: 2.3 grams, T2: 5.7 grams
 T3: 9.4 grams T4: 14.8 grams

ORDERING INFORMATION

ST	220	100	T4	M	I
SUPERTAN	CAPACITANCE	85°C	CASE	CAPACITANCE	INSULATING
COMMERCIAL	μ F	RATED DC	CODE	TOLERANCE	SLEEVE
CAP. TYPE*		VOLTAGE			
				M = $\pm$ 20% K = $\pm$ 10%	I = Insulated X = Uninsulated

*See DSCC drawing 93026 for MIL version of SuperTan.

RATINGS AND CASE CODES

CAP. AT 25°C & 120Hz μF	CASE CODE	MAX. ESR Ω 120Hz	MAX. DCL μA		MAX. IMP. AT - 55°C & 120Hz Ω	MAXIMUM CAPACITANCE CHANGE %			AC RIPPLE 85°C 40kHz mA rms	PART NUMBER
			25°C	85°C & 125°C		-55°C	85°C	125°C		
25VDC at 85°C						15VDC at 125°C				
120	T1	1.3	1	5	25	- 42	+ 8	+ 12	1250	ST120-25T1MI
560	T2	0.83	2	10	12	- 65	+ 10	+ 15	2100	ST560-25T2MI
1100	L2	0.5	3	25	7	- 60	+ 15	+ 30	2500	ST1100-25L2MI
1200	T3	0.65	5	20	7	- 70	+ 12	+ 18	2600	ST1200-25T3MI
1800	T4	0.5	6	25	7	- 72	+ 12	+ 20	3100	ST1800-25T4MI
30VDC at 85°C						20VDC at 125°C				
100	T1	1.3	1	5	25	- 38	+ 8	+ 12	1200	ST100-30T1MI
470	T2	0.85	2	10	15	- 65	+ 10	+ 18	1800	ST470-30T2MI
950	L2	0.5	5	30	7	- 45	+ 15	+ 30	2200	ST950-30L2MI
1000	T3	0.7	7	25	7	- 70	+ 10	+ 18	2500	ST1000-30T3MI
1500	T4	0.6	12	35	6	- 72	+ 10	+ 20	3000	ST1500-30T4MI
50VDC at 85°C						30VDC at 125°C				
68	T1	1.5	1	5	35	- 25	+ 8	+ 15	1050	ST68-50T1MI
220	T2	0.9	2	10	17.5	- 50	+ 8	+ 15	1800	ST220-50T2MI
450	L2	0.6	3	25	7	- 45	+ 10	+ 15	2200	ST450-50L2MI
470	T3	0.75	3	25	10	- 45	+ 8	+ 15	2100	ST470-50T3MI
680	T4	0.7	5	40	8	- 58	+ 10	+ 20	2750	ST680-50T4MI
60VDC at 85°C						40VDC at 125°C				
47	T1	2.0	1	5	44	- 25	+ 8	+ 12	1050	ST47-60T1MI
150	T2	1.1	2	10	20	- 40	+ 8	+ 15	1800	ST150-60T2MI
370	L2	0.6	3	25	9	- 30	+ 10	+ 35	2200	ST370-60L2MI
390	T3	0.9	3	25	15	- 45	+ 8	+ 15	2100	ST390-60T3MI
560	T4	0.8	5	40	10	- 58	+ 8	+ 15	2750	ST560-60T4MI
75VDC at 85°C						50VDC at 125°C				
33	T1	2.5	1	5	66	- 25	+ 5	+ 9	1050	ST33-75T1MI
110	T2	1.3	2	10	24	- 35	+ 6	+ 10	1650	ST110-75T2MI
250	L2	0.8	5	30	10	- 20	+ 5	+ 15	2000	ST250-75L2MI
330	T3	1.0	3	30	12	- 45	+ 6	+ 10	2100	ST330-75T3MI
470	T4	0.9	5	50	12	- 50	+ 6	+ 10	2750	ST470-75T4MI
100VDC at 85°C						65VDC at 125°C				
15	T1	3.5	1	5	125	- 18	+ 3	+ 10	1050	ST15-100T1MI
68	T2	2.1	2	10	37	- 30	+ 4	+ 12	1650	ST68-100T2MI
120	L2	1.0	3	25	18	- 20	+ 5	+ 15	1800	ST120-100L2MI
150	T3	1.6	3	25	22	- 35	+ 6	+ 12	2100	ST150-100T3MI
220	T4	1.2	5	50	15	- 40	+ 6	+ 12	2750	ST220-100T4MI
125VDC at 85°C						85VDC at 125°C				
10	T1	5.5	1	5	175	- 15	+ 3	+ 10	1050	ST10-125T1MI
47	T2	2.3	2	10	47	- 25	+ 5	+ 12	1650	ST47-125T2MI
90	L2	1.3	5	15	24	- 15	+ 5	+ 10	1800	ST90-125L2MI
100	T3	1.8	3	25	35	- 35	+ 5	+ 12	2100	ST100-125T3MI
150	T4	1.6	5	50	20	- 35	+ 6	+ 12	2750	ST150-125T4MI

(K = ± 10%, M = ± 20%) and insulation letter (I = Insulation, X = Uninsulated)

RIPPLE CURRENT MULTIPLIERS VERSUS FREQUENCY, TEMPERATURE AND APPLIES PEAK VOLTAGE

FREQUENCY OF APPLIED RIPPLE CURRENT		120Hz				800Hz				1kHz				10kHz				40kHz				100kHz			
AMBIENT STILL AIR TEMP. IN °C		≤55	85	105	125	≤55	85	105	125	≤55	85	105	125	≤55	85	105	125	≤55	85	105	125	≤55	85	105	125
% of	100%	0.60	0.39	-	-	0.71	0.43	-	-	0.72	0.45	-	-	0.88	0.55	-	-	1.0	0.63	-	-	1.1	0.69	-	-
85°C	90%	0.60	0.46	-	-	0.71	0.55	-	-	0.72	0.55	-	-	0.88	0.67	-	-	1.0	0.77	-	-	1.1	0.85	-	-
rated	80%	0.60	0.52	0.35	-	0.71	0.62	0.42	-	0.72	0.62	0.42	-	0.88	0.76	0.52	-	1.0	0.87	0.59	-	1.1	0.96	0.65	-
peak	70%	0.60	0.58	0.44	-	0.71	0.69	0.52	-	0.72	0.70	0.52	-	0.88	0.85	0.64	-	1.0	0.97	0.73	-	1.1	1.07	0.80	-
voltage	66 2/3%	0.60	0.60	0.46	0.27	0.71	0.71	0.55	0.32	0.72	0.72	0.55	0.32	0.88	0.88	0.68	0.40	1.0	1.0	0.77	0.45	1.1	1.1	0.85	0.50



SuperTan[®] Wet Tantalum Capacitors
with Hermetic Seal

ST
Vishay

93026 RATINGS AND CASE CODES

DSCC DRAWING 93026	CAP. at 25°C & 120Hz μF	CASE CODE	Max. ESR Ω 120Hz	Max. DCL μA		Max. IMP. at - 55°C & 120Hz Ω	Max. CAPACITANCE CHANGE %			AC RIPPLE 85°C 40kHz mA rms
				25°C	85°C & 125°C		-55°C	85°C	125°C	
25VDC at 85°C						15VDC at 125°C				
93026-29	120	T1	1.3	1	5	25	- 42	+ 8	+ 12	1250
93026-30	560	T2	0.83	2	10	12	- 65	+ 10	+ 15	2100
93026-57	1100	L2	0.5	3	25	7	- 60	+ 15	+ 30	2500
93026-31	1200	T3	0.65	5	20	7	- 70	+ 12	+ 18	2600
93026-32	1800	T4	0.5	6	25	7	- 75	+ 12	+ 20	3100
30VDC at 85°C						20VDC at 125°C				
93026-33	100	T1	1.3	1	5	25	- 38	+ 8	+ 12	1200
93026-34	470	T2	0.85	2	10	15	- 65	+ 10	+ 18	1800
93026-58	950	L2	0.5	5	30	7	- 45	+ 15	+ 30	2200
93026-35	1000	T3	0.7	7	25	7	- 70	+ 10	+ 18	2500
93026-36	1500	T4	0.6	12	35	6	- 72	+ 10	+ 20	3000
50VDC at 85°C						30VDC at 125°C				
93026-37	68	T1	1.5	1	5	35	- 25	+ 8	+ 15	1050
93026-38	220	T2	0.9	2	10	17.5	- 50	+ 8	+ 15	1800
93026-59	450	L2	0.6	3	25	7	- 25	+ 10	+ 30	2200
93026-39	470	T3	0.75	3	25	10	- 50	+ 8	+ 15	2100
93026-40	680	T4	0.7	5	40	8	- 58	+ 10	+ 20	2750
60VDC at 85°C						40VDC at 125°C				
93026-41	47	T1	2.0	1	5	44	- 25	+ 8	+ 12	1050
93026-42	150	T2	1.1	2	10	20	- 40	+ 8	+ 15	1650
93026-60	370	L2	0.6	3	25	9	- 30	+ 10	+ 25	2000
93026-43	390	T3	0.9	3	25	15	- 60	+ 8	+ 15	2100
93026-44	560	T4	0.8	5	40	10	- 58	+ 8	+ 15	2750
75VDC at 85°C						50VDC at 125°C				
93026-45	33	T1	2.5	1	5	66	- 25	+ 5	+ 9	1050
93026-46	110	T2	1.3	2	10	24	- 35	+ 6	+ 10	1650
93026-61	250	L2	0.8	5	30	10	- 20	+ 5	+ 15	2000
93026-47	330	T3	1.0	3	30	12	- 45	+ 6	+ 10	2100
93026-48	470	T4	0.9	5	50	12	- 55	+ 6	+ 10	2750
100VDC at 85°C						65VDC at 125°C				
93026-49	15	T1	3.5	1	5	125	- 18	+ 3	+ 10	1050
93026-50	68	T2	2.1	2	10	37	- 30	+ 4	+ 12	1650
93026-62	120	L2	1.0	3	25	18	- 20	+ 5	+ 15	1800
93026-51	150	T3	1.6	3	25	22	- 35	+ 6	+ 12	2100
93026-52	220	T4	1.2	5	50	15	- 40	+ 6	+ 12	2750
125VDC at 85°C						85VDC at 125°C				
93026-53	10	T1	5.5	1	5	175	- 15	+ 3	+ 10	1050
93026-54	47	T2	2.3	2	10	47	- 25	+ 5	+ 12	1650
93026-63	90	L2	1.3	5	15	24	- 15	+ 5	+ 10	1800
93026-55	100	T3	1.8	3	25	35	- 35	+ 5	+ 12	2100
93026-56	150	T4	1.6	5	50	20	- 35	+ 6	+ 12	2750

ORDERING INFORMATION - DSCC PART NUMBER

93026	-29	K	S
DSCC DRAWING NUMBER	DASH NUMBER	CAPACITANCE TOLERANCE	
		K = ± 10% M = ± 20%	S = Sleeved U = Unsleeved

DEFENSE SUPPLY CENTER, COLUMBUS
COLUMBUS, OHIO

DRAWING NO.
93026