















REVISONS				
LOC	DIST	P	LTR	DESCRIPTION
J	-			SEE SHEET 1



1. CAMSHAFT, BY TURNING 100° IN THE DIRECTION INDICATED, ENGAGES WITH RECEPTACLE
2. PLATING: MATING AREA: 1.27μmMIN GOLD OVER 1.27μmMIN NICKEL
POROSITY SEALING ALL OVER
SOLDER LEG AREA: 0.127μmMIN GOLD OVER 1.27μmMIN NICKEL
OTHERS: 1.27μmMIN NICKEL
3. TOLERANCE
10 OR LESS : ±0.3
30 OR LESS THAT IS LARGER THAN 10 : ±0.5
100 OR LESS THAT IS LARGER THAN 30 : ±0.7

1. カムシャフトは図示の方向に100°回転させる事によりリセプタクル側と嵌合状態となる。
2. めっき: 接触部: ニッケル下地1.27μmMINの上に金1.27μmMIN 全面に封孔処理を施す
半田付部: ニッケル下地1.27μmMINの上に金0.127μmMIN
その他: ニッケル下地1.27μmMIN

3. 公差
10以下 : ±0.3
10を越え30以下 : ±0.5
30を越え100以下 : ±0.7

RoHS COMPLIANT					
16	アダプタ スタビライザ ADAPTER STABILIZER	1	合成樹脂 PLASTIC	無し NONE	UL94V-0
14	タッピングスクリュー TAPPING SCREW L=8	2	鋼 STEEL	3価クロメート TRIVALENT CHROMATE	
13	サポートハウジング SUPPORT HSG	20	合成樹脂 PLASTIC	無し NONE	UL94V-0
12	コンタクト 0.64x0.4 CONTACT	(260)	ベリリウム銅 BERYLLIUM COPPER	ニッケル下地金メッキ Au OVER Ni PL	
8	リターンスプリング RETURN SPRING	2	ステンレス鋼 STAINLESS STEEL	無し NONE	
7	リテーナー RETAINER	1	ステンレス鋼 STAINLESS STEEL	無し NONE	
6	リテーニングリング RETAINING RING	2	ステンレス鋼 STAINLESS STEEL	無し NONE	
5	カムシャフトピン CAM SHAFT PIN	1	ステンレス鋼 STAINLESS STEEL	無し NONE	
4	カムシャフト CAM SHAFT	1	ステンレス鋼 STAINLESS STEEL	無し NONE	
3	ベアリングカム BEARING CAM	2	リン青銅 PHOSPHOR BRONZE	ニッケルメッキ Ni PLATING	
2	アクチュエータ ACTUATOR	2	合成樹脂 PLASTIC	無し NONE	UL94V-0
1	ハウジングプラグアッシー HOUSING PLUG ASSY	1	ナイロン樹脂 NYLON RESIN	無し NONE	UL94V-0
符号 ITEM	名前 DESCRIPTION	数量 QTY	材料 MATERIAL	仕上げ FINISH	備考 REMARK

DIMENSIONS mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWN K. SAKAI CHK E. TAKEMASA APVD M. KUMURA PRODUCT SPEC 108-5483 APPLICATION SPEC		NAME M-ZIF CONN PLUG 260P SHORT SOLDER TYPE		SIZE A1		CAGE CODE -		DRAWING NO. ©=5316717		RESTRICTED TO	
MATERIAL SEE TABLE		FINISH SEE TABLE		WEIGHT 118.2g		CUSTOMER DRAWING		SCALE 2:1		SHEET 3 OF 3		REV B1			