




RECOMMENDED P.C.B. LAYOUT



NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERMINAL NO.S FOR REF ONLY.
4. RATING: 250V AC 5A/80A, {TV-5@125V}
125V AC 10A. UL, CUL, {VDE} APPROVED
IN RUSH {080A @250V}
5. CONTACT RESISTANCE: 100mILLI Ohms MAX. (AT DC 5V@1A)
6. DIELECTRIC STRENGTH: AC 1500V
7. OPERATING FORCE: 300±100gf
8. TRAVEL: FULL STROKE: 3.5+0.5/-0mm
LOCK STROKE: 2.5+0.5/-0mm

CIRCUIT: SPST



E-SWITCH®

C		15741	EDIT PC LAYOUT	2/7/06	PH	TITLE			
B		12265	REVISED AND REDRAWN	6/26/02	CJB	P197EE PC (LATCHING)			
REV.		ECN NO.	DESCRIPTION	DATE	CHKD	SCALE	DATE	DR	DWG
						1.5:1	6/26/02	CJB	P030054
									REV
									C

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED