



SPECIFICATIONS:

1. MATERIAL:
 - (1). SCREW: STEEL.
 - (2). BODY: NYLON 66 (PA 66).
 - (3). TERMINAL: PHOSPHOR BRONZE
 - (4). CAGE (*): BRASS
 - (5). COVER: NYLON 66 (PA 66).
2. PRODUCT SPECIFICATION: PS-39500-001.
3. WIRE RANGE: 30 - 16AWG.
4. TORQUE: 2 in-lbs.
5. WIRE STRIP LENGTH: 6.50/.256.
6. NUMBER OF CIRCUIT POSITIONS AVAILABLE = 2 THROUGH 20.
7. ASSEMBLY IS ROHS COMPLIANT BY EXEMPTION.
COMPONENTS MARKED WITH AN ASTERISK (*) ARE ROHS COMPLIANT BY EXEMPTION, ALL OTHERS ARE ROHS COMPLIANT.

TOLERANCES			
MM	TOL	INCH	TOL
0-6	±0.25	0-.24	±.010
>6-30	±0.40	.24-1.18	±.016
>30-120	±0.50	1.18-4.76	±.020
>120	±0.80	>4.76	±.031

REVISED DOC TOL EC NO: IPG2017-0881 DRAWN: VASUTHKARP 2017/03/22 CHKD: APPR: BRUPERT 2017/04/18 C2	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)	DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION			
			MM/IN			INCH				
			mm	INCH	DRAWN BY	DATE	TITLE 3.50MM, EURO TERM BLOCK RIGHT ANGLE, PLUG			
			4 PLACES	± --- ± ---	LROTHAUS	12/06/05				
			3 PLACES	± --- ± ---	CHECKED BY	DATE	MOLEX INCORPORATED			
2 PLACES	± --- ± ---	C. YORK	01/06/06							
1 PLACE	± --- ± ---	APPROVED BY	DATE	DOCUMENT NO. SD-39500-001						
ANGULAR ± ---°		J. PAWLICKI	01/10/06					SHEET NO. 1 OF 2		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE SHEET 2		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						

	10	9	8	7	6	5	4	3	2	1							
F	Circuit size	Material Numbers											Dimensional Information				
		Black						Green									
		100% Tin			30 u" Gold			100% Tin			30 u" Gold		Dim. A		Dim. B		
		Printing Options			Printing Options			Printing Options			Printing Options						
None	10A	11A	None	10A	11A	None	10A	11A	None	10A	11A	mm	inch	mm	inch		
	2	395000002	395000102	395000202	395000502	395000602	395000702	395005002	395005102	395005202	395005502	395005602	395005702	7.80	0.307	3.50	0.138
	3	395000003	395000103	395000203	395000503	395000603	395000703	395005003	395005103	395005203	395005503	395005603	395005703	11.30	0.445	7.00	0.276
	4	395000004	395000104	395000204	395000504	395000604	395000704	395005004	395005104	395005204	395005504	395005604	395005704	14.80	0.583	10.50	0.413
	5	395000005	395000105	395000205	395000505	395000605	395000705	395005005	395005105	395005205	395005505	395005605	395005705	18.30	0.720	14.00	0.551
	6	395000006	395000106	395000206	395000506	395000606	395000706	395005006	395005106	395005206	395005506	395005606	395005706	21.80	0.858	17.50	0.688
	7	395000007	395000107	395000207	395000507	395000607	395000707	395005007	395005107	395005207	395005507	395005607	395005707	25.30	0.996	21.00	0.827
E	8	395000008	395000108	395000208	395000508	395000608	395000708	395005008	395005108	395005208	395005508	395005608	395005708	28.80	1.134	24.50	0.965
	9	395000009	395000109	395000209	395000509	395000609	395000709	395005009	395005109	395005209	395005509	395005609	395005709	32.30	1.272	28.00	1.102
	10	395000010	395000110	395000210	395000510	395000610	395000710	395005010	395005110	395005210	395005510	395005610	395005710	35.80	1.409	31.50	1.240
	11	395000011	395000111	395000211	395000511	395000611	395000711	395005011	395005111	395005211	395005511	395005611	395005711	39.30	1.547	35.00	1.378
	12	395000012	395000112	395000212	395000512	395000612	395000712	395005012	395005112	395005212	395005512	395005612	395005712	42.80	1.685	36.50	1.516
	13	395000013	395000113	395000213	395000513	395000613	395000713	395005013	395005113	395005213	395005513	395005613	395005713	46.30	1.823	42.00	1.654
	14	395000014	395000114	395000214	395000514	395000614	395000714	395005014	395005114	395005214	395005514	395005614	395005714	49.80	1.961	45.50	1.791
	15	395000015	395000115	395000215	395000515	395000615	395000715	395005015	395005115	395005215	395005515	395005615	395005715	53.30	2.098	49.00	1.929
D	16	395000016	395000116	395000216	395000516	395000616	395000716	395005016	395005116	395005216	395005516	395005616	395005716	56.80	2.236	52.50	2.067
	17	395000017	395000117	395000217	395000517	395000617	395000717	395005017	395005117	395005217	395005517	395005617	395005717	60.30	2.374	56.00	2.205
	18	395000018	395000118	395000218	395000518	395000618	395000718	395005018	395005118	395005218	395005518	395005618	395005718	63.80	2.512	59.50	2.343
	19	395000019	395000119	395000219	395000519	395000619	395000719	395005019	395005119	395005219	395005519	395005619	395005719	67.30	2.650	63.00	2.480
	20	395000020	395000120	395000220	395000520	395000620	395000720	395005020	395005120	395005220	395005520	395005620	395005720	70.80	2.787	66.50	2.618

1

2

3

18

19

20

2.0
.08 TYP.
CHARACTER
HEIGHT

10A IMPRINTING

20

19

18

3

2

1

2.0
.08 TYP.
CHARACTER
HEIGHT

11A IMPRINTING

REVISED DOC TOL EC NO: IPG2017-0881 DRAWN:VASUTHKARP 2017/03/22 CHKD: C2 APPR:BRUPERT 2017/04/18 REV	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE	DESIGN UNITS INCH	THIRD ANGLE PROJECTION		
		4 PLACES	± ---	± ---	DRAWN BY	DATE	TITLE			
		3 PLACES	± ---	± ---	LROTHAUS	12/6/05	3.50MM, EURO TERM. BLOCK			
		2 PLACES	± ---	± ---	CHECKED BY	DATE	RIGHT ANGLE, PLUG			
1 PLACE	± ---	± ---	C. YORK	01/06/06						
ANGULAR ±---°			APPROVED BY	DATE	MOLEX MOLEX INCORPORATED					
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			J. PAWLICKI	01/10/06						
SIZE B			MATERIAL NO.		DOCUMENT NO.		SHEET NO.			
			SEE CHART		SD-39500-001		2 OF 2			
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION										

1b_frame_B_P_ME_T Rev. D 2004/04/02	9	8	7	6	5	4	3	2	1
--	---	---	---	---	---	---	---	---	---

REVISED DOC TOL

EC NO: ICG2017-0881

DRW:VIBASUTHKARP 2017/03/22

CHKD: C2

APPR:BRUPERT 2017/04/18

QUALITY SYMBOLS

▽=0

▽=0

GENERAL TOLERANCES (UNLESS SPECIFIED)

mm

INCH

4 PLACES ± --- ± ---

3 PLACES ± --- ± ---

2 PLACES ± --- ± ---

1 PLACE ± --- ± ---

ANGULAR ± ---°

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

DIMENSION STYLE

MM/IN

DRAWN BY LROTHAUS

DATE 12/6/05

CHECKED BY C. YORK

DATE 01/06/06

APPROVED BY J. PAWLICKI

DATE 01/10/06

MATERIAL NO.

SEE CHART

SIZE B

SCALE

DESIGN UNITS

INCH

THIRD ANGLE PROJECTION

3.50MM, EURO TERM. BLOCK RIGHT ANGLE, PLUG

MOLEX

MOLEX INCORPORATED

DOCUMENT NO. SD-39500-001

SHEET NO. 2 OF 2

TOLERANCES

MM

TOL

INCH

TOL

0-6 ±0.25 0-.24 ±.010

>6-30 ±0.40 .24-1.18 ±.016

>30-120 ±0.50 1.18-4.76 ±.020

>120 ±0.80 >4.76 ±.031