



4		3		2		1																																																												
NOTES 1. All dimensions are in $\frac{\text{inches}}{\text{millimeters}}$ 2. Dimensions appearing in table are as follows: a - As Supplied b - After Unrestricted Recovery 3. Coating is optional. As supplied dimensions appearing in table are for uncoated parts. When coating is added, entry diameters will be reduced by .06 max. 4. Recovered parts may have angularity of 30° - 45°.						DIMENSIONING AND TOLERANCING PER ASME Y14.5M (ISO STANDARDS)																																																												
						REVISIONS																																																												
LTR		DESCRIPTION		DATE																																																														
U2		RELEASE PER ECO-12-002474		02/07/2012																																																														
				<table><tr><th colspan="5">TABLE OF DIMENSIONS</th></tr><tr><th rowspan="2">PART NUMBER</th><th colspan="2">H</th><th>P</th><th>W</th></tr><tr><th>Min a</th><th>Max b</th><th>Min b</th><th>±20% b</th></tr><tr><td>101A011</td><td>.20 [5,1]</td><td>.08 [2,0]</td><td>.90 [22,9]</td><td>.04 [1,02]</td></tr><tr><td>101A021</td><td>.29 [7,4]</td><td>.13 [3,3]</td><td>1.00 [25,4]</td><td>.05 [1,27]</td></tr><tr><td>101A031</td><td>.40 [10,2]</td><td>.18 [4,6]</td><td>1.20 [30,5]</td><td>.06 [1,52]</td></tr><tr><td>101A041</td><td>.60 [15,2]</td><td>.25 [6,4]</td><td>1.60 [40,6]</td><td>.07 [1,78]</td></tr><tr><td>101A052</td><td>.81 [20,6]</td><td>.37 [9,4]</td><td>2.40 [61,0]</td><td>.08 [2,03]</td></tr><tr><td>101A062</td><td>1.00 [25,4]</td><td>.45 [11,4]</td><td>2.70 [68,6]</td><td>.09 [2,29]</td></tr><tr><td>101A073</td><td>1.55 [39,4]</td><td>.71 [18,0]</td><td>3.60 [91,4]</td><td>.10 [2,54]</td></tr><tr><td>101A083</td><td>2.00 [50,8]</td><td>.90 [22,9]</td><td>4.00 [101,6]</td><td>.11 [2,79]</td></tr><tr><td>101A094</td><td>3.30 [83,8]</td><td>1.50 [38,1]</td><td>4.50 [114,3]</td><td>.12 [3,05]</td></tr></table>				TABLE OF DIMENSIONS					PART NUMBER	H		P	W	Min a	Max b	Min b	±20% b	101A011	.20 [5,1]	.08 [2,0]	.90 [22,9]	.04 [1,02]	101A021	.29 [7,4]	.13 [3,3]	1.00 [25,4]	.05 [1,27]	101A031	.40 [10,2]	.18 [4,6]	1.20 [30,5]	.06 [1,52]	101A041	.60 [15,2]	.25 [6,4]	1.60 [40,6]	.07 [1,78]	101A052	.81 [20,6]	.37 [9,4]	2.40 [61,0]	.08 [2,03]	101A062	1.00 [25,4]	.45 [11,4]	2.70 [68,6]	.09 [2,29]	101A073	1.55 [39,4]	.71 [18,0]	3.60 [91,4]	.10 [2,54]	101A083	2.00 [50,8]	.90 [22,9]	4.00 [101,6]	.11 [2,79]	101A094	3.30 [83,8]	1.50 [38,1]	4.50 [114,3]	.12 [3,05]
								TABLE OF DIMENSIONS																																																										
PART NUMBER	H		P	W																																																														
	Min a	Max b	Min b	±20% b																																																														
101A011	.20 [5,1]	.08 [2,0]	.90 [22,9]	.04 [1,02]																																																														
101A021	.29 [7,4]	.13 [3,3]	1.00 [25,4]	.05 [1,27]																																																														
101A031	.40 [10,2]	.18 [4,6]	1.20 [30,5]	.06 [1,52]																																																														
101A041	.60 [15,2]	.25 [6,4]	1.60 [40,6]	.07 [1,78]																																																														
101A052	.81 [20,6]	.37 [9,4]	2.40 [61,0]	.08 [2,03]																																																														
101A062	1.00 [25,4]	.45 [11,4]	2.70 [68,6]	.09 [2,29]																																																														
101A073	1.55 [39,4]	.71 [18,0]	3.60 [91,4]	.10 [2,54]																																																														
101A083	2.00 [50,8]	.90 [22,9]	4.00 [101,6]	.11 [2,79]																																																														
101A094	3.30 [83,8]	1.50 [38,1]	4.50 [114,3]	.12 [3,05]																																																														
ORDERING INFORMATION																																																																		
Base part number 101A021 -X -XX /XXX -X																																																																		
Material dash number (See Compatability Chart)																																																																		
Modification number																																																																		
Adhesive slash number (If necessary, see Compatability Chart)																																																																		
Color designator																																																																		
* Color code based on SAE-AMS-DTL-23053																																																																		
* not all colors available for this molded part.																																																																		
COMPATIBILITY CHART																																																																		
MATERIAL DASH NO.	MATERIAL DESCRIPTION	RT SPEC	ADHESIVE SLASH NO.	ADHESIVE S NUMBER																																																														
-3	Polyolefin, Semi-rigid	RT-301	/42; /86	S-1017; S-1048																																																														
-4	Polyolefin, Flexible	RT-1304	/42; /86	S-1017; S-1048																																																														
-12	*VITON, Flexible	RT-1312	N/A	N/A																																																														
-25	Elastomer, Fluid Resistant	RT-1325	/86; /225	S-1048; S-1206																																																														
-100	Polyolefin, Semi-flexible	RT-1323																																																																
THIS DRAWING AND THE INFORMATION SET FORTH HEREON ARE THE PROPERTY OF TYCO ELECTRONICS CORPORATION, AND ARE TO BE HELD IN TRUST AND CONFIDENCE. PUBLICATION, DUPLICATION, DISCLOSURE OR USE FOR ANY PURPOSE NOT EXPRESSLY AUTHORIZED IN WRITING BY TYCO ELECTRONICS CORPORATION IS PROHIBITED.																																																																		
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE METRIC AND INCHES ARE IN BRACKETS. DECIMAL TOLERANCES XXX ± 0.13 (.005) XX ± 0.25 (.01) X ± 0.50 (.10) ANGLE TOLERANCE .X ± 1 DEG.																																																																		
DRAWN M. Mazariegos 01/31/12 APPROVED D. Hurrell 02/01/12 RPN CAD FILE: 101A011thru094_CD THIRD ANGLE PROJECTION																																																																		
TE Connectivity Cap, Round End SIZE B CODE IDENT. NO. 06090 DWG. NO. 101A011thru094 DO NOT SCALE THIS DRAWING SHEET 1 OF 1																																																																		