

**Part Number: 74526-4050**

0.50mm Pitch LaneLink™ 10Gbase-CX4 Cable Assembly, 28 AWG, Lanyard Latch, 5.0m Length



Series image - Reference only

Status:	OBsolete
Replacement:	Contact Molex
Series:	74526
Category:	Cable Assemblies
Overview:	LaneLink™

Mates With Part(s):
[91525](#) 4X/12X Latch LaneLink™ Receptacle
[91804](#) LaneLink™ Connector

Use With:
[74735](#) X2 Transceiver
[74739](#) XPAK Transceiver

Product Environmental Compliance[EU RoHS](#): ELV and RoHS Compliant[China RoHS](#): [REACH SVHC](#): Not Reviewed[Low-Halogen Status](#): Not Reviewed**Part Detail****General**

Status	Obsolete
Category	Cable Assemblies
Series	74526
Connector to Connector	4X Plug-to-4X Plug
Overview	LaneLink™
Product Name	10Gbase-CX4, 4X, LaneLink™

Physical

Cable Length	5.0m
Circuits (Loaded)	16
Gender	Plug/Plug
Lock to Mating Part	Yes
Packaging Type	Bag
Single Ended	No
Waterproof / Dustproof	No
Wire Insulation Diameter	N/A
Wire Size AWG	28
Wire/Cable Type	Round

Electrical**(Please review the Product Specification for specific details.)**

Current - Maximum per Contact	0.5A
Impedance	100Ω
Shield Type	Full Shield
Shielded	Yes
Voltage - Maximum	30V AC

Material Info

UPC	800756825052
-----	--------------

Reference - Drawing Numbers

Sales Drawing	SD-74526-400
---------------	--------------

Application Tooling

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling

[Check our list of old tooling that used to be available for this part](#)