



1750F



DIMENSIONS:

A	3.250" ± 0.063
B	1.687" ± 0.125
C	1.995" ± 0.063
D	2.813" ± 0.063
G	0.187" ± 0.015



ELECTRICAL DATA:

Turns ratio:	29.19 : 1
Inductance	@240V, 70Hz => 27.28H (Open circuit)
DCR	@ 20C, BLU - RED = 97.36 Ω $\pm 20\%$
	@ 20C, RED - BRN = 97.36 Ω $\pm 20\%$
	@ 20C, BLU - BRN = 194.7 Ω $\pm 20\%$
	@ 20C, BLK - GRN = 0.409 Ω $\pm 20\%$
FREQ. RESP	@ 15W(322.75V), 70Hz-15kHz, BLU-BRN ± 1 db (Ref. 1kHz)
Pri. Impedance	6950 Ω CT(322.75V)
Sec. Impedance	8 Ω (10.95V @ 1.370A)
Power	15 WATTS



**HAMMOND
ELECTRONICS**

52 RANKIN PLACE,
WATERLOO, ONTARIO, N2L 3Z5.

PHONE (519) 886-6181
FAX # (519) 886-9540

TITLE

OUTPUT TRANSFORMER

			DR BY IOAN POP
0	05/11/09	PRELIMINARY.	I.P. DATE 05/11/09
NO	DATE	REVISION	DIM IN(X)MM()

1750F