

SMD MICROPROCESSOR CRYSTAL

ABMC2



11.0 x 5.0 x 2.0 mm



RoHS
Compliant

FEATURES:

- 2.0 mm height
- Hermetically sealed package offers high reliability.
- AT cut offers tighter stability
- Resistance welded
- Extended temperature available
- Low frequency in SMD package
- IR Reflow capable

APPLICATIONS:

- PCMCIA applications
- Microprocessors
- Communication equipment, Networking, Thin equipment

STANDARD SPECIFICATIONS:

ABRACON P/N:	ABMC2 Series
Frequency:	3.579545 MHz to 70 MHz
Operation mode:	AT-strip or BT-strip 3.5 MHz - 32.00 MHz (Fundamental AT-cut: Standard) 32.00 MHz - 70.00 MHz (3rd OT AT-cut: Standard) 32.00 MHz - 41.00 MHz (Fundamental AT-cut: See options) 22.00 MHz - 46.00 MHz (Fundamental BT-cut: See options)
Operating temperature:	- 10°C to + 60°C (see options)
Storage temperature:	- 40°C to + 85° C
Frequency tolerance:	± 50 ppm max. (see options)
Frequency stability over the operating temperature (Ref to +25° C):	± 100 ppm max. (see options) ± 100 ppm max. over - 40°C to + 85° C only for BT-cut
Equivalent series resistance (max.):	See Table 1
Shunt capacitance C0:	7.0pF max.
Load capacitance CL:	18.0pF (see option)
Drive level:	100 µW max.
Aging (per year) @ 25° C:	± 5 ppm max.
Insulation resistance:	500 M Ω min. at 100 Vdc ± 15 Vdc

Table 1 Standard ESR


Frequency (MHz)	ESR(Ω) max.
3.500 - 3.999 (AT cut fund.)	180
4.000 - 4.999 (AT cut fund.)	150
5.000 - 5.999 (AT cut fund.)	120
6.000 - 6.999 (AT cut fund.)	100
7.000 - 8.999 (AT cut fund.)	80
9.000 - 12.999 (AT cut fund.)	60
13.00 - 19.999 (AT cut fund.)	50
20.00 - 41.00 (AT cut fund.)	40
22.00 - 46.00 (BT cut)	60
32.00 - 70.00 (3rd O/T)	80






OPTIONS AND PART IDENTIFICATION:

(Left blank if standard)



OUTLINE DRAWING:




ABMC2



RoHS
Compliant


11.0 x 5.0 x 2.0 mm

TAPE & REEL: T = Tape and reel 1,000pcs/reel



Dimensions: mm

➤ **REFLOW PROFILE:**



ATTENTION: Abracon Corporation's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependant Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon Corporation is required. Please contact Abracon Corporation for more information.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ABRACON:

[ABMC2-10.000MHZ-B4Z-T](#) [ABMC2-11.0592MHZ-B4Z-T](#) [ABMC2-11.2896MHZ-B4Z-T](#) [ABMC2-12.000MHZ-B4Z-T](#)
[ABMC2-12.288MHZ-B4Z-T](#) [ABMC2-14.31818MHZ-B4Z-T](#) [ABMC2-14.7456MHZ-B4Z-T](#) [ABMC2-15.000MHZ-B4Z-T](#)
[ABMC2-15.360MHZ-B4Z-T](#) [ABMC2-16.000MHZ-B4Z-T](#) [ABMC2-16.666MHZ-B4Z-T](#) [ABMC2-18.432MHZ-B4Z-T](#)
[ABMC2-19.440MHZ-B4Z-T](#) [ABMC2-20.000MHZ-B4Z-T](#) [ABMC2-20.480MHZ-B4Z-T](#) [ABMC2-22.1184MHZ-B4Z-T](#)
[ABMC2-24.000MHZ-B4Z-T](#) [ABMC2-24.576MHZ-B4Z-T](#) [ABMC2-25.000MHZ-B4Z-T](#) [ABMC2-3.579545MHZ-B4Z-T](#)
[ABMC2-3.6864MHZ-B4Z-T](#) [ABMC2-4.000MHZ-B4Z-T](#) [ABMC2-4.096MHZ-B4Z-T](#) [ABMC2-4.9152MHZ-B4Z-T](#) [ABMC2-](#)
[5.000MHZ-B4Z-T](#) [ABMC2-6.000MHZ-B4Z-T](#) [ABMC2-6.144MHZ-B4Z-T](#) [ABMC2-7.3728MHZ-B4Z-T](#) [ABMC2-](#)
[7.680MHZ-B4Z-T](#) [ABMC2-8.000MHZ-B4Z-T](#) [ABMC2-9.8304MHZ-B4Z-T](#)