

Line Conditioner - Automatic voltage regulation with surge protection

MODEL NUMBER: **LC2400**



Description

2400 watt Automatic Voltage Regulation (AVR) system. Protects sensitive electronics, computer accessories and home theater equipment from power-related damage and performance problems. Extends the useful life of connected equipment by providing optimum voltage conditions for enhanced efficiency and cooler internal operating temperatures. Reliable transformer-based voltage correction circuits maintain 120V nominal output during voltage fluctuations between 89 and 140V. Three levels of voltage stabilization offer targeted response for overvoltages, undervoltages and severe brownouts. Prevents equipment damage and power related performance problems for computer accessories, printers, home theater equipment, a/v components and other sensitive electronic devices. Network-grade AC surge and EMI/RFI noise suppression. Supports loads up to 2400 watts, 20A. Includes 6 AC outlets, 6 ft AC line cord and 7 diagnostic LEDs which display incoming voltage level, surge suppression status and line fault status. \$25,000 connected equipment insurance (USA and Canada Only).

Features

- Maintains usable 120V nominal output during brownouts as low as 89V and overvoltages as high as 140V
- 2,400 watts output power rating supports heavy 120V loads up to 20 amps
- Network grade surge suppression
- Complete EMI/RFI noise filtering
- 7 diagnostic LEDs indicate input voltage levels, surge suppression status and line fault conditions
- 6 protected outlets (four NEMA5-15R and two NEMA5-20R)
- 6-ft. AC power cord with standard NEMA5-15P input plug
- \$25,000 Ultimate Lifetime connected equipment insurance (USA and Canada Only)

Specifications

OUTPUT	
Output watts	2400

Highlights

- Automatically adjusts low or high voltage
- 2400 watts continuous
- 4 NEMA 5-15R outlets; 2 NEMA 5-20R outlets
- \$25,000 Ultimate Lifetime Insurance (USA, Puerto Rico & Canada only)

Applications

- Maintains regulated output voltage during severe brownouts and overvoltages for computer accessories, printers, home theater equipment, a/v components, point-of-sale equipment, and other applications requiring clean, regulated AC power.

Package Includes

- LC2400 Line Conditioner
- Instruction manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Output nominal voltage	120V / 60Hz
Outlet quantity / type	6 (4 NEMA5-15R, 2 NEMA5-20R)
INPUT	
Input cord length (ft.)	6
Input cord length (m)	1.83
UPC ASSIGNMENT	
Unit Carton UPC#	037332040060
LEDS ALARMS & SWITCHES	
Front panel LEDs	7 LEDs show incoming voltage status, protection present and line fault conditions
SURGE / NOISE SUPPRESSION	
UPS AC suppression joule rating	1440 joules
EMI / RFI AC noise suppression	80 dB
PHYSICAL	
Shipping weight (lbs)	13.00
Shipping weight (kg)	5.90
Unit Dimensions (HWD/in)	6.75 x 5.75 x 6.75
Unit Dimensions (HWD/cm)	17.15 x 14.61 x 17.15
Material of construction	Plastic
Form factors supported	Small Tower
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$25,000 Ultimate Lifetime Insurance

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[LC2400](#)