


CUSTOMER INFORMATION SHEET

MAX. PIN LENGTH = 7.0

$L = (2.54 \times \text{No. OF PITCHES}) + 2.48 \text{ MAX}$
E.G. 12 WAY = 30.42 MAX
15 WAY = 38.04 MAX



MOULDING:

MATERIAL = GLASS-FILLED
POLYESTER UL94V-0

SOCKETS:

MATERIAL = PHOSPHOR BRONZE

FINISH =

06 - 90/10 TIN/LEAD

22 - GOLD OVER NICKEL ON CONTACT FACE,
90/10 TIN/LEAD ON P.C. TAILS27 - 0.8µ GOLD OVER NICKEL ON CONTACT FACE,
90/10 TIN/LEAD ON P.C. TAILS

ORDER CODE:M20-989XXXX

No. OF WAYS

02 TO 36

FINISH:

06 = TIN/LEAD

22 = SELECTIVE GOLD/TIN-LEAD

27 = 0.8µ SELECTIVE GOLD/TIN-LEAD

13	17.11.95	3104
12	29.09.95	3049
3	13.07.93	2334
2	17.03.93	2223
1	24.05.91	----

ISS.	DATE	C/N
APPROVED:		
CHECKED:		
DRAWN: V. BOURNE		
CUSTOMER REF:		
ASSEMBLY DRG:		

HARWIN

HARWIN INC
U.S.A.
TEL: (812) 285 0055
FAX: (812) 285 0056

HARWIN PLC
U.K.
TEL: (01705) 370451
FAX: (01705) 324010

HARWIN PTE
SINGAPORE
TEL: 7794909
FAX: 7793868

TOLERANCES

X. = ±1mm

X.X = ±0.25mm

X.XX = ±0.10mm

X.XXX = ±0.01mm

ANGLES = ±1°

UNLESS STATED

MATERIAL:

SEE ABOVE

FINISH:

SEE ABOVE

S/AREA:

mm²

TITLE:

P.C. SOCKET ASSEMBLY
(SINGLE ROW - HORIZONTAL)

DRAWING NUMBER:

M20-989XXXX

SHT
2
OF
2