




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
FT	0		B1	HOUISNG MATERIAL DETAIL ADDED	05DEC 2014	PS	JK



SCALE 2:1
-4 AS SHOWN



1 SEE FIG			
	46.50	9	2-1986711-6
	126.50	25	2-1986711-5
	121.50	24	2-1986711-4
	116.50	23	2-1986711-3
	111.50	22	2-1986711-2
	106.50	21	2-1986711-1
	101.50	20	2-1986711-0
	96.50	19	1-1986711-9
	91.50	18	1-1986711-8
	86.50	17	1-1986711-7
	81.50	16	1-1986711-6
	76.50	15	1-1986711-5
	71.50	14	1-1986711-4
	66.50	13	1-1986711-3
	61.50	12	1-1986711-2
	56.50	11	1-1986711-1
	51.50	10	1-1986711-0
	46.50	9	1986711-9
	41.50	8	1986711-8
	36.50	7	1986711-7
	31.50	6	1986711-6
	26.50	5	1986711-5
	21.50	4	1986711-4
	16.50	3	1986711-3
	11.50	2	1986711-2
	"L"	POLE	PART NO

1 PRELIMINARY PART

MATERIALS:
HOUSING - PA66-UL94 V0, COLOR - GREEN
CLAMPING SPRING - STEEL
PIN - COPPER ALLOY - TIN PLATED

MECHANICAL
PCB THICKNESS - 2.40 MAX
PCB HOLE DIAMETER - 1.20 MIN
STRIP LENGTH - 10-11 MM
OPERATING TEMPERATURE - -40 °C TO +110 °C


ELECTRICAL
WIRE RANGE- 30 TO 12 AWG
VOLTAGE RATING- 300 VOLTS
CURRENT RATING-16 AMP
CONTACT RESISTANCE-15 MILLOHM MAX
INSULATION RESISTANCE-10⁹ OHMS MIN (500V DC)




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 08AUG2011 RAGHAVENDRA	TE Connectivity SPRING TYPE. SIDE WIRE ENTRY TERMINAL BLOCK SIDE STACKABLE STRAIGHT 02 - 25 POLES PITCH 5.00mm			
		CHK 08AUG2011 SARVER MICHAEL				
		APVD 08AUG2011 SARVER MICHAEL	NAME			
		PRODUCT SPEC				
		APPLICATION SPEC				
		WEIGHT				
MATERIAL SEE NOTES		FINISH SEE NOTES	SIZE A3	CAGE CODE 00779	DRAWING NO C-1986711	RESTRICTED TO -
CUSTOMER DRAWING		SCALE 4:1	SHEET 1	OF 2	REV B1	

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	2011
© COPYRIGHT 2011	-	ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
FT	0	P	LTR	DESCRIPTION	DATE	APVD
			-	SEE SHEET 1	-	-



2-1986711-6

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RAGHAVENDRA 08AUG2011	 TE Connectivity SPRING TYPE. SIDE WIRE ENTRY TERMINAL BLOCK SIDE STACKABLE STRAIGHT 02 - 25 POLES PITCH 5.00mm				
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK SARVER MICHAEL 08AUG2011					
	0 PLC ±- 1 PLC ±0.5 2 PLC ±0.25 3 PLC ±- 4 PLC ±- ANGLES ±1°	APVD SARVER MICHAEL 08AUG2011					
MATERIAL -	FINISH -	PRODUCT SPEC - APPLICATION SPEC - WEIGHT -					
CUSTOMER DRAWING			NAME	SIZE A3	CAGE CODE 00779	DRAWING NO C-1986711	RESTRICTED TO -
			SCALE 4:1	SHEET 2	OF 2	REV B1	