




THIS INFORMATION IS CONFIDENTIAL AND DISCLOSED TO YOU ON CONDITION THAT NO FURTHER DISCLOSURE IS MADE BY YOU TO OTHER THAN AMP PERSONNEL WITHOUT WRITTEN AUTHORIZATION FROM AUSTRALIAN AMP



CONTROLLED

Technical drawing of a U-shaped profile. The vertical dimension is 3.6 and the horizontal dimension is 3.9. The profile has a rounded bottom with a radius labeled $R1$.

SECTION X-X



SECTION Y-Y

1	OBSOLETE	#6.2	-	-	NICKEL SILVER SIZE 0.4±0.013X11.43±0.050	190225-4
	OBSOLETE	#5.2	-	-	PRE TIN BRASS SIZE 0.5±0.03X11.43±0.050	190225-3
		#5	-	-	PRE TIN BRASS SIZE 0.5±0.03X11.43±0.050	190225-2
	OBSOLETE	#5	-	-	PRE TIN BRASS SIZE 0.5±0.03X11.43±0.050	190225-0
		# A	REMARKS	FINISH	MATERIAL	PART No.

WIRE RANGE 0.5-1.3 sq.mm
INSULATION RANGE 2.54-3.56 mm

ALL DIMENSIONS ARE IN mm TOLERANCES UNLESS OTHERWISE SPECIFIED ARE AS FOLLO					
DIM INCLUDING & UP TO TOLERANCE ±	0-6	6-30	30-120	120-315	>315
	0.1	0.2	0.3	0.5	0.8
	ANGLES ± 0° 30'				

SIZE	AS PER TABLE
------	--------------

DATE 11/04/94

DR RB

NAME

RING TONGUE

AMP Australian AMP Pty. Limited
Nelson Avenue, CASTLE HILL, NSW

SCALE	SIZE	DWG No.
-------	------	---------

C-190225

SHEET	REV
-------	-----

SHEET	REV
1 OF 1	K1

CUSTOMER DRAWING 1

ORIGINAL