

60V DUAL N-CHANNEL ENHANCEMENT MODE MOSFET


Product Summary

$V_{(BR)DSS}$	$R_{DS(on)}$	I_D $T_A = 25^\circ C$
60V	66m Ω @ $V_{GS} = 10V$	4.4A
	97m Ω @ $V_{GS} = 4.5V$	3.6A


Description and Applications

This MOSFET has been designed to minimize the on-state resistance and yet maintain superior switching performance, making it ideal for high efficiency power management applications.


- Motor control
- Backlighting
- DC-DC Converters
- Power management functions



Top View



Top View



Equivalent Circuit

Features and Benefits

- Low on-resistance
- Fast switching speed
- 100% Unclamped Inductive Switch (UIS) test in production
- “Green” component and RoHS compliant (Note 1)
- Qualified to AEC-Q101 Standards for High Reliability

Mechanical Data


- Case: SO-8
- Case Material: Molded Plastic, “Green” Molding Compound. UL Flammability Classification Rating 94V-0 (Note 1)
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals Connections: See diagram below
- Terminals: Finish - Matte Tin annealed over Copper lead frame. Solderable per MIL-STD-202, Method 208
- Weight: 0.074 grams (approximate)

Ordering Information (Note 1)

Product	Marking	Reel size (inches)	Tape width (mm)	Quantity per reel
DMN6066SSD-13	N6066SD	13	12	2,500

Note: 1. Diodes, Inc. defines “Green” products as those which are RoHS compliant and contain no halogens or antimony compounds; further information about Diodes Inc.’s “Green” Policy can be found on our website. For packaging details, go to our website.

Marking Information



𐄂𐄂𐄂 = Manufacturer's Marking
 N6066SD = Product Type Marking Code
 YYWW = Date Code Marking
 YY = Year (ex: 09 = 2009)
 WW = Week (01 - 53)

Maximum Ratings @T_A = 25°C unless otherwise specified





Characteristic		Symbol	Value	Unit
Drain-Source voltage		V _{DSS}	60	V
Gate-Source voltage	(Note 2)	V _{GS}	±20	V
Single Pulsed Avalanche Energy	(Note 9)	E _{AS}	37.5	mJ
Single Pulsed Avalanche Current	(Note 9)	I _{AS}	5.0	A
Continuous Drain current	V _{GS} = 10V	I _D	(Note 4)	A
			T _A = 70°C (Note 4)	
			(Note 3)	
Pulsed Drain current	V _{GS} = 10V	I _{DM}	17.0	A
Continuous Source current (Body diode)	(Note 4)	I _S	3.2	A
Pulsed Source current (Body diode)	(Note 5)	I _{SM}	17.0	A

Thermal Characteristics @T_A = 25°C unless otherwise specified

Characteristic		Symbol	Value	Unit
Power dissipation Linear derating factor	(Notes 3 & 6)	P _D	1.25	W
	(Notes 3 & 7)		10	
	(Notes 4 & 6)		1.8	
	(Notes 4 & 6)		14.3	
Thermal Resistance, Junction to Ambient	(Notes 3 & 6)	R _{θJA}	2.14	°C/W
	(Notes 3 & 7)		17.2	
	(Notes 4 & 6)		100	
Thermal Resistance, Junction to Lead	(Notes 3 & 7)	R _{θJL}	70	°C/W
	(Notes 4 & 6)		58	
	(Notes 6 & 8)		55	
Operating and storage temperature range		T _J , T _{STG}	-55 to 150	°C

- Notes:
- AEC-Q101 V_{GS} maximum is ±16V.
 - For a device surface mounted on 25mm x 25mm x 1.6mm FR4 PCB with high coverage of single sided 1oz copper, in still air conditions; the device is measured when operating in a steady-state condition.
 - Same as note (3), except the device is measured at t ≤ 10 sec.
 - Same as note (3), except the device is pulsed with D = 0.02 and pulse width 300μs. The pulse current is limited by the maximum junction temperature.
 - For a dual device with one active die.
 - For a device with two active die running at equal power.
 - Thermal resistance from junction to solder-point (at the end of the drain lead).
 - UIS in production with L = 3.0mH, I_{AS} = 5.0A, R_G = 25Ω, V_{DD} = 50V, starting T_J = 25°C.

Thermal Characteristics









Electrical Characteristics @T_A = 25°C unless otherwise specified


Characteristic	Symbol	Min	Typ	Max	Unit	Test Condition	
OFF CHARACTERISTICS							
Drain-Source Breakdown Voltage	BV _{DSS}	60	—	—	V	I _D = 250μA, V _{GS} = 0V	
Zero Gate Voltage Drain Current	I _{DSS}	—	—	0.5	μA	V _{DS} = 60V, V _{GS} = 0V	
Gate-Source Leakage	I _{GSS}	—	—	±100	nA	V _{GS} = ±20V, V _{DS} = 0V	
ON CHARACTERISTICS							
Gate Threshold Voltage	V _{GS(th)}	1.0	—	3.0	V	I _D = 250μA, V _{DS} = V _{GS}	
Static Drain-Source On-Resistance (Note 10)	R _{DS (ON)}	—	0.048	0.066	Ω	V _{GS} = 10V, I _D = 4.5A	
			0.068	0.097		V _{GS} = 4.5V, I _D = 3.5A	
Forward Transconductance (Notes 10 & 11)	g _{fs}	—	19.2	—	S	V _{DS} = 15V, I _D = 6A	
Diode Forward Voltage (Note 10)	V _{SD}	—	0.89	1.15	V	I _S = 4.5A, V _{GS} = 0V	
Reverse recovery time (Note 11)	t _{rr}		22.2	—	ns	I _S = 1.9A, di/dt= 100A/μs	
Reverse recovery charge (Note 11)	Q _{rr}	—	16.9	—	nC		
DYNAMIC CHARACTERISTICS (Note 11)							
Input Capacitance	C _{iSS}	—	502	—	pF	V _{DS} = 30V, V _{GS} = 0V f= 1MHz	
Output Capacitance	C _{oSS}	—	45.7	—	pF		
Reverse Transfer Capacitance	C _{rSS}	—	27.1	—	pF		
Total Gate Charge (Note 12)	Q _g	—	5.4	—	nC	V _{GS} = 4.5V	V _{DS} = 30V I _D = 4.5A
Total Gate Charge (Note 12)	Q _g	—	10.3	—	nC	V _{GS} = 10V	
Gate-Source Charge (Note 12)	Q _{gs}	—	1.7	—	nC		
Gate-Drain Charge (Note 12)	Q _{gd}	—	3.2	—	nC		
Turn-On Delay Time (Note 12)	t _{D(on)}	—	2.7	—	ns	V _{DD} = 30V, V _{GS} = 10V I _D = 1A, R _G ≐ 6.0Ω	
Turn-On Rise Time (Note 12)	t _r	—	2.4	—	ns		
Turn-Off Delay Time (Note 12)	t _{D(off)}	—	14.7	—	ns		
Turn-Off Fall Time (Note 12)	t _f	—	5.4	—	ns		

Notes: 10. Measured under pulsed conditions. Pulse width ≤ 300μs; duty cycle ≤ 2%
11. For design aid only, not subject to production testing.
12. Switching characteristics are independent of operating junction temperatures.


Typical Characteristics




Typical Characteristics - continued



Capacitance v Drain-Source Voltage




Gate-Source Voltage v Gate Charge




Single-Pulsed Avalanche Rating


Test Circuits




Basic gate charge waveform



Gate charge test circuit




Switching time waveforms




Switching time test circuit

Package Outline Dimensions



DIM	Inches		Millimeters		DIM	Inches		Millimeters	
	Min.	Max.	Min.	Max.		Min.	Max.	Min.	Max.
A	0.053	0.069	1.35	1.75	e	0.050 BSC		1.27 BSC	
A1	0.004	0.010	0.10	0.25	b	0.013	0.020	0.33	0.51
D	0.189	0.197	4.80	5.00	c	0.008	0.010	0.19	0.25
H	0.228	0.244	5.80	6.20	θ	0°	8°	0°	8°
E	0.150	0.157	3.80	4.00	h	0.010	0.020	0.25	0.50
L	0.016	0.050	0.40	1.27	-	-	-	-	-

Suggested Pad Layout



IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

A. Life support devices or systems are devices or systems which:

1. are intended to implant into the body, or
2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.

B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2011, Diodes Incorporated

www.diodes.com