

NOTE:

1. MATERIAL,
HOUSING: HIGH TEMP PLASTIC, UL94-V0, BLACK
TERMINAL: COPPER ALLOY, SQ=0.40±0.03MM
2. FINISH:
TERMINAL: GOLD AT CONTACT,
G/F OVER 1um(40u")MIN Ni OVER ALL
3. SPEC.:
PRODUCT SPEC: GS-12-629
PACKING SPEC: GS-14-1420
4. THE HSG. WILL WITHSTAND EXPOSURE TO 260C
PEAK TEMP. FOR 5 SEC. IN A WAVE SOLDER APPLICATION
WITH A PCB.
5. PRODUCT NUMBERING:
20021511 - 0 0 0 XX X X LF

LEAD FREE

PLATING:

1:GOLD FLASH ALL OVER

4:0.25um(10U")GOLD AT CONTACT

8:0.76um(30U")GOLD AT CONTACT

9:1u" GOLD OVER 30u" PdNi AT CONTACT

PACKING

T: TUBE

PIN COUNT

SEE TABLE 1






TABLE 1 ,DIM INFORMATION

DASH No.	Dim.	Amount of Pins	Dim.A	Dim.B
-000 06 XX LF	06	2.54	10.11	
-000 10 XX LF	10	5.08	12.65	
-000 12 XX LF	12	6.35	13.92	
-000 14 XX LF	14	7.62	15.19	
-000 16 XX LF	16	8.89	16.46	
-000 20 XX LF	20	11.43	19.00	
-000 26 XX LF	26	15.24	22.81	
-000 30 XX LF	30	17.78	25.35	

DASH No.	Dim.	Amount of Pins	Dim.A	Dim.B
-000 34 XX LF	34	20.32	27.89	
-000 40 XX LF	40	24.13	31.70	
-000 44 XX LF	44	26.67	34.24	
-000 50 XX LF	50	30.48	38.05	
-000 60 XX LF	60	36.83	44.40	
-000 64 XX LF	64	39.37	46.94	
-000 68 XX LF	68	41.91	49.48	
-000 80 XX LF	80	49.53	57.10	
-000 A0 XX LF	100	62.23	69.80	

Recommended P.C.B. Layout
Layout Tolerance = ± 0.05 mm

mat'l. code		surface	tolerance	projection	product family
ISO1302		ISO1101	ISO406	MM	MINITEK
l t r e c n n o d r		date		title	
A		T09-1117 S.LIN		09/15/09	
B		T10-0022 S.LIN		01/20/10	
C		BX-N-010362 ZK		01/16/12	
		dr		STERLING LIN	
		engr		STERLING LIN	
		chr		GRAY HSIEH	
		appd		JOSEPH	
sheet		revision		scale 5:1	
index		sheet		dwg no	
		1		20021511	
				type	
				Product Customer Drawing	