



Have a Question?
Chat with a Product
Information Specialist



[My Cart](#) | [My Part Lists](#) | [Sign In/Register](#)

[English](#) (Change)

What can we help you find?

[Submit](#)

[Products](#) [Industries](#) [Resources](#) [About TE](#) [My Account](#) [Innovation](#) [Support Center](#)

1571541-1 Product Details




[Share](#)



[Print](#)



[Email](#)



1571541-1

TE Internal Number: 1571541-1



[Pending Obsolescence](#)

[Contact Product Information Center](#)



[View 3D PDF](#)

PLCC Sockets



Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Socket Type = PCS Series
- 44 Positions
- 2.54 mm Centerline
- Normal Insertion Force
- Through Hole Contact Termination Type

[View all Features](#)

Quick Links

[Check Pricing & Availability](#)
[Search for Tooling](#)
[Product Feature Selector](#)
[Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [OUTLINE DRAWING PLCC SOCKET](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: (CAD Format & Compression Information)

- [2D Drawing](#) (DXF, Version D)
- [3D Model](#) (IGES, Version D)
- [3D Model](#) (STEP, Version D)

[List all Documents](#)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Insertion Force](#) = Normal
- [Polarizing Pin](#) = Without
- Package Configuration = Square

Electrical Characteristics:

- Current Rating (A) = 1
- Contact Resistance (mΩ) = 30

Termination Features:

- [Contact Termination Type](#) = Through Hole

Dimensions:

- [Height Above PC Board](#) (mm [in]) = 9.15 [0.360]

Body Features:

- Socket Type = PCS Series

Contact Features:

- Contact Base Material = Copper Alloy
- Contact Plating, Mating Area, Material = Tin

Housing Features:

- Centerline (mm [in]) = 2.54 [0.100]
- Housing Material = PPS
- UL Flammability Rating = UL 94V-0

Configuration Features:

- [Number of Positions](#) = 44

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Packaging Features:

- Packaging Method = Carton

Other:

- Brand = AMP

Corporate Information

[About TE](#)

[Investors](#)

[News Room](#)

[Supplier Portal](#)

[Careers](#)

[Terms & Conditions](#)

[Privacy Policy](#)

Quick Links

[Check Distributor Inventory](#)

[Cross Reference Products](#)

[Find Documents & Drawings](#)

[Product Compliance Support Center](#)

[Site Map](#)

Customer Support

[Email or Chat With Us](#)

[Find a Phone Number](#)

[Search Knowledge Base](#)

[Manage Your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address



