


THESE DRAWINGS ARE THE PROPERTY OF QUALTEK ELECTRONICS AND NOT TO BE REPRODUCED FOR OR COMMUNICATED TO A THIRD PARTY WITHOUT THE EXPRESS WRITTEN PERMISSION OF AN OFFICER OF QUALTEK ELECTRONICS.

REVISION			
REV.	DESCRIPTION	DATE	APPROVED
B	RoHS Compliancy	06-01-06	DP
C	Updated Dimensions	06-30-08	DP
D	Updated Panel Thickness, Cutout, and Approvals	03-03-16	LY



NOTES:

RATING:

UL, CSA: 15A 250V AC
VDE, CCC: 10A 250V AC
INSULATION RESISTANCE: OVER 100M OHM 500V DC
DIELECTRIC RESISTANCE: 2000V AC ONE MINUTE
PANEL THICKNESS: 0.8mm ~ 1.5mm
APPROVALS: UL, CSA, VDE, CCC
RoHS COMPLIANT

CONTROLLED

2	Contact Pin Brass Strip Tin-Plated	3
1	Body Insulator Nylon Black Color	1
Qualtek Electronics Corp. PPC DIVISION		
Dim range (mm)	Tolerance +/- (mm)	Part Number: 701W-X2/02 RoHS Compliant
0-1	0.15	Description: AC RECEPTACLE
1-6	0.20	
6-18	0.30	
18-50	0.50	UNIT: mm REV.D
50-120	0.70	
120-250	0.90	Drawn / Date Checked / Date Approved / Date
250-500	1.20	B.Zhang 10-25-04 10-25-04 JJH / 10-25-04