

△6	101.19 [3.984]	99.06 [3.900]	39	80	9-146487-0
△6	98.65 [3.884]	96.52 [3.800]	38	78	8-146487-9
△6	96.11 [3.784]	93.98 [3.700]	37	76	8-146487-8
△6	93.57 [3.684]	91.44 [3.600]	36	74	8-146487-7
△6	91.03 [3.584]	88.90 [3.500]	35	72	8-146487-6
△6	88.49 [3.484]	86.36 [3.400]	34	70	8-146487-5
△6	85.95 [3.384]	83.82 [3.300]	33	68	8-146487-4
△6	83.41 [3.284]	81.28 [3.200]	32	66	8-146487-3
△6	80.87 [3.184]	78.74 [3.100]	31	64	8-146487-2
△6	78.33 [3.084]	76.20 [3.000]	30	62	8-146487-1
△6	75.79 [2.984]	73.66 [2.900]	29	60	8-146487-0
△6	73.25 [2.884]	71.12 [2.800]	28	58	7-146487-9
△6	70.71 [2.784]	68.58 [2.700]	27	56	7-146487-8
△6	68.17 [2.684]	66.04 [2.600]	26	54	7-146487-7
△6	65.63 [2.584]	63.50 [2.500]	25	52	7-146487-6
△6	63.09 [2.484]	60.96 [2.400]	24	50	7-146487-5
△6	60.55 [2.384]	58.42 [2.300]	23	48	7-146487-4
△6	58.01 [2.284]	55.88 [2.200]	22	46	7-146487-3
△6	55.47 [2.184]	53.34 [2.100]	21	44	7-146487-2
△6	52.93 [2.084]	50.80 [2.000]	20	42	7-146487-1
△6	50.39 [1.984]	48.26 [1.900]	19	40	7-146487-0
△6	47.85 [1.884]	45.72 [1.800]	18	38	6-146487-9
△6	45.31 [1.784]	43.18 [1.700]	17	36	6-146487-8
△6	42.77 [1.684]	40.64 [1.600]	16	34	6-146487-7
△6	40.23 [1.584]	38.10 [1.500]	15	32	6-146487-6
△6	37.69 [1.484]	35.56 [1.400]	14	30	6-146487-5
△6	35.15 [1.384]	33.02 [1.300]	13	28	6-146487-4
△6	32.61 [1.284]	30.48 [1.200]	12	26	6-146487-3
△6	30.07 [1.184]	27.94 [1.100]	11	24	6-146487-2
△6	27.53 [1.084]	25.40 [1.000]	10	22	6-146487-1
△6	24.99 [.984]	22.86 [.900]	9	20	6-146487-0
△6	22.45 [.884]	20.32 [.800]	8	18	5-146487-9
△6	19.91 [.784]	17.78 [.700]	7	16	5-146487-8
△6	17.37 [.684]	15.24 [.600]	6	14	5-146487-7
△6	14.83 [.584]	12.70 [.500]	5	12	5-146487-6
△6	12.29 [.484]	10.16 [.400]	4	10	5-146487-5
△6	9.75 [.384]	7.62 [.300]	3	8	5-146487-4
△6	7.21 [.284]	5.08 [.200]	2	6	5-146487-3
△6	4.67 [.184]	2.54 [.100]	1	4	5-146487-2
△6	2.13 [.084]	-	-	2	5-146487-1
PLATING	G	F	E	NO. OF POSITIONS	LEAD FREE P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN T. HOFFMAN 05DEC95		STE TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:			
0. PLC ± -		1. PLC ± -		G. DUBNICZKI 02JAN96	
1. PLC ± -		2. PLC ± 0.51[.02]		APVD G. DUBNICZKI 02JAN96	
2. PLC ± -		3. PLC ± 0.12[.005]		NAME	
3. PLC ± -		4. PLC ± 0.012[.0005]		PRODUCT SPEC	
4. PLC ± -		ANGLES ± -		APPLICATION SPEC	
MATERIAL		FINISH		SIZE	
SEE TABLE		WEIGHT		CAGE CODE	
		A1		DRAWING NO.	
		-		RESTRICTED TO	
		-		C=146487	
		-		SCALE	
		-		1:1	
		-		SHEET	
		-		2 OF 2	
		-		REV	
		-		B	