



Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NO.	ROWS	POWER				SIG			PWR			SIG			E1
		E2	P4	P3	P2	7	6	5	P1	4	3	2	1		
51940-125-- NOTE 3	D C B A		PF	PC	PC	F	F	F	PC	F	F	F	F		
						F	F	F		F	F	F	F		
						F	F	F		F	F	F	F		
						F	F	F		F	F	F	F		



CODE	DIM "M" MATING LENGTH	CONTACT TYPE
PC	.042 [1.07]	POWER
F	N/A [N/A]	SIGNAL
PF	.092 [2.34]	POWER
X	OMITTED	OMITTED

mat'l code				tolerances unless otherwise specified		CUSTOMER		FCI	
SEE NOTE 2						COPY		www.fciconnect.com	
lir	ecr no.	dr	date	linear	.XX±.01/0.X±0.3	projection		title	
A	DG05-0029	SLUO	3/9/05		.XXX±.005/0.XX±0.13			16S+1P+12S +3P VERTICAL PF RECEPT	
B	DG05-0057	SLUO	3/24/05		.XXX±.0020/0.XXX±0.051				
C	DG06-0181	RYAN	05/12/06	angles	0°±2°	INCH/MM		product family	
				dr	SLUO 3/9/05	scale		PwrBlade	
				enrg	M. MOSTOLLER mm/dd/yy			code	
				chr	VICTOR LIN 3/9/05	1:1		size	
				appd	JOSEPH HSIA 3/9/05			dwg no	
sheet index		revision	C	C	C			A	
		sheet	1	2	3			51940-125	
								213	
								sheet	
								1 of 4	

cage code 22526




Pro/E

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NUMBER
51940-125--
NOTE 3




mat'l code				SEE NOTE 2		tolerances unless otherwise specified		CUSTOMER		FCI	
lir	ecr no.	dr	date	linear	linear	.XX±.01/0.X±0.3	projection	COPY	www.fciconnect.com		
B				angles	angles	.XXX±.005/0.XX±0.13	INCH/MM		title	16S+1P+12S +3P	
				dr	dr	.XXX±.002/0.XXX±0.051	scale	1:1	product family	PwrBlade	code
				enrg	enrg	0°±2°			size	dwg no	213
				chr	chr				A	51940-125	sheet
				appd	appd						2 of 4
sheet index	revision	sheet									

Pro/E

cage code 22526



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.



coge code	22526
-----------	-------

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

1 | 2

3 |

4

PRODUCT NUMBER

51940-125--
NOTE 3

NOTES:

1. DIMENSIONS AND TOLERANCES ARE IN ACCORDANCE WITH
ASME Y14.5M, 1994 UNLESS OTHERWISE SPECIFIED.

CONNECTOR NOTES:

- 2 HOUSING MATERIAL: UL 94 V-0 GLASS FILLED
HIGH-TEMP THERMOPLASTIC
POWER CONTACT MATERIAL: COPPER ALLOY
SIGNAL PIN MATERIAL: COPPER ALLOY
3. PLATING:
SEE PRINT 10064183 FOR PLATING SPEC OF 51940-125; 51940-125LF
- 4 MANUFACTURER'S NAME, P/N, AND DATE CODE TO APPEAR ON
THIS SURFACE.
5. PRODUCT SPECIFICATION GS-12-149.
APPLICATION SPECIFICATION BUS-20-067.
6. PACKAGED IN TRAYS.

PCB NOTES:

7. ALL HOLE DIAMETERS ARE FINISHED HOLE SIZE.
- 8 MOUNTING HOLES, WHERE APPLICABLE, ARE UNPLATED.
- 9 $\varnothing.0453 \pm .0010$ [1.151 $\pm$ 0.025] DRILLED HOLES PLATED WITH
.0003 [0.008] MIN SnPb OVER .001 [0.03]
TO .003 [0.08] Cu PLATING TO ACHIEVE
 $\varnothing.040 \pm .003$ [1.02 $\pm$.07] HOLE.
- 10 "DIM XXX" TO BE DETERMINED BY THE CUSTOMER.
- 11 CONNECTOR KEEP-OUT ZONE.

mat'l code				SEE NOTE 2		tolerances unless otherwise specified		CUSTOMER				www.fciconnect.com	
lfr	ecr no.	dr	date	linear	.XX $\pm$.01/0.X $\pm$ 0.3			COPY			title 16S+1P+12S +3P VERTICAL PF RECEPT		
B					.XXX $\pm$.005/0.XX $\pm$ 0.13			projection					
					.XXX $\pm$.002/0.XXX $\pm$ 0.051								
				angles	0 $^{\circ}$ $\pm$ 2 $^{\circ}$			INCH/MM					
				dr	SLUO	3/9/05		scale		product family		PwrBlade	code
				enrg	M. MOSTOLLER	mm/dd/yy		1:1		size		dwg no	213
				chr	VICTOR LIN	3/9/05				A		51940-125	sheet
				appd	JOSEPH HSIA	3/9/05							4 of 4
sheet index		revision sheet											

1 | 2

Pro/E

3 |

cage code 22526

4