




LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			N5	REVISED PER ECO-11-004587	11MAR11	RK	HMR



- ① FINISH OVER INDICATED AREA: .000100—.000200
BRIGHT TIN LEAD OVER .000050 NICKEL.
- ② FINISH OVER INDICATED AREA: .000015
GOLD OVER .000050 NICKEL.
- ③ POINT OF MEASUREMENT FOR PLATING THICKNESS.
- ④ RECESSED DATE CODE AND CSA LOGO.
- ⑤ OBSOLETE PART NUMBER.
- ⑥ FINISH OVER INDICATED AREA: .000100—.000200
MATTE TIN OVER .000050 NICKEL.
- ⑦ PRELIMINARY PART.
- ⑧ ROHS 2002/95/EC COMPLIANT
- ⑨ HEADER: GLASS—FILLED, FLAME RETARDANT
THERMOPLASTIC COLOR: BLACK
POST: COPPER ALLOY
- ⑩ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. HAYMAKER 30MAR00 CHK J. GESFORD 30MAR00 APVD J. GESFORD 30MAR00		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± -		NAME	
		PRODUCT SPEC —		HEADER ASSEMBLY, MOD II, .100 X .100CL	
MATERIAL		APPLICATION SPEC —		SIZE	RESTRICTED TO
		WEIGHT —		CAGE CODE A2 00779	DRAWING NO C-102567
SEE NOTES		CUSTOMER DRAWING		SCALE 4:1	SHEET 1 OF 2
				REV N5	

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	00		—	SEE SHEET 1	—	—	—

D

D

C

C

B

B

A

A

5 10 OBSOLETE	5 8	7-102567-9					
	5 8	7-102567-8					
	5 8	7-102567-7					
	5 8	7-102567-6					
	5 8	7-102567-5					
	5 8	7-102567-4					
	5 8	7-102567-3					
	5 8	7-102567-2					
	5 8	7-102567-1					
	5 8	7-102567-0					
5 10	5 8	6-102567-9					
5 10	5 8	6-102567-8					
5 10	5 8	6-102567-7					
5 10	5 8	6-102567-6					
5 10	5 8	6-102567-5					
5 10	5 8	6-102567-4					
2 6	5 8	6-102567-3					
	5 8	6-102567-2					
	5 8	6-102567-1					
	5 8	6-102567-0					
	5 8	5-102567-9					
	5 8	5-102567-8					
	5 8	5-102567-7					
	5 8	5-102567-6					
	5 8	5-102567-5					
	5 8	5-102567-4					
	5 8	5-102567-3					
	5 8	5-102567-2					
	5 8	5-102567-1					
FINISH	E	D	C	B	A	NO. OF POSN	PART NUMBER

SUPERSEDED BY 5-102567-1			2 6	.870	.980	.900	.500	5	12	3-102567-0
8 7	10 7	OBSOLETE	1 2	1.870	1.980	1.900	1.500	15	32	2-102567-9
10 7	OBSOLETE	9.270		9.380	9.300	8.900	89	180	2-102567-8	
	OBSOLETE	7.670		7.780	7.700	7.300	73	148	2-102567-7	
	OBSOLETE	6.670		6.780	6.700	6.300	63	128	2-102567-6	
	OBSOLETE	4.970		5.080	5.000	4.600	46	94	2-102567-5	
	OBSOLETE	2.470		2.580	2.500	2.100	21	44	2-102567-4	
		.970		1.080	1.000	.600	6	14	2-102567-3	
	OBSOLETE	8.270		8.380	8.300	7.900	79	160	2-102567-2	
	5	10.270		10.380	10.300	9.900	99	200	2-102567-1	
	OBSOLETE	7.270		7.380	7.300	6.900	69	140	2-102567-0	
	5	6.770		6.880	6.800	6.400	64	130	1-102567-9	
	OBSOLETE	1.070		1.180	1.100	.700	7	16	1-102567-8	
10	OBSOLETE	4.570		4.680	4.600	4.200	42	86	1-102567-7	
		3.870		3.980	3.900	3.500	35	72	1-102567-6	
		5.770		5.880	5.800	5.400	54	110	1-102567-5	
10	OBSOLETE	4.770		4.880	4.800	4.400	44	90	1-102567-4	
1 2		1.770		1.880	1.800	1.400	14	30	1-102567-3	
		2.270		2.380	2.300	1.900	19	40	1-102567-2	
		1.270		1.380	1.300	.900	9	20	1-102567-1	
		3.770		3.880	3.800	3.400	34	70	1-102567-0	
		5.270		5.380	5.300	4.900	49	100	102567-9	
		4.270		4.380	4.300	3.900	39	80	102567-8	
	10	OBSOLETE		6.270	6.380	6.300	5.900	59	120	102567-7
		2.770		2.880	2.800	2.400	24	50	102567-6	
	10	OBSOLETE	5.070	5.180	5.100	4.700	47	96	102567-5	
		3.270	3.380	3.300	2.900	29	60	102567-4		
		2.070	2.180	2.100	1.700	17	36	102567-3		
		1.470	1.580	1.500	1.100	11	24	102567-2		
		.870	.980	.900	.500	5	12	102567-1		
FINISH			E	D	C	B	A	NO. OF POSN	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

0

1

2

3

4

PLC
PLC
PLC
PLC
PLC

±
±
±
±
±

-
-
-
.005
-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

FINISH

SEE NOTES

DWN
B. HAYMAKER

CHK
J. GESFORD

APVD
J. GESFORD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

30MAR00

30MAR00

30MAR00

TE Connectivity

NAME

HEADER ASSEMBLY, MOD II,
.100 X .100CL

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

SCALE

SHEET

REV

A2

00779

C=102567

4:1

2 of 2

N5