


2SC4668
(TE7S4)

7A NPN

OUTLINE DIMENSIONS



RATINGS

●Absolute Maximum Ratings


Item	Symbol	Conditions	Ratings	Unit
Storage Temperature	Tstg		-55~150	℃
Junction Temperature	Tj		150	℃
Collector to Base Voltage	V _{CBO}		60	V
Collector to Emitter Voltage	V _{CEO}		40	V
Emitter to Base Voltage	V _{EBO}		7	V
Collector Current DC	I _C		7	A
Collector Current Peak	I _{CP}		14	A
Base Current DC	I _B		1.5	A
Base Current Peak	I _{BP}		2	A
Total Transistor Dissipation	P _T	Tc = 25℃	10	W

●Electrical Characteristics (Tc=25℃)


Item	Symbol	Conditions	Ratings	Unit
Collector to Emitter Sustaining Voltage	V _{CEO(sus)}	I _C = 0.1A	Min 40	V
Collector Cutoff Current	I _{CBO}	At rated Voltage	Max 0.1	mA
	I _{CEO}		Max 0.1	
Emitter Cutoff Current	I _{EBO}	At rated Voltage	Max 0.1	mA
DC Current Gain	h _{FE}	V _{CE} = 2V, I _C = 3.5A	Min 70	
Collector to Emitter Saturation Voltage	V _{CE(sat)}	I _C = 3.5A	Max 0.3	V
Base to Emitter Saturation Voltage	V _{BE(sat)}	I _B = 0.2A	Max 1.2	V
Thermal Resistance	θ jc	Junction to case	Max 12.5	℃/W
Transition Frequency	f _T	V _{CE} = 10V, I _C = 0.7A	TYP 50	MHz
Turn on Time	ton	I _C = 3.5A I _{B1} = 0.35A, I _{B2} = 0.35A R _L = 8Ω, V _{BB2} = 4V	Max 0.3	μ s
Storage Time	ts		Max 1.5	
Fall Time	tf		Max 0.5	

2SC4668

$h_{FE} - I_C$




2SC4668 Saturation Voltage




2SC4668

Switching Time - I_C




2SC4668


Switching Time - Tc



2SC4668 Transient Thermal Impedance




2SC4668 Forward Bias SOA



2SC4668

Collector Current Derating



2SC4668

Reverse Bias SOA

