


### Dual IGBTMOD™ NFH-Series Module 600 Amperes/600 Volts



Outline Drawing and Circuit Diagram

| Dimensions | Inches          | Millimeters   |
|------------|-----------------|---------------|
| A          | 4.33            | 110.0         |
| B          | 3.15            | 80.0          |
| C          | 1.14+0.04/-0.01 | 29.0+1.0/-0.5 |
| D          | 3.66±0.01       | 93.0±0.25     |
| E          | 2.44±0.01       | 62.0±0.25     |
| F          | 0.83            | 21.2          |
| G          | 0.28            | 7.0           |
| H          | 0.24            | 6.0           |
| J          | 0.59            | 15.0          |
| K          | 0.55            | 14.0          |
| L          | 0.35            | 9.0           |
| M          | 0.33            | 8.5           |
| N          | 0.69            | 17.5          |
| P          | 0.85            | 21.5          |

| Dimensions | Inches    | Millimeters |
|------------|-----------|-------------|
| Q          | 0.98      | 25.0        |
| R          | 1.23      | 31.4        |
| S          | M6 Metric | M6          |
| T          | 0.26 Dia. | 6.5 Dia.    |
| U          | 0.4       | 10.0        |
| V          | 0.16      | 4.0         |
| W          | 0.87      | 22.2        |
| X          | 0.72      | 18.25       |
| Y          | 0.36      | 9.25        |
| Z          | 0.71      | 18.0        |
| AA         | 0.11      | 2.8         |
| AB         | 0.29      | 7.5         |
| AC         | 0.21      | 5.3         |
| AD         | 0.47      | 12.0        |



#### Description:

Powerex IGBTMOD™ Modules are designed for use in high frequency applications; 30 kHz for hard switching applications and 60 to 70 kHz for soft switching applications. Each module consists of two IGBT Transistors in a half-bridge configuration with each transistor having a reverse-connected super-fast recovery free-wheel diode. All components and interconnects are isolated from the heat sinking baseplate, offering simplified system assembly and thermal management.

#### Features:

- ☐ Low  $V_{CE(sat)}$
- ☐ Low  $ESW(off)$
- ☐ Discrete Super-Fast Recovery Free-Wheel Diode
- ☐ Isolated Baseplate for Easy Heat Sinking

#### Applications:

- ☐ Power Supplies
- ☐ Induction Heating
- ☐ Welders

#### Ordering Information:

Example: Select the complete part module number you desire from the table below -i.e.

CM600DU-12NFH is a 600V ( $V_{CES}$ ), 600 Ampere Dual IGBTMOD™ Power Module.

| Type | Current Rating<br>Amperes | $V_{CES}$<br>Volts (x 50) |
|------|---------------------------|---------------------------|
| CM   | 600                       | 12                        |

## CM600DU-12NFH

### Dual IGBTMOD™ NFH-Series Module

600 Amperes/600 Volts

#### Absolute Maximum Ratings, $T_j = 25^\circ\text{C}$ unless otherwise specified

| Item                                                                                  | Symbol            | Rating         | Units            |
|---------------------------------------------------------------------------------------|-------------------|----------------|------------------|
| Collector-Emitter Voltage (G-E Short-circuited)                                       | $V_{CES}$         | 600            | Volts            |
| Gate-Emitter Voltage (C-E Short-circuited)                                            | $V_{GES}$         | $\pm 20$       | Volts            |
| Collector Current (Operation)*5                                                       | $I_C$             | 600            | Amperes          |
| Collector Current (Operation)*5                                                       | $I_{C(rms)}$      | 400            | Amperes          |
| Collector Current (Pulse, Repetitive)*4                                               | $I_{CRM}$         | 1200           | Amperes          |
| Total Power Dissipation ( $T_C = 25^\circ\text{C}$ )*2,*5                             | $P_{tot}$         | 1130           | Watts            |
| Total Power Dissipation ( $T_C' = 25^\circ\text{C}$ )*3,*5                            | $P_{tot}'$        | 2350           | Watts            |
| Emitter Current (Free Wheeling Diode Forward Current, Operation)*5                    | $I_E^{*1}$        | 600            | Amperes          |
| Emitter Current (Free Wheeling Diode Forward Current, Operation)*5                    | $I_{E(rms)}^{*1}$ | 400            | Amperes          |
| Emitter Current (Free Wheeling Diode Forward Current, Operation, Pulse, Repetitive)*4 | $I_{ERM}^{*1}$    | 1200           | Amperes          |
| Junction Temperature                                                                  | $T_j$             | $-40$ to $150$ | $^\circ\text{C}$ |
| Storage Temperature                                                                   | $T_{stg}$         | $-40$ to $125$ | $^\circ\text{C}$ |
| Isolation Voltage (Terminals to Baseplate, RMS, $f = 60\text{Hz}$ , AC 1 min.)        | $V_{ISO}$         | 2500           | Volts            |


\*1 Represent ratings and characteristics of the anti-parallel, emitter-to-collector free wheeling diode (FWD).

\*2 Case temperature ( $T_C$ ) and heatsink temperature ( $T_S$ ) is measured on the surface (mounting side) of the baseplate and the heatsink side just under the chips. Refer to the figure to the right for chip location.

\*3 Case temperature ( $T_C'$ ) and heatsink temperature ( $T_S'$ ) is measured on the surface (mounting side) of the baseplate and the heatsink side just under the chips. Refer to the figure to the right for chip location. The heatsink thermal resistance ( $R_{th(s-a)}$ ) should be measured just under the chips.

\*4 Pulse width and repetition rate should be such that device junction temperature ( $T_j$ ) does not exceed  $T_{j(max)}$  rating.

\*5 Junction temperature ( $T_j$ ) should not increase beyond maximum junction temperature ( $T_{j(max)}$ ) rating.



Each mark points to the center position of each chip.  
T1 / T2 : IGBT      D1 / D2 : FWD

## CM600DU-12NFH

### Dual IGBTMOD™ NFH-Series Module

600 Amperes/600 Volts

#### Electrical Characteristics, $T_j = 25^\circ\text{C}$ unless otherwise specified

| Characteristics                      | Symbol        | Test Conditions                                                      | Min. | Typ. | Max. | Units    |
|--------------------------------------|---------------|----------------------------------------------------------------------|------|------|------|----------|
| Collector-Emitter Cutoff Current     | $I_{CES}$     | $V_{CE} = V_{CES}, V_{GE} = 0V$                                      | —    | —    | 1.0  | mA       |
| Gate-Emitter Leakage Current         | $I_{GES}$     | $\pm V_{GE} = V_{GES}, V_{CE} = 0V$                                  | —    | —    | 0.5  | $\mu A$  |
| Gate-Emitter Threshold Voltage       | $V_{GE(th)}$  | $I_C = 60mA, V_{CE} = 10V$                                           | 5.0  | 6.0  | 7.0  | Volts    |
| Collector-Emitter Saturation Voltage | $V_{CE(sat)}$ | $I_C = 600A, V_{GE} = 15V, T_j = 25^\circ\text{C}^{*6}$              | —    | 2.0  | 2.7  | Volts    |
|                                      |               | $I_C = 600A, V_{GE} = 15V, T_j = 125^\circ\text{C}^{*6}$             | —    | 1.95 | —    | Volts    |
| Input Capacitance                    | $C_{ies}$     | $V_{CE} = 10V, V_{GE} = 0V$                                          | —    | —    | 166  | nF       |
| Output Capacitance                   | $C_{oes}$     |                                                                      | —    | —    | 11   | nF       |
| Reverse Transfer Capacitance         | $C_{res}$     |                                                                      | —    | —    | 6.0  | nF       |
| Gate Charge                          | $Q_G$         | $V_{CC} = 300V, I_C = 600A, V_{GE} = 15V$                            | —    | 3720 | —    | nC       |
| Turn-on Delay Time                   | $t_{d(on)}$   | $V_{CC} = 300V, I_C = 600A,$<br>$V_{GE} = \pm 15V, R_G = 2.0\Omega,$ | —    | —    | 650  | ns       |
| Rise Time                            | $t_r$         |                                                                      | —    | —    | 250  | ns       |
| Turn-off Delay Time                  | $t_{d(off)}$  |                                                                      | —    | —    | 800  | ns       |
| Fall Time                            | $t_f$         | Inductive Load Switching Operation                                   | —    | —    | 150  | ns       |
| Emitter-Collector Voltage            | $V_{EC}^{*1}$ | $I_E = 600A, V_{GE} = 0V^{*6}$                                       | —    | 2.0  | 2.6  | Volts    |
| Reverse Recovery Time                | $t_{rr}^{*1}$ | $V_{CC} = 300V, I_E = 600A, V_{GE} = \pm 15V$                        | —    | —    | 200  | ns       |
| Reverse Recovery Charge              | $Q_{rr}^{*1}$ | $R_G = 2.0\Omega, \text{Inductive Load}$                             | —    | 11   | —    | $\mu C$  |
| Turn-on Switching Energy per Pulse   | $E_{on}$      | $V_{CC} = 300V, I_C = I_E = 600A,$                                   | —    | 11   | —    | mJ       |
| Turn-off Switching Energy per Pulse  | $E_{off}$     | $V_{GE} = \pm 15V, R_G = 2.0\Omega,$                                 | —    | 27   | —    | mJ       |
| Reverse Recovery Energy per Pulse    | $E_{rr}^{*1}$ | $T_j = 125^\circ\text{C}, \text{Inductive Load}$                     | —    | 6.3  | —    | mJ       |
| Internal Gate Resistance             | $r_g$         | Per Switch                                                           | —    | 0.8  | —    | $\Omega$ |

\*1 Represent ratings and characteristics of the anti-parallel, emitter-to-collector free wheeling diode (FWDi).

\*6 Pulse width and repetition rate should be such as to cause negligible temperature rise.

## CM600DU-12NFH

### Dual IGBTMOD™ NFH-Series Module

600 Amperes/600 Volts

## Thermal Resistance Characteristics

|                                                               |                 |                                                        |   |      |       |     |
|---------------------------------------------------------------|-----------------|--------------------------------------------------------|---|------|-------|-----|
| Thermal Resistance, Junction to Case* <sup>2</sup>            | $R_{th(j-c)}Q$  | Per IGBT                                               | — | —    | 0.11  | K/W |
| Thermal Resistance, Junction to Case* <sup>2</sup>            | $R_{th(j-c)}D$  | Per FWDi                                               | — | —    | 0.12  | K/W |
| Contact Thermal Resistance,<br>Case to Heatsink* <sup>2</sup> | $R_{th(c-f)}$   | Thermal Grease Applied<br>(Per 1 Module)* <sup>7</sup> | — | 0.02 | —     | K/W |
| Thermal Resistance, Junction to Case* <sup>3</sup>            | $R_{th(j-c')}Q$ | Per IGBT                                               | — | —    | 0.053 | K/W |
| Thermal Resistance, Junction to Case* <sup>3</sup>            | $R_{th(j-c')}D$ | Per FWDi                                               | — | —    | 0.078 | K/W |

## Mechanical Characteristics

|                       |       |                                  |      |     |      |         |
|-----------------------|-------|----------------------------------|------|-----|------|---------|
| Mounting Torque       | $M_t$ | Main Terminals, M6 Screw         | 31   | 35  | 40   | in-lb   |
|                       | $M_s$ | Mounting to Heatsink, M6 Screw   | 31   | 35  | 40   | in-lb   |
| Weight                | m     |                                  | —    | 580 | —    | Grams   |
| Flatness of Baseplate | $e_c$ | On Centerline X, Y* <sup>8</sup> | -100 | —   | +100 | $\mu m$ |

## Recommended Operating Conditions, $T_a = 25^\circ C$

|                               |              |                                |      |      |      |          |
|-------------------------------|--------------|--------------------------------|------|------|------|----------|
| (DC) Supply Voltage           | $V_{CC}$     | Applied Across C1-E2           | —    | 300  | 400  | Volts    |
| Gate (-Emitter Drive) Voltage | $V_{GE(on)}$ | Applied Across G1-Es1 / G2-Es2 | 13.5 | 15.0 | 16.5 | Volts    |
| External Gate Resistance      | $R_G$        | Per Switch                     | 1.0  | —    | 10   | $\Omega$ |

\*<sup>2</sup> Case temperature ( $T_C$ ) and heatsink temperature ( $T_S$ ) is measured on the surface (mounting side) of the baseplate and the heatsink side just under the chips. Refer to the figure to the right for chip location.



The heatsink thermal resistance should be measured just under the chips.

\*<sup>3</sup> Case temperature ( $T_C'$ ) and heatsink temperature ( $T_S'$ ) is measured on the surface (mounting side) of the baseplate and the heatsink side just under the chips. Refer to the figure to the right for chip location.

The heatsink thermal resistance ( $R_{th(s-a)}$ ) should be measured just under the chips.

\*<sup>7</sup> Typical value is measured by using thermally conductive grease of  $\lambda = 0.9 [W/(m \cdot K)]$ .

\*<sup>8</sup> Baseplate (mounting side) flatness measurement points (X, Y) are shown in the figure below.












Each mark points to the center position of each chip.

T1 / T2 : IGBT D1 / D2 : FWDi

## CM600DU-12NFH

### Dual IGBTMOD™ NFH-Series Module

600 Amperes/600 Volts



## CM600DU-12NFH

### Dual IGBTMOD™ NFH-Series Module

600 Amperes/600 Volts

