

SPECIFICATION CONTROL DRAWING

55A0122TITLE
TWO CONDUCTOR CABLE, UNSHIELDED, UNJACKETED, GENERAL PURPOSE, 600 VOLTDate
5-2-12Revision
D

This specification sheet forms a part of the latest issue of Raychem Specification 55A.

COMPONENT WIRES - 55A0112



CABLE CONSTRUCTION DETAILS

PART NUMBER <u>1/</u>	CONDUCTOR SIZE (AWG)	OUTSIDE DIAMETER (inches)		MAXIMUM WEIGHT (lbs/1000 ft.)
		NOMINAL	MAXIMUM	
55A0122-30-*	30	.048	.052	1.4
55A0122-28-*	28	.054	.058	1.9
55A0122-26-*	26	.064	.068	2.9
55A0122-24-*	24	.074	.078	4.1
55A0122-22-*	22	.086	.090	5.7
55A0122-20-*	20	.100	.104	8.8
55A0122-18-*	18	.120	.124	13.3
55A0122-16-*	16	.136	.140	16.9
55A0122-14-*	14	.170	.176	26.5
55A0122-12-*	12	.206	.212	40.2
55A0122-10-*	10	.256	.268	65.9

CABLE RATINGS AND ADDITIONAL REQUIREMENTS

TEMPERATURE RATING: 200°C

Maximum continuous conductor temperature

VOLTAGE RATING: 600 volts (rms) at sea level

INSULATION FLAWS:

Spark Test, 5.7 kV (rms) at 3 kHz

Impulse Dielectric Test, 8.0 kV (peak)

PART NUMBER:

The "*" in the part numbers above shall be replaced by color code designators with a slash separating the component wire colors.

1/ Example: AWG 22, black and brown component wires:
55A0122-22-0/1

NOTE: Nominal values are for information only.
Nominal values are not requirements.

Users should evaluate the suitability of this product for their application. Specifications are subject to change without notice.
Tyco Electronics Corporation also reserves the right to make changes in materials or processing, which do not affect compliance with any specification, without notification to Buyer.

1/ COLORS AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681. HOWEVER, DUE TO LENGTH LIMITATIONS OF THE RAYCHEM PART NUMBER, AN ALTERNATIVE COLOR CODE MAY REPLACE MIL-STD-681 COLOR CODE DESIGNATORS. (EXAMPLE: "901/902..." MAY BE REPLACED BY "Axxx".) OTHER CODES AND SUFFIXES MAY BE ADDED TO THE PART NUMBER AS NECESSARY, TO CAPTURE ANY ADDITIONAL REQUIREMENTS IMPOSED BY THE PURCHASE ORDER.