

PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION

**Part Number:** [76460-4020](#)  
**Status:** **Active**  
**Overview:** [Impact™ Backplane Connectors and Cable Assemblies](#)  
**Description:** Impact™ 100 Ohm 2 Pair Right Angle Daughtercard Receptacle, 1.90 by 1.35mm Pitch, Right Guided, 10 Columns, 60 Circuits, Plated Through Hole Dimension 0.39mm, Tin (Sn) Lead (Pb)

**Documents:**  
[3D Model](#)  
[Drawing \(PDF\)](#)  
[Product Specification PS-76060-999 \(PDF\)](#)  
[Application Specification AS-76060-990 \(PDF\)](#)  
[RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

UL E29179

**General**

Product Family Backplane Connectors  
Series [76460](#)  
Application Coplanar, Daughtercard  
Application Tooling Documents TM-622018799  
Component Type PCB Receptacle  
Overview [Impact™ Backplane Connectors and Cable Assemblies](#)  
Product Name Impact™  
Style N/A  
UPC 883906850371

**Physical**

Circuits (Loaded) 60  
Circuits (maximum) 60  
Color - Resin Black  
Durability (mating cycles max) 200  
First Mate / Last Break No  
Flammability 94V-0  
Guide to Mating Part Yes  
Keying to Mating Part None  
Material - Metal High Performance Alloy (HPA)  
Material - Plating Mating Gold  
Material - Plating Termination Tin-Lead  
Material - Resin High Temperature Thermoplastic  
Net Weight 11.137/g  
Number of Columns 10  
Number of Pairs 2  
Number of Rows 6  
Orientation Right Angle  
PC Tail Length 1.20mm  
PCB Locator No  
PCB Retention Yes  
PCB Thickness - Recommended 1.00mm  
Packaging Type Tray  
Pitch - Mating Interface 1.90mm  
Pitch - Termination Interface 1.90mm  
Plating min - Mating 0.762µm  
Polarized to PCB Yes  
Stackable Yes  
Temperature Range - Operating -55°C to +85°C  
Termination Interface: Style Through Hole - Compliant Pin




image - Reference only

Series

**EU RoHS**  
**RoHS Compliant by Exemption**  
**REACH SVHC**  
**Contains SVHC: No**  
**Low-Halogen Status**  
**Low-Halogen**

**China RoHS**

Pb

**Need more information on product environmental compliance?**  
Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
For a multiple part number RoHS Certificate of Compliance, [click here](#)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**  
[76460Series](#)

**Mates With**  
76455 Impact™ 100 Ohm Vertical Backplane Header, 76450 Impact™ 100 Ohm Right Angle Male Header

**Application Tooling | FAQ**  
*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

| Description                                   | Product #                  |
|-----------------------------------------------|----------------------------|
| Press-in-Tool for Daughtercard                | <a href="#">0622018778</a> |
| Signal Module, 2-Pair by 10-Column Assemblies |                            |
| Impact Daughtercard Extraction Tool           | <a href="#">0622024300</a> |

**Electrical**

|                               |                 |
|-------------------------------|-----------------|
| Current - Maximum per Contact | 0.75A           |
| Data Rate                     | 25.0 Gbps       |
| Impedance                     | 100#            |
| Shield Type                   | N/A             |
| Shielded                      | No              |
| Voltage - Maximum             | 30V AC (RMS)/DC |

**Material Info**

**Reference - Drawing Numbers**

|                           |              |
|---------------------------|--------------|
| Application Specification | AS-76060-990 |
| Product Specification     | PS-76060-999 |
| Sales Drawing             | SD-76460-004 |

This document was generated on 12/03/2012

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**