

10

9

8

7

6

5

4

3

2

1

F

E

D

C

B

A

SEE CHART

SDA-90122

DIM C

(±0.20)
±.008

(6.75)
.266

DIM D

(±0.25)
±.010

(2.90)
.114

CIRCUIT SIZE

2 X 1

2 X 2

2 X 3

2 X 4

2 X 5

2 X 6

2 X 7

2 X 8

2 X 9

2 X 10

2 X 11

2 X 12

2 X 13

2 X 14

2 X 15

2 X 16

2 X 17

2 X 18

2 X 19

2 X 20

2 X 21

2 X 22

2 X 23

2 X 24

2 X 25

2 X 26

2 X 27

2 X 28

2 X 29

2 X 30

2 X 31

2 X 32

2 X 33

2 X 34

2 X 35

2 X 36

2 X 37

2 X 38

2 X 39

2 X 40

PLATING TYPE A

PART NO.

90122-0121

↑

-0122

↑

-0123

↑

-0124

↑

-0125

↑

-0126

↑

-0127

↑

-0128

↑

-0129

↑

-0130

↑

-0131

↑

-0132

↑

-0133

↑

-0134

↑

-0135

↑

-0136

↑

-0137

↑

-0138

↑

-0139

↑

-0140

↑

-0141

↑

-0142

↑

-0143

↑

-0144

↑

-0145

↑

-0146

↑

-0147

↑

-0148

↑

-0149

↑

-0150

↑

-0151

↑

-0152

↑

-0153

↑

-0154

↑

-0155

↑

-0156

↑

-0157

↑

-0158

↑

-0159

↓

90122-0160

PLATING TYPE E

PART NO.

90122-0761

↑

-0762

↑

-0763

↑

-0764

↑

-0765

↑

-0766

↑

-0767

↑

-0768

↑

-0769

↑

-0770

↑

-0771

↑

-0772

↑

-0773

↑

-0774

↑

-0775

↑

-0776

↑

-0777

↑

-0778

↑

-0779

↑

-0780

↑

-0781

↑

-0782

↑

-0783

↑

-0784

↑

-0785

↑

-0786

↑

-0787

↑

-0788

↑

-0789

↑

-0790

↑

-0791

↑

-0792

↑

-0793

↑

-0794

↑

-0795

↑

-0796

↑

-0797

↑

-0798

↑

-0799

↓

90122-0800

PLATING TYPE F

PART NO.

90122-0921

↑

-0922

↑

-0923

↑

-0924

↑

-0925

↑

-0926

↑

-0927

↑

-0928

↑

-0929

↑

-0930

↑

-0931

↑

-0932

↑

-0933

↑

-0934

↑

-0935

↑

-0936

↑

-0937

↑

-0938

↑

-0939

↑

-0940

↑

-0941

↑

-0942

↑

-0943

↑

-0944

↑

-0945

↑

-0946

↑

-0947

↑

-0948

↑

-0949

↑

-0950

↑

-0951

↑

-0952

↑

-0953

↑

-0954

↑

-0955

↑

-0956

↑

-0957

↑

-0958

↑

-0959

↓

90122-0960

NOTES:
FOR PLATING VARIATIONS SEE
ENG.STD. SDES-99000-0003.

STANDARD PRODUCTS

FOR PREVIOUS
DRAWING ISSUES
SEE MRI.

SEE SHEET I.

LTR

DIMENSIONS SHOWN (METRIC) INCH
UNLESS OTHERWISE SPECIFIED
TOLERANCES: ANGULAR ± 1°
INCH (METRIC)
3 PLACE ± . ---
2 PLACE ± . --- ± ---
1 PLACE ± ---
DRAFT WHERE APPLICABLE MUST
REMAIN WITHIN DIMENSIONS
DESIGN DIMENSION (PRIMARY) ☒ (MM) ☐ IN.
EQUIVALENT DIMENSION (SECONDARY) ☐ (MM) ☒ IN.

DRWG BY DB

CHK'D BY

APP'D BY

SCALE

REVISE ONLY ON CAD SYSTEM

SHL REV.

CAD/CAM FILENAME
SA90122X2
DGN

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO
MOLEX INC. & SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

TITLE
C-GRID III
DUAL ROW RIGHT
ANGLE HEADER

MOLEX

MOLEX EUROPE

SHEET NO. DATE
20F 16/ 7/87

PART NO.
SEE CHART

DWG NO.
SDA-90122

SIZE
B

7132-1283

10

9

8

7

6

5

4

3

2

1