

SOT23 NPN SILICON PLANAR MEDIUM POWER DARLINGTON TRANSISTOR


FMMT614

ISSUE 3 – APRIL 1996

FEATURES

- * h_{FE} up to 5k at $I_c = 500\text{mA}$
- * Fast switching
- * Low $V_{CE(sat)}$ at High I_c

PARTMARKING DETAILS – 614



ABSOLUTE MAXIMUM RATINGS.

PARAMETER	SYMBOL	VALUE	UNIT
Collector-Base Voltage	V_{CBO}	120	V
Collector-Emitter Voltage	V_{CEO}	100	V
Emitter-Base Voltage	V_{EBO}	10	V
Peak Pulse Current	I_{CM}	2	A
Continuous Collector Current	I_C	500	mA
Power Dissipation at $T_{amb}=25^{\circ}\text{C}$	P_{tot}	500	mW
Operating and Storage Temperature Range	$T_j; T_{stg}$	-55 to +150	$^{\circ}\text{C}$

ELECTRICAL CHARACTERISTICS (at $T_{amb} = 25^{\circ}\text{C}$).

PARAMETER	SYMBOL	MIN.	TYP.	MAX.	UNIT	CONDITIONS.
Collector-Base Breakdown Voltage	$V_{(BR)CBO}$	120	300		V	$I_C=10\mu\text{A}$, $I_E=0$
Collector-Emitter Sustaining Voltage	$V_{CEO(sus)}$	100	130		V	$I_C=10\text{mA}$, $I_B=0^*$
Emitter-Base Breakdown Voltage	$V_{(BR)EBO}$	10	14		V	$I_E=10\mu\text{A}$, $I_C=0$
Collector Cut-Off Current	I_{CBO}		0.02	10	nA	$V_{CB}=100\text{V}$, $I_E=0$
Collector Cut-Off Current	I_{CES}			10	μA	$V_{CES}=100\text{V}$, $I_E=0$
Emitter Cut-Off Current	I_{EBO}			100	nA	$V_{EB}=8\text{V}$, $I_C=0$
Collector-Emitter Saturation Voltage	$V_{CE(sat)}$		0.9 0.78	1.0 0.9	V V	$I_C=500\text{mA}$, $I_B=5\text{mA}^*$ $I_C=100\text{mA}$, $I_B=0.1\text{mA}$
Base-Emitter Saturation Voltage	$V_{BE(sat)}$		1.7	1.9	V	$I_C=500\text{mA}$, $I_B=5\text{mA}^*$
Base-Emitter Turn-On Voltage	$V_{BE(on)}$		1.5	1.8	V	$I_C=500\text{mA}$, $V_{CE}=5\text{V}^*$
Static Forward Current Transfer Ratio	h_{FE}	15K 5K				$I_C=100\text{mA}$, $V_{CE}=5\text{V}^*$ $I_C=500\text{mA}$, $V_{CE}=5\text{V}^*$
Output Capacitance	C_{obo}		6		pF	$V_{CB}=10\text{V}$, $f=100\text{MHz}$
Switching Times	t_{on}		0.7		μs	$I_C=100\mu\text{A}$, $I_B=0.1\text{mA}$
	t_{off}		2.5		μs	$V_S=10\text{V}$

*Measured under pulsed conditions. Pulse Width=300 μs . Duty cycle $\leq 2\%$

Spice parameter data is available upon request for this device

Typical Characteristics graphs are in preparation. Contact your local Sales office for more information.

FMMT614

TYPICAL CHARACTERISTICS

