



IWLAN ACCESS POINT, SCALANCE W786-1 RJ45, ONLY FOR USE IN USA, 1 RADIO, 3 R-SMA ANT.CONNECT., IEEE 802.11A/B/G/H/N, 2.4/5GHZ, BRUTTO 450 MBIT/S PRO RADIO, 1 X RJ45 (MAX. 1 GBIT/S), POE, 24VDC, IP65 (-40-+60 DGR C), POE, WPA2/802.11I/E, PLEASE NOTE NATIONAL APPROVALS! SCOPE OF SUPPLY: MANUALS ON CD ROM GERMAN/ENGLISH, 1 X TERMINAL BLOCK.

### Transmission rate

#### Transfer rate

• with WLAN / maximum	450 Mbit/s
• 1 / for Industrial Ethernet	10 Mbit/s
• 2 / for Industrial Ethernet	100 Mbit/s
• 3 / for Industrial Ethernet	1000 Mbit/s
• for Industrial Ethernet	10 Mbit/s, 1000 Mbit/s

### Interfaces

#### Number of electrical connections

• for network components or terminal equipment	1
• for power supply	1
• for redundant voltage supply	1

#### Type of electrical connection

• for network components or terminal equipment	RJ45 socket
• for power supply	2-pole connector (24 V DC) or optionally available power supply adapter (4-pole 24 V DC or 3-pole 110 to 230 V AC)

#### design of the removable storage

• C-PLUG	Yes
• KEY-PLUG	Yes

### Interfaces / wireless

#### Number of radio cards / permanently installed

1

#### Transmission mode / for multiple input multiple output (MIMO)

3x3

#### Number of spatial streams

3

Number of electrical connections / for external antenna(s)	3
Type of electrical connection / for external antenna(s)	R-SMA (socket)
Product property / external antenna can be mounted directly on device	No

Supply voltage, current consumption, power loss	
Type of voltage / of the supply voltage	DC
Supply voltage / 1	
• from terminal block	19.2 V
Supply voltage / 2	
• from terminal block	28.8 V
Supply voltage	
• from Power-over-Ethernet acc. to IEEE802.3at for type 1 and IEEE802.3af	48 V
• from Power-over-Ethernet acc. to IEEE802.3at for type 2	50 V
• from optional integrable power supply	
— with AC	100 ... 240 V
— for DC	12 ... 24 V
Consumed current	
• for DC / at 24 V / typical	0.45 A
• with AC / at 230 V / typical	0.05 A
• with Power-over-Ethernet according to IEEE802.3at for type 1 and IEEE802.3af / typical	0.22 A
Active power loss	
• for DC / at 24 V / typical	10.7 W
• with AC / at 230 V / typical	10.7 W
• with Power-over-Ethernet according to IEEE802.3at for type 1 and IEEE802.3af / typical	10.7 W

Permitted ambient conditions	
Ambient temperature	
• during operation	-40 ... +60 °C
• during storage	-40 ... +85 °C
• during transport	-40 ... +85 °C
Relative humidity / at 25 °C / without condensation / during operation / maximum	100 %
Ambient condition / for operation	When using the power supply 100 to 240 V AC, an operating temperature of -40 °C to +60 °C is permissible
Protection class IP	IP65

Design, dimensions and weight	
Width / of the enclosure / without antenna	251 mm
Height / of the enclosure / without antenna	251 mm

Depth / of the enclosure / without antenna	72 mm
Net weight	2.24 kg
Mounting type	For mast mounting, 35 mm DIN rail mounting and S7-300 rail mounting, an additional support plate is required
• S7-1500 rail mounting	No
• wall mounting	Yes
<b>Wireless frequencies</b>	
Operating frequency	
• for WLAN in 2.4 GHz frequency band	2.41 ... 2.48 GHz
• for WLAN in 5 GHz frequency band	4.9 ... 5.8 GHz
<b>Product properties, functions, components / general</b>	
Product function / Access Point Mode	Yes
Product function / Client Mode	Yes
Number of SSIDs	8
Product function	
• Dual Client	No
• iPCF Access Point	Yes; Only in combination with the 'KEY-PLUG W780 iFeatures'
• iPCF client	Yes; Only in combination with the 'KEY-PLUG W780 iFeatures' or 'KEY-PLUG W740 iFeatures'
• iPCF-MC Access Point	No
• iPCF-MC client	Yes; Only in combination with 'KEY-PLUG W780 iFeatures' or 'KEY-PLUG W740 iFeatures'
Number of iPCF-capable radio modules	1
Product function / iREF	Yes; In combination only with 'KEY-PLUG W780 iFeatures'
Number of iREF-capable radio modules	1
<b>Product functions / management, configuration</b>	
Number of manageable IP addresses / in client	8
Product function	
• CLI	Yes
• web-based management	Yes
• MIB support	Yes
• TRAPs via email	Yes
• Configuration with STEP 7	No
• configuration with STEP 7 in the TIA Portal	No
• operation with IWLAN controller	No
• operation with Enterasys WLAN controller	No
• forced roaming with IWLAN	Yes
• WDS	Yes
Protocol / is supported	
• Address Resolution Protocol (ARP)	Yes
• ICMP	Yes

• Telnet	Yes
• HTTP	Yes
• HTTPS	Yes
• TFTP	Yes
• DCP	Yes
• LLDP	Yes
Identification & maintenance function	
• I&M0 - device-specific information	Yes
• I&M1 – higher-level designation/location designation	Yes
<b>Product functions / Diagnosis</b>	
Product function	
• PROFINET IO diagnosis	No
• Link Check	No
• connection monitoring IP-Alive	No
• localization via Aeroscout	No
• SysLog	Yes
Protocol / is supported	
• SNMP v1	Yes
• SNMP v2	Yes
• SNMP v3	Yes
<b>Product functions / VLAN</b>	
Product function	
• function VLAN with WLAN	Yes
<b>Product functions / DHCP</b>	
Product function	
• DHCP client	Yes
• in Client Mode / DHCP server via LAN	No
<b>Product functions / Redundancy</b>	
Protocol / is supported	
• STP/RSTP	Yes
<b>Product functions / Security</b>	
Product function	
• Management security, ACL-IP based	Yes
• IEEE 802.1x (radius)	Yes
• NAT/NAPT	No
• access protection according to IEEE802.11i	Yes
• WPA/WPA2	Yes
• TKIP/AES	Yes
Protocol / is supported	

• SSH	Yes
<b>Product functions / Time</b>	
Protocol / is supported	
• SNTP	Yes
• SIMATIC Time	Yes
<b>Standards, specifications, approvals</b>	
Standard	
• for FM	FM 3611: Class I, Division 2, Groups A,B,C,D, T4 / Class 1, Zone 2, Group IIC, T4
• for hazardous zone	EN 60079-15:2005, EN 60079-0:2006, II 3 G Ex nA II T4 KEMA 07 ATEX 0145X
• for safety / from CSA and UL	UL 60950-1 CSA C22.2 No. 60950-1
• for hazardous zone / from CSA and UL	ANSI/ISA 12.12.01-2013, CAN/CSA C22.2 No.213-M1987, CL. 1, Div. 2, GP. A,B,C,D, T4 / CL. 1, Zone 2, GP IIC
Certificate of suitability	
• EC declaration of conformity	Yes
• CE marking	Yes
• C-Tick	Yes
• CCC	No
• E1 approval	Yes
• Railway application in accordance with EN 50155	No
• Fire protection in accordance with EN 45545-2	No
• NEMA TS2	No
• IEC 61375	No
• IEC 61850-3	No
• NEMA4X	Yes
• Power-over-Ethernet according IEEE802.3at for type 1 and IEEE802.3af	Yes
• Power-over-Ethernet according to IEEE802.3at for type 2	Yes
Standard for wireless communication	
• IEEE 802.11a	Yes
• IEEE 802.11b	Yes
• IEEE 802.11e	Yes
• IEEE 802.11g	Yes
• IEEE 802.11h	Yes
• IEEE 802.11i	Yes
• IEEE 802.11n	Yes
Wireless approval	For operation in the USA, you can find more detailed information at: <a href="http://www.siemens.com/simatic-net/ik-info">www.siemens.com/simatic-net/ik-info</a>
Marine classification association	

• American Bureau of Shipping Europe Ltd. (ABS)	No
• Bureau Veritas (BV)	No
• Det Norske Veritas (DNV)	No
• Germanische Lloyd (GL)	No
• Lloyds Register of Shipping (LRS)	No
• Nippon Kaiji Kyokai (NK)	No
• Polski Rejestr Statkow (PRS)	No

## Accessories

accessories	24 V DC screw terminal included in scope of delivery
-------------	--

## Further Information / Internet Links

### Internet-Link

• to website: TIA Selection Tool	<a href="http://www.siemens.com/tia-selection-tool">http://www.siemens.com/tia-selection-tool</a>
• to the website: IWLAN	<a href="http://www.siemens.com/iwlan">http://www.siemens.com/iwlan</a>
• to website: Industry Mall	<a href="https://mall.industry.siemens.com">https://mall.industry.siemens.com</a>
• to website: Information and Download Center	<a href="http://www.siemens.com/automation/net/catalog">http://www.siemens.com/automation/net/catalog</a>
• to website: Image database	<a href="http://automation.siemens.com/bilddb">http://automation.siemens.com/bilddb</a>
• to website: CAx Download Manager	<a href="http://www.siemens.com/cax">http://www.siemens.com/cax</a>
• to website: Industry Online Support	<a href="https://support.industry.siemens.com">https://support.industry.siemens.com</a>

## Security information

### Security information

Siemens provides products and solutions with industrial security functions that support the secure operation of plants, solutions, machines, equipment and/or networks. They are important components in a holistic industrial security concept. With this in mind, Siemens' products and solutions undergo continuous development. Siemens recommends strongly that you regularly check for product updates. For the secure operation of Siemens products and solutions, it is necessary to take suitable preventive action(e.g. cell protection concept) and integrate each component into a holistic, state-of-the-art industrial security concept. Third-party products that may be in use should also be considered. For more information about industrial security, visit <http://www.siemens.com/industrialsecurity>. To stay informed about product updates as they occur, sign up for a product-specific newsletter. For more information, visit <http://support.automation.siemens.com>. (V3.4)

last modified:

09.03.2015