






LOC		DIST		P		F		ZONE		LTR		REVISIONS		DATE		APPD	
EY	24											A	REV; EC 0230-0194-94	6/13/95	BHS	LR	

1. DIMENSIONS ARE MAXIMUM UNLESS OTHERWISE SPECIFIED.
2. EACH WIRE ENTRY HOLE ACCEPTS ONE UNSTRIPPED DROP-WIRE CONDUCTOR: EITHER A SINGLE 18-1/2 AWG COPPER-STEEL 4.572 [1.180] OUTSIDE INSULATION MAXIMUM DIAMETER OR A SINGLE 22 - 24 AWG SOLID COPPER 0.762 [0.030] OUTSIDE INSULATION MINIMUM DIAMETER. DROP-WIRES WITH CONDUCTORS OTHER THAN THESE SHALL BE SUBMITTED TO AMP PRODUCT ENGINEERS FOR APPLICATION APPROVAL.
3. EACH WIRE SHALL BE INSERTED TO THE FOLLOWING DEPTHS: 18 1/2 AWG - 11.68 [4.6] MAX, 7.62 [0.30] MIN. 22 - 24 AWG - 18.80 [0.74] MAX, 15.75 [0.62] MIN.
4. TERMINATION IS ACCOMPLISHED BY FIRST INSERTING ONE WIRE INTO EACH HOLE DESIRED THEN ROTATING THE LUG 70° CW.
5. YELLOW STRIPES ON LUG AND MODULE WILL BE ALIGNED WHEN IN CLOSED POSITION. STRIPES MUST BE FULLY ALIGNED TO COMPLETE TERMINATION.
6. FOR WIRING EASE, PRESS WIRES DOWN THROUGH 3 HOLE GROMMET AFTER TERMINATION.



775259-1												PART NO	
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± 3 PLC DEC ± ANGLES ±												AMP AMP Incorporated Harrisburg, PA 17105-3608	
DR 9-22-94 T. WOOTEN												NAME	
CHK 10-14-94 D. HUSSEY												CROSS CONNECT ASSEMBLY, WALL MOUNTED, PROTECTED, QUIET FRONT	
APPD 10-14-94 T. PIZZULO												SIZE	
APPD 10-14-94 R. GUZMAN												CAGE CODE	
PRODUCT SPEC 108-30300												DRAWING NO	
FINISH												SCALE	
APPLICATION SPEC												1:1	
WEIGHT												SHEET	
1 OF 1												CUSTOMER DRAWING	

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.