






P.C. BOARD LAYOUT FOR 4 PIN 74626-X11XB

NOTES:

1. MATERIAL:
CONTACTS: COPPY ALLOY
SHELL: COPPY ALLOY
HOUSING: UL 94V-0 RATED THERMOPLASTIC
2. PLATING:
SEE PRODUCT NUMBER CODE
3. DATUM AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER
4. RECOMMENDED PC BOARD THICKNESS OF 1.57mm
5. 2.67mm MAXIMUM PANEL THICKNESS IF MOUNTED BEHIND PANEL
6. CONTACT PLATING CODE OPTION 1 DOES NOT MEET THE PLATING SPECIFIED PER UNIVERSAL SERIAL BUS SPECIFICATION REVISION 1.0
7. MAXIMUM PANEL THICKNESS TO BE 2.67mm IF MOUNED BEHIND PANEL.
8. TORQUE SPEC 2.0kgf-cm MAX.



rev	ecn no	dr	date
M	N05-0103	PH	04/06/05
N	N06-0298	HB	11/29/06
P	N08-0031	R.B	2008/02/27
R	N08-0238	R.B	2008/11/03
S	ELX-N15753	R.B	2013/09/05
-	-	-	-

www.fciconnect.com

FCI

RECEIPTABLE SMT

Dr	PETER	7/8/98	surface	tolerance	std	projection	MM
Eng	R Y LIU	7/8/98	ANGULAR	0.X	±0.3	size	A4
Chr	R Y LIU	7/8/98	LINEAR	0.XX	±0.2	Scale	1:1
Appr	JENN TSAO	7/8/98	Product family	0.XXX	±	ECN	ELX-N15753
						Spec ref	
						Customer	74626
						Rev.	S




REV F - 2004-04-17

catalog no

customer

sheet 1 of 3





P.C. BOARD LAYOUT FOR 5 PIN 74626-X01XB

www.fciconnect.com		surface 		tolerance std		projection 		MM 	
		TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	PETER	7/8/98	ANGULAR	0.X	±0.3	size	A4	Scale	1:1
Eng	R Y LIU	7/8/98	LINEAR	0.XX	±0.2				
Chr	R Y LIU	7/8/98	0° ±5°	0.XXX	±	ECN EX-MH5753			
Appr	JENN TSAO	7/8/98	Product family		Spec ref				
				USB REVERSED					
		RECEPTACLE SMT		dwg no		74626		Rev. S	
catalog no				CUSTOMER				sheet 2 of 3	

1

2

3

4

PRODUCT NUMBER CODE

A
74626 - X X X X P LF

BASE PRODUCT NUMBER

HOUSING COLOR OPTIONS

- 0 - WHITE
1 - BLACK
2 - WHITE + SHELL NICKEL PLATING ONLY
- SENSOR CONTACT OPTION

- 0 - WITH SENSOR CONTACT
1 - WITHOUT SENSOR CONTACT

SHELL OPTIONS

- 1 - WITHOUT BACK SHIELD
3 - WITHOUT BACK SHIELD & NICKEL PLATING ONLY
S - WITHOUT BACK SHIELD & NICKEL PLATING ONLY
(SPECIAL MATERIAL FOR DURABILITY 12,000 CYCLES)
- TERMINAL PLATING OPTION

- 0 - 1.25um Ni UNDERPLATE
0.76um GXT CONTACT AREA
2.50 um TIN/LEAD TAIL AREA

PACKAGING OPTION

- B - TUBES
R - TAPE & REEL


DATE CODE

LEAD FREE




Copyright FCI.

D



STYLE 1



STYLE 2

NOTES:

1. P/N'S WITH SUFFIX "LF" ARE LEAD FREE P/N'S
2. PACKING STANDARD GS-14-920 WILL BE APPLIED FOR LEAD FREE P/N'S
3. FOR LEAD FREE P/N, THE PRODUCT MEET EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATION AS DESCRIBED IN GS-22-008
4. FOR LEAD FREE P/N, THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 40 SECONDS IN A CONVECTION, INFRARED OR VAPOR PHASE REFLOW OVEN.
5. AVAILABLE P/N'S NOW IN FCI ARE

PART NUMBER	STYLE
74626-010XXLF	STYLE 1
74626-1010XXLF	STYLE 1
74626-0110XXLF	STYLE 1
74626-1130XXLF	STYLE 1
74626-2010XXLF	STYLE 2
74626-2110XXLF	STYLE 2
74626-1110XXLF	STYLE 1
74626-01S0XPLF	STYLE 2
74626-11S0XPLF	STYLE 2

www.fciconnect.com		surface		tolerance std		projection		MM	
		✓							
TOLERANCES UNLESS OTHERWISE SPECIFIED									
Dr	PETER	7/8/98	ANGULAR	0.X	±0.3	size	A4	Scale	1:1
Eng	R Y LIU	7/8/98	LINEAR	0.XX	±0.2	ECN	ELX-N15753		
Chr	R Y LIU	7/8/98	0° ±5°	0.XXX	±	Spec ref			
Appr	JENN TSAO	7/8/98	Product family						
USB REVERSED		RECEPTACLE SMT		74626		Rev.		S	
catalog no		CUSTOMER		sheet 3 of 3					



1

2

3

4