




All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

Tous droits strictement réservés. Reproduction ou communication à des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.

PRODUCT NUMBER
51416-00X---
NOTE ③



THIS FILE WAS ORIGINALLY CREATED IN THE PRO ENGINEER ENVIRONMENT AND ANY FUTURE REVISIONS TO THIS FILE MUST BE MADE IN THE PRO ENGINEER ENVIRONMENT

mat'l code				SEE NOTES		tolerances unless otherwise specified		CUSTOMER		FCI	
ltr	ecr no.	dr	date					COPY		www.fciconnect.com	
A	V90563	CHB	02-18-99	linear		.XX $\pm$.01 / .X $\pm$.3		projection		title IP + 24S + 1P RIGHT ANGLE SOLDER RECEPT	
B	V90919	SAR	04-14-99			.XXX $\pm$.005 / .XX $\pm$.13				product family PwrBlade	
C	V94029	CHB	10-08-99	angles		.XXX $\pm$.0020 / .XXX $\pm$.051				code 213	
D	V01376	EKK	06-08-00	dr	LEVEL 4	01-12-99				size dwg no 51416	
E	DG05-0049	SW	03-17-05	enrg	J. BROWN	01-12-99				sheet 1 of 5	
F	DG05-0230	LH	07-19-05	chr	J. BROWN	01-12-99					
G	DG08-0239	JC	09/12/08	appd	J. BROWN	01-12-99					
sheet index		revision sheet		G	G	G	G	G	G		
				1	2	3	4	5			

Pro/E



cage code 22526




All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

Tous droits strictement réservés. Reproduction ou communication à des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.

PRODUCT NUMBER
51416-00X
NOTE (3)



SECTION P-P



SECTION X-X

mat'l code				SEE NOTES		tolerances unless otherwise specified		CUSTOMER		FCI	
litr	ecn no.	dr	date	linear		.XX ± .01 / .X ± .3		COPY		www.fciconnect.com	
G						.XXX ± .005 / .XX ± .13		projection		title	
						.XXX ± .0020 / .XXX ± .051				IP + 24S + 1P RIGHT ANGLE SOLDER RECEPT	
				angles		0° ± 2°		INCH/MM		product family	PwrBlade
				dr	LEVEL 4	01-12-99		scale		size	dwg no
				enr	J. BROWN	01-12-99		3:2		A	51416-001
				chr	J. BROWN	01-12-99					sheet
				appd	J. BROWN	01-12-99					2
sheet index	revision sheet										

Pro/E

cage code 22526




All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

Tous droits strictement réservés. Reproduction ou communication à des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.

B

A

PRODUCT NUMBER
51416-00X--
NOTE ③



RECOMMENDED PCB LAYOUT

mat'l code				SEE NOTES				tolerances unless otherwise specified				CUSTOMER COPY				 www.fciconnect.com			
ltr	ecn no.	dr	date	linear	.XX ±.01/.X ±.3				projection		title IP + 24S + IP RIGHT ANGLE SOLDER RECEPT								
G					.XXX ±.005/.XX ±.13														
					.XXXX ±.0020/.XXX ±.051														
					angles	0° ± 2°													
				dr	LEVEL 4		01-12-99		INCH/MM 	product family				PwrBlade		code			
				enrg	J. BROWN		01-12-99			size				dwg no		213			
				chr	J. BROWN		01-12-99			scale 3:2				A 51416					
				appd	J. BROWN		01-12-99												
sheet index		revision sheet																	

B

1 | 2

Pro/E

3 |

cage code 22526

4




All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

Tous droits strictement réservés. Reproduction ou communication à des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.


A

B

ITEM NO.	QTY	DIM "M" MATING LENGTH ±.010		DIM "T" TAIL LENGTH +.005- [.13]-.010 [.25]		CONTACT TYPE
PB	2	0.042	[1.07]	0.090	[2.29]	POWER
J	6	N/A	[N/A]	0.090	[2.29]	SIGNAL
K	6	N/A	[N/A]	0.090	[2.29]	SIGNAL
L	6	N/A	[N/A]	0.090	[2.29]	SIGNAL
M	6	N/A	[N/A]	0.090	[2.29]	SIGNAL
HA	2	N/A	[N/A]	N/A	[N/A]	HOLD-DOWN



ITEM NO.	QTY	DIM "M" MATING LENGTH ±.010 [.25]		DIM "T" TAIL LENGTH ±.010 [.25]		CONTACT TYPE
PA	2	0.042	[1.07]	0.135	[3.43]	POWER
E	6	N/A	[N/A]	0.135	[3.43]	SIGNAL
F	6	N/A	[N/A]	0.135	[3.43]	SIGNAL
G	6	N/A	[N/A]	0.135	[3.43]	SIGNAL
H	6	N/A	[N/A]	0.135	[3.43]	SIGNAL
HA	2	N/A	[N/A]	N/A	[N/A]	HOLD-DOWN



mat'l code				SEE NOTES		tolerances unless otherwise specified		CUSTOMER COPY		www.fciconnect.com	
ltr	ecr no.	dr	date	linear	.XX ±.01/.X ±.3		projection		title IP + 24S + 1P RIGHT ANGLE SOLDER RECEPT		
G					.XXX ±.005/.XX ±.13 .XXXX ±.0020/.XXX ±.051						
				angles	0° ± 2°		INCH/MM		product family		code
				dr	LEVEL 4	01-12-99	PwrBlade		213		
				enrg	J. BROWN	01-12-99	scale 1:1	A	size	dwg no	sheet
				chr	J. BROWN	01-12-99			51416	4	
				appd	J. BROWN	01-12-99					
sheet index	revision sheet										

A

B

1 | 2

3 |

4

1 | 2

Pro/E

3 |

cage code 22526

4



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor.
Property of FCI. Copyright FCI.

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire.
Propriete de c FCI. Droits de reproduction FCI.

A

B

PRODUCT NUMBER
51416-00X--- NOTE(3)

NOTES:

1. DIMENSIONS AND TOLERANCES ARE IN ACCORDANCE WITH
ASME Y14.5M, 1994 UNLESS OTHERWISE SPECIFIED.

CONNECTOR NOTES:

2. HOUSING MATERIAL: UL 94 V-0 GLASS FILLED
HIGH-TEMP THERMOPLASTIC
POWER CONTACT MATERIAL: COPPER ALLOY
SIGNAL PIN MATERIAL: COPPER ALLOY
3. PLATING(51416-00X STAND FOR 51416-001 AND 51416-002)

△ SEE ITEM 5 & 6 IN PRINT 10064183 FOR PLATING SPEC OF 51416-00X
AND 51416-00XLF RESPECTIVELY

4. MANUFACTURER'S NAME, P/N, AND DATE CODE TO APPEAR ON THIS SURFACE.

5. PRODUCT SPECIFICATION GS-12-149.
APPLICATION SPECIFICATION BUS-20-067.

PCB NOTES:

6. ALL HOLE DIAMETERS ARE FINISHED HOLE SIZE.
7. MOUNTING HOLES, WHERE APPLICABLE, ARE UNPLATED.
8. $\varnothing.0453\pm0.0010$ [1.151 ± 0.025] DRILLED HOLES PLATED WITH
.0003 [0.008] MIN SnPb OVER .001 [0.03]
TO .003 [0.08] Cu PLATING TO ACHIEVE
 $\varnothing.040\pm.003$ [$1.02\pm.07$] HOLE.
9. "DIM XXX" TO BE DETERMINED BY THE CUSTOMER.
10. CONNECTOR KEEP-OUT ZONE.
11. A △ SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW, OR NOTE
WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION.

THIS FILE WAS ORIGINALLY CREATED IN THE PRO
ENGINEER ENVIRONMENT AND ANY FUTURE REVISIONS TO
THIS FILE MUST BE MADE IN THE PRO ENGINEER
ENVIRONMENT

mat'l code				SEE NOTES		tolerances unless otherwise specified		CUSTOMER		www.fciconnect.com	
ltr	ecr no.	dr	date	linear		.XX±.01/0.X±0.3		COPY		title IP + 24S + 1P RIGHT ANGLE SOLDER RECEPT	
G						.XXX±.005/0.XX±0.13		projection			
						.XXX±.0020/0.XXX±0.051					
				angles		0°±2°		INCH/MM		product family PwrBlade code	
				dr		LEVEL 4 01-12-99		scale 3:2		size	
				enrg		J. BROWN 01-12-99				dwg no	
				chr		J. BROWN 01-12-99				51416	
				appd		J. BROWN 01-12-99				213 sheet 5	
sheet index		revision sheet									

A

B

1 | 2

3 |

4

1 | 2

Pro/E

3 |

cage code 22526

4