


DWG. NO. 10-5263-1

PART MDSR-4

**ELECTRICAL RATINGS**

CONTACT FORM			A
CONTACT RATING		WATTS	10
RATING SENSITVITY	AMPERE TURNS		20
VOLTAGE	SWITCHING	VDC-MAX.	200
	BREAKDOWN	VDC-MIN	250
	ARC-QUENCH	VDC-MIN	200
CURRENT	SWITCHING	AMPERES-MAX.	0.5
	CARRY	AMPERES-MAX.	1.2
RESISTANCE	CONTACT, INITIAL	OHMS-MAX.	0.10
	INSULATION	OHMS-MIN.	10 10
CAPACITANCE		PICOFARADS-TYP.	0.2

MAGNETIC CHARACTERISTICS

TEST COIL		L4989
STANDARD TOLERANCE	AMPERE TURNS	12-23
PULL-IN RANGES		17-28
		22-33
		27-38
TIGHTENED TOLERANCE	AMPERE TURNS	12-18
PULL-IN RANGES		17-23
		22-28
		27-33
		32-38


OPERATING CHARACTERISTICS

OPERATE TIME		ms-MAX.	0.6
RELEASE TIME		ms-MAX.	0.2
SHOCK	G's MAX., 11ms 1/2 SINE WAVE		100
VIBRATION	G's MAX., 50-2000 HERTZ		30
RESONANT FREQUENCY		HERTZ, TYP.	3900
TEMPERATURE OPERATING	DEGREES, CELSIUS	-40 TO +125	
	STORAGE	DEGREES, CELSIUS	-65 TO +125

SEE REED SWITCH CATALOG FOR DEFINITION OF TERMS

DRAWING REVISIONS

REV. NO.	DATE	DCR NO.

DROP-OUT (DESIGN PARAMETER)

EXAMPLE:
17-33 AT PULL-IN
8-21 AT DROP-OUT

HAMLIN

1993

THIS DESIGN AND PRINT IS COPYRIGHT AND IS THE PROPERTY OF HAMLIN INC. IT MUST NOT BE COPIED OR PERMITTED TO BE COPIED. NOR MUST ITS CONTENTS BE DIVULGED TO ANY THIRD PARTY WITHOUT PRIOR WRITTEN PERMISSION FROM THE COMPANY.

SHEET 1 OF 1 SHEET(S)

DIM.: INCHES (mm)

DWG. NO. 10-5263-1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Hamlin:

[MDSR-4 17-23](#) [MDSR-4 22-28](#) [MDSR-4 27-38](#) [MDSR-4 12-38](#) [MDSR-4 22-33](#) [MDSR-4 17-28](#) [MDSR-4 17-38](#)
[MDSR-4 12-28](#)

Littelfuse:

[MDSR-4 12-18](#)