


M



THIRD ANGLE PROJECTION		
		
SCALE 3 : 1		
DO NOT SCALE PRINT		
UNLESS OTHERWISE SPECIFIED TOLERANCES ARE		
ONE PLACE	(.0)	±.030
TWO PLACES	(.00)	±.015
THREE PLACES	(.000)	±.005
ANGLES		±
WEIGHT		

											SOLDER PLATED TERMINALS	
"D" LEVER ACTUATION POINT	LEVER TYPE	"E" FREE POSITION (MAX)	"F" OPERATION POINT (MIN)	"G" RELEASE POINT (MAX)	OVER-TRAVEL (MIN)	DIFF TRAVEL (MIN)	FORCE AT OPERATE POINT		UNACTUATED OUTPUT VOLTAGE	OUTPUT TRANSISTOR 	CATALOG LISTING	
							OUNCES	GRAMS			STYLE 1 	STYLE 2 
.795	NONE	$\frac{16.38}{.645}$	$\frac{14.22}{.560}$	$\frac{15.54}{.612}$	$\frac{1.02}{.040}$	$\frac{0.05}{.002}$	$.35 \begin{smallmatrix} +.18 \\ -.14 \end{smallmatrix}$	$10 \begin{smallmatrix} +5 \\ -4 \end{smallmatrix}$	HIGH	OFF	VX10	VX12
									LOW	ON	VX11	VX13
							$3.0 \pm .88$	85 ± 25	HIGH	OFF	VX80	
									LOW	ON	VX81	
.860	A	$\frac{17.27}{.680}$	$\frac{14.71}{.579}$	$\frac{16.33}{.643}$	$\frac{1.02}{.040}$	$\frac{0.05}{.002}$	$.35 \pm .2$	10 ± 5	HIGH	OFF	VX10-A1	VX12-A1
									LOW	ON	VX11-A1	
							2.8 ± 1.1	80 ± 30	HIGH	OFF	VX80-A1	
									LOW	ON	VX81-A1	
1.400	A	$\frac{19.28}{.759}$	$\frac{13.94}{.549}$	$\frac{17.32}{.682}$	$\frac{2.16}{.085}$	$\frac{0.10}{.004}$	$0.2 \pm .1$	$5 \begin{smallmatrix} +3 \\ -2 \end{smallmatrix}$	HIGH	OFF	VX10-A2	
									LOW	ON		VX13-A2
							$1.41 \pm .50$	40 ± 15	HIGH	OFF	VX80-A2	VX82-A2
									LOW	ON	VX81-A2	
2.340	A	$\frac{22.58}{.889}$	$\frac{12.62}{.497}$	$\frac{18.97}{.747}$	$\frac{4.06}{.160}$	$\frac{0.20}{.008}$	$.10 \pm .07$	3 ± 2	HIGH	OFF	VX10-A3	VX12-A3
									LOW	ON	VX11-A3	VX13-A3
							$.75 \begin{smallmatrix} +.35 \\ -.25 \end{smallmatrix}$	$21 \begin{smallmatrix} +9 \\ -7 \end{smallmatrix}$	HIGH	OFF	VX80-A3	
									LOW	ON	VX81-A3	
1.285	B	$\frac{22.23}{.875}$	$\frac{17.02}{.670}$	$\frac{20.52}{.808}$	$\frac{1.91}{.075}$	$\frac{0.10}{.004}$	$0.20 \begin{smallmatrix} +.15 \\ -.10 \end{smallmatrix}$	$5 \begin{smallmatrix} +4 \\ -2 \end{smallmatrix}$	HIGH	OFF	VX10-B1	VX12-B1
									LOW	ON	VX11-B1	VX13-B1
							$1.55 \pm .53$	44 ± 15	HIGH	OFF	VX80-B1	
									LOW	ON		
.810	C	$\frac{22.48}{.885}$	$\frac{19.99}{.787}$	$\frac{21.62}{.851}$	$\frac{1.02}{.040}$	$\frac{0.05}{.002}$	$.40 \pm .20$	12 ± 5	HIGH	OFF	VX10-C1	VX12-C1
									LOW	ON	VX11-C1	VX13-C1
							3.0 ± 1.06	85 ± 30	HIGH	OFF	VX80-C1	
									LOW	ON	VX81-C1	
$\begin{smallmatrix} .795 \\ \triangle A \end{smallmatrix}$	A	$\frac{17.78}{.700}$	$\frac{14.73}{.580}$	$\frac{16.13}{.635}$	$\frac{1.02}{.040}$	$\frac{0.10}{.004}$	$.35 \begin{smallmatrix} +.18 \\ -.14 \end{smallmatrix}$	$10 \begin{smallmatrix} +5 \\ -4 \end{smallmatrix}$	LOW	ON	VX81-A2-GE	
1.226	F	$\frac{25.73}{1.013}$	$\frac{21.72}{.855}$	$\frac{23.98}{.944}$	$\frac{1.65}{.065}$	$\frac{0.13}{.005}$	$.35 \begin{smallmatrix} +.18 \\ -.14 \end{smallmatrix}$	$10 \begin{smallmatrix} +5 \\ -4 \end{smallmatrix}$	HIGH	OFF	VX10-F1 VX11-F1	
1.250	F	$\frac{25.58}{1.007}$	$\frac{21.72}{.855}$	$\frac{23.83}{.938}$	$\frac{1.65}{.065}$	$\frac{0.13}{.005}$	$.35 \begin{smallmatrix} +.18 \\ -.14 \end{smallmatrix}$	$10 \begin{smallmatrix} +5 \\ -4 \end{smallmatrix}$	HIGH	OFF	VX10-FA	

NOTE
A MEASUREMENTS TAKEN OVER PLUNGER



MASTER REDUCED
ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

MICRO SWITCH
a Honeywell Division

FED. MFG. CODE 81828


SWITCH - SOLID STATE

CATALOG LISTING

VX SERIES

CHART 1

THIRD ANGLE PROJECTION



SCALE	NONE
-------	------

DO NOT SCALE PRINT

UNLESS OTHERWISE SPECIFIED
TOLERANCES ARE

ONE PLACE (.0) $\pm .030$

TWO PLACES (.00) $\pm .015$

THREE PLACES (.000) $\pm .005$

ANGLES $\pm$

WEIGHT

FORMTEK
DRAWN

ISSUE
21

DRAWING NUMBER
VX SERIES CHART 1
PAGE 3 OF 4

REPLACES
X80986-VX

REVISIONS

A

PR16589

J A S

22 JUL 88

JAF

13JAN99

A

PR16590

J A S

22 JUL 88

JAF

13JAN99

A

C084025

J A S

22 JUL 88

JAF

13JAN99

B

PR17180

K A C

3 MAR 89

JAF

13JAN99

C

C093789

P T T

3 NOV 98

JAF

13JAN99

D

PR23775

P B T

08 DEC 98

JAF

13JAN99

E

PR23787

M P O

13 JAN 99

JAF

13JAN99

F

PR23780

G R T

25 FEB 99

JAF

13JAN99

G

C093843

D L T

14 APR 99

JAF

13JAN99

H

C0-95107

G J W

29 APR 99

JAF

13JAN99

J

C0-95704

D L W

22 MAR 00

JAF

13JAN99

UNLESS OTHERWISE NOTED MECHANICAL CHARACTERISTICS ARE GIVEN ON LEVER OVER PLUNGER													
"D" LEVER ACTUATION POINT	LEVER TYPE	"E" FREE POSITION (MAX)	"F" OPERATION POINT (MIN)	"G" RELEASE POINT (MAX)	OVER- TRAVEL (MIN)	DIFF TRAVEL (MIN)	FORCE AT OPERATE POINT		UNACTUATED OUTPUT VOLTAGE	OUTPUT TRANSISTOR 	CATALOG	LISTING	COMMENTS
							OUNCES	GRAMS			STYLE 1 	STYLE 2 	
.795	F 	<u>17.02</u> .670	<u>14.86</u> .585	<u>16.18</u> .637	<u>0.91</u> .036	<u>0.05</u> .002	.35 ⁺¹⁸ -14	10 ⁺⁵ -4	HIGH	OFF	VX10-F4		GENICOM DRAWING NO. 44A501960-001
.795	H	<u>17.02</u> .670	<u>15.37</u> .605	<u>16.69</u> .657	<u>0.91</u> .036	<u>0.05</u> .002	.35 ⁺¹⁸ -14	10 ⁺⁵ -4	HIGH	OFF			
.795	F 	<u>17.02</u> .670	<u>14.86</u> .585	<u>16.18</u> .637	<u>0.91</u> .036	<u>0.05</u> .002	.35 ⁺¹⁸ -14	10 ⁺⁵ -4	LOW	ON			
.795	H	<u>17.02</u> .670	<u>15.37</u> .605	<u>16.69</u> .657	<u>0.91</u> .036	<u>0.05</u> .002	.35 ⁺¹⁸ -14	10 ⁺⁵ -4	HIGH	OFF	VX10-H2		
	NONE	<u>16.38</u> .645	<u>14.22</u> .560	<u>15.54</u> .612	<u>1.02</u> .040	<u>0.05</u> .002	1.2*18	34*5	HIGH	OFF	VX30HP		
.795	A	<u>17.02</u> .670	<u>14.86</u> .585	<u>16.18</u> .637	<u>0.91</u> .036	<u>0.05</u> .002	.35 ⁺¹⁸ -14	10 ⁺⁵ -4	HIGH	OFF			
.795	F	<u>17.02</u> .670	<u>14.86</u> .585	<u>16.18</u> .637	<u>0.91</u> .036	<u>0.05</u> .002	.35 ⁺¹⁸ -14	10 ⁺⁵ -4	HIGH	OFF			
.795	F	<u>17.02</u> .670	<u>14.86</u> .585	<u>16.18</u> .637	<u>0.91</u> .036	<u>0.05</u> .002	.35 ⁺¹⁸ -14	10 ⁺⁵ -4	HIGH	OFF	VX10-F8		
.810	C	<u>22.48</u> .885	<u>19.99</u> .787	<u>21.62</u> .851	<u>1.02</u> .040	<u>0.05</u> .002	.19*09	5.4*2.6	HIGH	OFF	VX10-C1L		



MASTER REDUCED
ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

MICRO SWITCH
a Honeywell Division

FED. REG. CODE 91829

SWITCH – SOLID STATE

CATALOG LISTING

VX SERIES

CHART 1

THIRD ANGLE PROJECTION

SCALE NONE

DO NOT SCALE PRINT

UNLESS OTHERWISE SPECIFIED
TOLERANCES ARE

ONE PLACE (.0) ±.030

TWO PLACES (.00) ±.015

THREE PLACES (.000) ±.005

ANGLES ±

WEIGHT

UNLESS OTHERWISE NOTED MECHANICAL CHARACTERISTICS ARE GIVEN ON LEVER OVER PLUNGER


"D" LEVER ACTUATION POINT	LEVER TYPE	"E" FREE POSITION (MAX)	"F" OPERATION POINT (MIN)	"G" RELEASE POINT (MAX)	OVER- TRAVEL (MIN)	DIFF TRAVEL (MIN)	FORCE AT OPERATE POINT		UNACTUATED OUTPUT VOLTAGE	OUTPUT TRANSISTOR 	CATALOG LISTING		IBM DRAWING NO.	COMMENTS		
							OUNCES	GRAMS			STYLE 1 	STYLE 2 				
.795	F 	$\frac{17.02}{.670}$	$\frac{14.86}{.585}$	$\frac{16.18}{.637}$	$\frac{0.91}{.036}$	$\frac{0.05}{.002}$	.35	$\frac{+18}{-14}$	10	$\frac{+5}{-4}$	HIGH	OFF	VX10-F1		4592340	
.795	F 	$\frac{17.02}{.670}$	$\frac{14.86}{.585}$	$\frac{16.18}{.637}$	$\frac{0.91}{.036}$	$\frac{0.05}{.002}$	.35	$\frac{+18}{-14}$	10	$\frac{+5}{-4}$	HIGH	OFF			4593242	
.795	F 	$\frac{17.02}{.670}$	$\frac{14.86}{.585}$	$\frac{16.18}{.637}$	$\frac{0.91}{.036}$	$\frac{0.05}{.002}$	.35	$\frac{+18}{-14}$	10	$\frac{+5}{-4}$	HIGH	OFF			4593470	
.795	F 	$\frac{17.02}{.670}$	$\frac{14.86}{.585}$	$\frac{16.18}{.637}$	$\frac{0.91}{.036}$	$\frac{0.05}{.002}$	.35	$\frac{+18}{-14}$	10	$\frac{+5}{-4}$	HIGH	OFF			4592552	

IBM CORPORATION SWITCHES ONLY THIS PAGE

[illegible]


MASTER REDUCED
ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.		
MICRO SWITCH a Honeywell Division FED. MFG. CODE 91929	SWITCH — SOLID STATE	CATALOG LISTING
		VX SERIES CHART 1

THIRD ANGLE PROJECTION		
		
SCALE	NONE	
DO NOT SCALE PRINT		
UNLESS OTHERWISE SPECIFIED TOLERANCES ARE		
ONE PLACE	(.0)	$\pm .030$
TWO PLACES	(.00)	$\pm .015$
THREE PLACES	(.000)	$\pm .005$
ANGLES	$\pm$	
WEIGHT		

M



THIRD ANGLE PROJECTION		
		
SCALE 3 : 1		
DO NOT SCALE PRINT		
UNLESS OTHERWISE SPECIFIED TOLERANCES ARE		
ONE PLACE	(.0)	±.030
TWO PLACES	(.00)	±.015
THREE PLACES	(.000)	±.005
ANGLES		±
WEIGHT		

											SOLDER PLATED TERMINALS	
"D" LEVER ACTUATION POINT	LEVER TYPE	"E" FREE POSITION (MAX)	"F" OPERATION POINT (MIN)	"G" RELEASE POINT (MAX)	OVER-TRAVEL (MIN)	DIFF TRAVEL (MIN)	FORCE AT OPERATE POINT		UNACTUATED OUTPUT VOLTAGE	OUTPUT TRANSISTOR 	CATALOG LISTING	
							OUNCES	GRAMS			STYLE 1 	STYLE 2 
.795	NONE	$\frac{16.38}{.645}$	$\frac{14.22}{.560}$	$\frac{15.54}{.612}$	$\frac{1.02}{.040}$	$\frac{0.05}{.002}$	$.35 \begin{smallmatrix} +.18 \\ -.14 \end{smallmatrix}$	$10 \begin{smallmatrix} +5 \\ -4 \end{smallmatrix}$	HIGH	OFF	VX10	VX12
									LOW	ON	VX11	VX13
							$3.0 \pm .88$	85 ± 25	HIGH	OFF	VX80	
									LOW	ON	VX81	
.860	A	$\frac{17.27}{.680}$	$\frac{14.71}{.579}$	$\frac{16.33}{.643}$	$\frac{1.02}{.040}$	$\frac{0.05}{.002}$	$.35 \pm .2$	10 ± 5	HIGH	OFF	VX10-A1	VX12-A1
									LOW	ON	VX11-A1	
							2.8 ± 1.1	80 ± 30	HIGH	OFF	VX80-A1	
									LOW	ON	VX81-A1	
1.400	A	$\frac{19.28}{.759}$	$\frac{13.94}{.549}$	$\frac{17.32}{.682}$	$\frac{2.16}{.085}$	$\frac{0.10}{.004}$	$0.2 \pm .1$	$5 \begin{smallmatrix} +3 \\ -2 \end{smallmatrix}$	HIGH	OFF	VX10-A2	
									LOW	ON		VX13-A2
							$1.41 \pm .50$	40 ± 15	HIGH	OFF	VX80-A2	VX82-A2
									LOW	ON	VX81-A2	
2.340	A	$\frac{22.58}{.889}$	$\frac{12.62}{.497}$	$\frac{18.97}{.747}$	$\frac{4.06}{.160}$	$\frac{0.20}{.008}$	$.10 \pm .07$	3 ± 2	HIGH	OFF	VX10-A3	VX12-A3
									LOW	ON	VX11-A3	VX13-A3
							$.75 \begin{smallmatrix} +.35 \\ -.25 \end{smallmatrix}$	$21 \begin{smallmatrix} +9 \\ -7 \end{smallmatrix}$	HIGH	OFF	VX80-A3	
									LOW	ON	VX81-A3	
1.285	B	$\frac{22.23}{.875}$	$\frac{17.02}{.670}$	$\frac{20.52}{.808}$	$\frac{1.91}{.075}$	$\frac{0.10}{.004}$	$0.20 \begin{smallmatrix} +.15 \\ -.10 \end{smallmatrix}$	$5 \begin{smallmatrix} +4 \\ -2 \end{smallmatrix}$	HIGH	OFF	VX10-B1	VX12-B1
									LOW	ON	VX11-B1	VX13-B1
							$1.55 \pm .53$	44 ± 15	HIGH	OFF	VX80-B1	
									LOW	ON		
.810	C	$\frac{22.48}{.885}$	$\frac{19.99}{.787}$	$\frac{21.62}{.851}$	$\frac{1.02}{.040}$	$\frac{0.05}{.002}$	$.40 \pm .20$	12 ± 5	HIGH	OFF	VX10-C1	VX12-C1
									LOW	ON	VX11-C1	VX13-C1
							3.0 ± 1.06	85 ± 30	HIGH	OFF	VX80-C1	
									LOW	ON	VX81-C1	
	A	$\frac{17.78}{.700}$	$\frac{14.73}{.580}$	$\frac{16.13}{.635}$	$\frac{1.02}{.040}$	$\frac{0.10}{.004}$	$.35 \begin{smallmatrix} +.18 \\ -.14 \end{smallmatrix}$	$10 \begin{smallmatrix} +5 \\ -4 \end{smallmatrix}$	LOW	ON	VX81-A2-GE	
1.226	F	$\frac{25.73}{1.013}$	$\frac{21.72}{.855}$	$\frac{23.98}{.944}$	$\frac{1.65}{.065}$	$\frac{0.13}{.005}$	$.35 \begin{smallmatrix} +.18 \\ -.14 \end{smallmatrix}$	$10 \begin{smallmatrix} +5 \\ -4 \end{smallmatrix}$	HIGH	OFF	VX10-F1 VX11-F1	
1.250	F	$\frac{25.58}{1.007}$	$\frac{21.72}{.855}$	$\frac{23.83}{.938}$	$\frac{1.65}{.065}$	$\frac{0.13}{.005}$	$.35 \begin{smallmatrix} +.18 \\ -.14 \end{smallmatrix}$	$10 \begin{smallmatrix} +5 \\ -4 \end{smallmatrix}$	HIGH	OFF	VX10-FA	

NOTE
A MEASUREMENTS TAKEN OVER PLUNGER



MASTER REDUCED
ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

MICRO SWITCH
a Honeywell Division

FED. MFG. CODE 81828


SWITCH - SOLID STATE

CATALOG LISTING

VX SERIES

CHART 1

THIRD ANGLE PROJECTION



SCALE	NONE
-------	------

DO NOT SCALE PRINT

UNLESS OTHERWISE SPECIFIED
TOLERANCES ARE

ONE PLACE (0) $\pm .030$

TWO PLACES (.00) $\pm .015$

THREE PLACES (.000) $\pm .005$

ANGLES $\pm$

WEIGHT

FORMTEK
DRAWN

ISSUE
21

DRAWING NUMBER
VX SERIES CHART 1
PAGE 3 OF 4

REPLACES
X80986-VX

REVISIONS

A

PR16589

J A S

22 JUL 88

JAF

13JAN99

A

PR16590

J A S

22 JUL 88

JAF

13JAN99

A

C084025

J A S

22 JUL 88

JAF

13JAN99

B

PR17180

K A C

3 MAR 89

JAF

13JAN99

C

C093789

D T T

3 NOV 98

JAF

13JAN99

D

PR23775

P B T

08 DEC 98

JAF

13JAN99

E

PR23787

M P O

13 JAN 99

JAF

13JAN99

F

PR23780

G R T

25 FEB 99

JAF

13JAN99

G

C093843

D L T

14 APR 99

JAF

13JAN99

H

C0-95107

G J W

29 APR 99

JAF

13JAN99

J

C0-95704

D L W

22 MAR 00

JAF

13JAN99

UNLESS OTHERWISE NOTED MECHANICAL CHARACTERISTICS ARE GIVEN ON LEVER OVER PLUNGER													
"D" LEVER ACTUATION POINT	LEVER TYPE	"E" FREE POSITION (MAX)	"F" OPERATION POINT (MIN)	"G" RELEASE POINT (MAX)	OVER- TRAVEL (MIN)	DIFF TRAVEL (MIN)	FORCE AT OPERATE POINT		UNACTUATED OUTPUT VOLTAGE	OUTPUT TRANSISTOR 	CATALOG	LISTING	COMMENTS
							OUNCES	GRAMS			STYLE 1 	STYLE 2 	
.795	F 	<u>17.02</u> .670	<u>14.86</u> .585	<u>16.18</u> .637	<u>0.91</u> .036	<u>0.05</u> .002	.35 ⁺¹⁸ -14	10 ⁺⁵ -4	HIGH	OFF	VX10-F4		GENICOM DRAWING NO. 44A501960-001
.795	H	<u>17.02</u> .670	<u>15.37</u> .605	<u>16.69</u> .657	<u>0.91</u> .036	<u>0.05</u> .002	.35 ⁺¹⁸ -14	10 ⁺⁵ -4	HIGH	OFF			
.795	F 	<u>17.02</u> .670	<u>14.86</u> .585	<u>16.18</u> .637	<u>0.91</u> .036	<u>0.05</u> .002	.35 ⁺¹⁸ -14	10 ⁺⁵ -4	LOW	ON			
.795	H	<u>17.02</u> .670	<u>15.37</u> .605	<u>16.69</u> .657	<u>0.91</u> .036	<u>0.05</u> .002	.35 ⁺¹⁸ -14	10 ⁺⁵ -4	HIGH	OFF	VX10-H2		
	NONE	<u>16.38</u> .645	<u>14.22</u> .560	<u>15.54</u> .612	<u>1.02</u> .040	<u>0.05</u> .002	1.2*18	34*5	HIGH	OFF	VX30HP		
.795	A	<u>17.02</u> .670	<u>14.86</u> .585	<u>16.18</u> .637	<u>0.91</u> .036	<u>0.05</u> .002	.35 ⁺¹⁸ -14	10 ⁺⁵ -4	HIGH	OFF			
.795	F	<u>17.02</u> .670	<u>14.86</u> .585	<u>16.18</u> .637	<u>0.91</u> .036	<u>0.05</u> .002	.35 ⁺¹⁸ -14	10 ⁺⁵ -4	HIGH	OFF			
.795	F	<u>17.02</u> .670	<u>14.86</u> .585	<u>16.18</u> .637	<u>0.91</u> .036	<u>0.05</u> .002	.35 ⁺¹⁸ -14	10 ⁺⁵ -4	HIGH	OFF	VX10-F8		
.810	C	<u>22.48</u> .885	<u>19.99</u> .787	<u>21.62</u> .851	<u>1.02</u> .040	<u>0.05</u> .002	.19*09	5.4*2.6	HIGH	OFF	VX10-C1L		



MASTER REDUCED
ANSI Y14.5M-1982 APPLIES

MICRO SWITCH

a Honeywell Division

FED. REG. CODE 91929

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

SWITCH – SOLID STATE

CATALOG LISTING
VX SERIES
CHART 1

THIRD ANGLE PROJECTION

SCALE NONE

DO NOT SCALE PRINT

UNLESS OTHERWISE SPECIFIED
TOLERANCES ARE

ONE PLACE (.0) ±.030

TWO PLACES (.00) ±.015

THREE PLACES (.000) ±.005

ANGLES ±

WEIGHT

UNLESS OTHERWISE NOTED MECHANICAL CHARACTERISTICS ARE GIVEN ON LEVER OVER PLUNGER

"D" LEVER ACTUATION POINT	LEVER TYPE	"E" FREE POSITION (MAX)	"F" OPERATION POINT (MIN)	"G" RELEASE POINT (MAX)	OVER- TRAVEL (MIN)	DIFF TRAVEL (MIN)	FORCE AT OPERATE POINT		UNACTUATED OUTPUT VOLTAGE	OUTPUT TRANSISTOR 	CATALOG LISTING		IBM DRAWING NO.	COMMENTS		
							OUNCES	GRAMS			STYLE 1 	STYLE 2 				
.795	F 	$\frac{17.02}{.670}$	$\frac{14.86}{.585}$	$\frac{16.18}{.637}$	$\frac{0.91}{.036}$	$\frac{0.05}{.002}$	.35	$\frac{+18}{-14}$	10	$\frac{+5}{-4}$	HIGH	OFF	VX10-F1		4592340	
.795	F 	$\frac{17.02}{.670}$	$\frac{14.86}{.585}$	$\frac{16.18}{.637}$	$\frac{0.91}{.036}$	$\frac{0.05}{.002}$	.35	$\frac{+18}{-14}$	10	$\frac{+5}{-4}$	HIGH	OFF			4593242	
.795	F 	$\frac{17.02}{.670}$	$\frac{14.86}{.585}$	$\frac{16.18}{.637}$	$\frac{0.91}{.036}$	$\frac{0.05}{.002}$	.35	$\frac{+18}{-14}$	10	$\frac{+5}{-4}$	HIGH	OFF			4593470	
.795	F 	$\frac{17.02}{.670}$	$\frac{14.86}{.585}$	$\frac{16.18}{.637}$	$\frac{0.91}{.036}$	$\frac{0.05}{.002}$	.35	$\frac{+18}{-14}$	10	$\frac{+5}{-4}$	HIGH	OFF			4592552	


IBM CORPORATION SWITCHES ONLY THIS PAGE

FORMTEK		DRAWING NUMBER	VX SERIES CHART 1	
		ISSUE	M	
		21	PAGE 4 OF 4	
REVISIONS				
A	C064025	J A S 9 AUG 88		
B	C093789	D L T 3 NOV 88		
C	PR23775	P P F 09 DEC 88		
D	PR23787	M P O 13 JAN 99		
E	PR23760	G R T 25 FEB 99		
F	C093843	D L T 14 APR 99		
G	C-95107	G J W 29 APR 99		
H	C-95704	D L M 22 MAR 00		
I				
J				
K				
L				
M				
N				
O				
P				
Q				
R				
S				
T				
U				
V				
W				
X				
Y				
Z				
DRAWN		CHECK	RELEASE NO.	REPLACES
J A S 9AUG88		J A F 13JAN99	PR-13487	X80986-VX



MASTER REDUCED
ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.		
MICRO SWITCH a Honeywell Division FED. MFG. CODE 91929	SWITCH — SOLID STATE	CATALOG LISTING
		VX SERIES CHART 1

THIRD ANGLE PROJECTION		
		
SCALE	NONE	
DO NOT SCALE PRINT		
UNLESS OTHERWISE SPECIFIED TOLERANCES ARE		
ONE PLACE	(.0)	± .030
TWO PLACES	(.00)	± .015
THREE PLACES	(.000)	± .005
ANGLES	±	
WEIGHT		