


**Part Number: 500463-2279**

0.40mm Pitch Board-to-Board SlimStack™ Receptacle, Surface Mount, Single Row, Vertical Stacking, 0.95mm Stacking Height, 22 Circuits, Lead-Free



Series Image - Reference only

Status:	<b>OBsolete</b>
Replacement:	NONE
Series:	500463
Category:	PCB Receptacles
Overview:	<a href="#">SlimStack™ 0.40mm Pitch Board-to-Board Connectors</a>

**Mates With Part(s):**

[500464](#)

**Product Environmental Compliance**

**EU RoHS:** ELV and RoHS Compliant

**China RoHS:**

**REACH SVHC:**

**Low-Halogen Status:** Not Reviewed

**Part Detail****General**

<b>Status</b>	<b>Obsolete</b>
Category	PCB Receptacles
Series	<a href="#">500463</a>
Application	Board-to-Board, Signal
Comments	Solder Tab Plating: Lead-Free, Tin
Overview	<a href="#">SlimStack™ 0.40mm Pitch Board-to-Board Connectors</a>
Product Name	SlimStack™

**Physical**

Circuits (Loaded)	22
Circuits (maximum)	22
Durability (mating cycles max)	10
Glow-Wire Compliant	No
Mated Height	0.95mm
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Number of Rows	1
Orientation	Vertical
PCB Locator	No
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	0.40mm
Plating min - Mating	0.102µm
Plating min - Termination	0.102µm
Polarized to PCB	Yes
Surface Mount Compatible (SMC)	N/A
Temperature Range - Operating	-25°C to +85°C
Termination Interface: Style	Surface Mount

**Electrical**

**(Please review the Product Specification for specific details.)**

Current - Maximum per Contact	0.1A
Voltage - Maximum	50V

**Material Info**

UPC	822348249466
-----	--------------

**Reference - Drawing Numbers**

Product Specification	PS-500463-002, RPS-500463-003
Sales Drawing	SD-500463-009, SD-500463-010

**Application Tooling**

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then

contained in the Application Tooling Specification document.

---

**Previously Available Application Tooling**

[Check our list of old tooling that used to be available for this part](#)