



Aluminum Capacitors



FEATURES

- Load life: 2000 h at 105 °C
- Miniature dimension
- SMD style
- Reflow soldering
- Polarized aluminum electrolytic capacitors
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



RoHS
COMPLIANT

QUICK REFERENCE DATA

DESCRIPTION	VALUE
Nominal case size (Ø D x L in mm)	4 x 5.3 to 12.5 x 13.5
Rated capacitance range, C _R	10 µF to 2200 µF
Capacitance tolerance	± 20 %
Rated voltage range	6.3 V to 50 V
Category temperature range	-40 °C to 105 °C
Load life	2000 h
Based on sectional specification	IEC 60384-4 / EN130300
Climatic category IEC 60068	40 / 105 / 56

APPLICATIONS

- Industrial electronics, automotive electronics, telecommunication systems
- Smoothing and filtering
- Miniature power supply units, dc-to-dc converters

PACKAGING


Supplied in blister tape.

SELECTION CHART FOR C_R, U_R, AND RELEVANT NOMINAL CASE SIZES (Ø D x L in mm)

C _R (µF)	RATED VOLTAGE (V)					
	6.3	10	16	25	35	50
10	→	→	4 x 5.3	→	5 x 5.3	6.3 x 5.8
22	→	→	→	6.3 x 5.8	6.3 x 5.8	8 x 6.2
33	→	→	6.3 x 5.8	6.3 x 5.8	8 x 6.2	8 x 10
47	5 x 5.3	→	6.3 x 5.8	8 x 6.2	8 x 10	10 x 10
100	→	6.3 x 5.8	→	8 x 10	→	10 x 10
220	→	8 x 10	10 x 10	→	10 x 10	12.5 x 13.5
330	8 x 10	→	10 x 10	10 x 10	12.5 x 13.5	-
470	→	10 x 10	10 x 10	10 x 10	12.5 x 13.5	-
680	→	→	→	12.5 x 13.5	-	-
1000	→	10 x 10	12.5 x 13.5	-	-	-
1500	10 x 10	12.5 x 13.5	-	-	-	-
2200	12.5 x 13.5	-	-	-	-	-

**DIMENSIONS** in millimeters

CASE SIZE CODE	D ± α	L ± α	A ± α	B ± α	C ± α	E ± α	R	N	P
BB	4 ± 0.5	5.3 ± 0.2	1.9 ± 0.2	4.3 ± 0.2	4.3 ± 0.2	1.0 ± 0.2	0.5 to 0.8	0.3	0.5
BC	5 ± 0.5	5.3 ± 0.2	2.3 ± 0.2	5.3 ± 0.2	5.3 ± 0.2	1.4 ± 0.2	0.5 to 0.8	0.3	0.5
AD	6.3 ± 0.5	5.8 ± 0.3	2.4 ± 0.2	6.6 ± 0.2	6.6 ± 0.2	2.2 ± 0.2	0.5 to 0.8	0.3	0.5
BM	6.3 ± 0.5	7.7 ± 0.4	2.4 ± 0.2	6.6 ± 0.2	6.6 ± 0.2	2.2 ± 0.2	0.5 to 0.8	0.3	0.5
AE	8 ± 0.5	6.2 ± 0.4	3.3 ± 0.2	8.3 ± 0.2	8.3 ± 0.2	2.3 ± 0.2	0.5 to 0.8	0.3	0.5
AF	8 ± 0.5	10 ± 0.5	2.9 ± 0.2	8.3 ± 0.2	8.3 ± 0.2	3.1 ± 0.2	0.8 to 1.1	0.3	0.5
AG	10 ± 0.5	10 ± 0.5	3.2 ± 0.2	10.3 ± 0.2	10.3 ± 0.2	4.5 ± 0.2	0.8 to 1.1	0.3	0.5
AH	12.5 ± 0.5	13.5 ± 0.5	4.6 ± 0.2	12.8 ± 0.2	12.8 ± 0.2	4.5 ± 0.2	1.1 to 1.4	0.3	0.5

**ELECTRICAL DATA**

SYMBOL	DESCRIPTION
U_R	Rated voltage
C_R	Rated capacitance at 120 Hz
$\tan \delta$	Max. dissipation factor at 120 Hz
R_{ESR}	Max. equivalent series resistance at 120 Hz
I_R	Rated alternating current at 120 Hz and upper category temperature

Note

- Unless otherwise specified, all electrical values apply at $T_{amb} = 20^\circ\text{C}$, $P = 86\text{ kPa}$ to 106 kPa , $RH = 45\%$ to 75% .

ORDERING EXAMPLE

ECV 220 μF / 35 V, $\pm 20\%$, size 10 mm x 10 mm

Ordering code: MALSECV00AG322FARK

For Standard Packaging Quantity (SPQ) and Minimum Order Quantity (MOQ) please refer to our price list or contact customer service.

ELECTRICAL DATA AND ORDERING INFORMATION


U_R (V)	C_R 120 Hz (μF)	DIMENSIONS D x L (mm)	$\tan \delta$ 120 Hz	R_{ESR} 120 Hz / 20 °C (Ω)	I_R 120 Hz / 105 °C (mA)	WEIGHT (g)	CATALOG NUMBER
6.3	47	5 x 5.3	0.22	6.21	36	0.17	MALSECV00BC247BARK
	330	8 x 10	0.28	1.13	288	1.00	MALSECV00AF333BARK
	1500	10 x 10	0.28	0.25	560	1.21	MALSECV00AG415BARK
	2200	12.5 x 13.5	0.28	0.17	730	2.00	MALSECV00AH422BARK
10	100	6.3 x 5.8	0.19	2.52	60	0.30	MALSECV00AD310CARK
	220	8 x 10	0.24	1.45	173	1.00	MALSECV00AF322CARK
	470	10 x 10	0.24	0.68	351	1.21	MALSECV00AG347CARK
	1000	10 x 10	0.24	0.32	550	1.21	MALSECV00AG410CARK
	1500	12.5 x 13.5	0.24	0.21	650	2.00	MALSECV00AH415CARK
16	10	4 x 5.3	0.16	21.22	17	0.12	MALSECV00BB210DARK
	33	6.3 x 5.8	0.16	6.43	40	0.30	MALSECV00AD233DARK
	47	6.3 x 5.8	0.16	4.52	50	0.30	MALSECV00AD247DARK
	220	10 x 10	0.20	1.21	330	1.21	MALSECV00AG322DARK
	330	10 x 10	0.20	0.80	441	1.21	MALSECV00AG333DARK
	470	10 x 10	0.20	0.56	489	1.21	MALSECV00AG347DARK
	1000	12.5 x 13.5	0.20	0.27	600	2.00	MALSECV00AH410DARK



ELECTRICAL DATA AND ORDERING INFORMATION

U_R (V)	C_R 120 Hz (μ F)	DIMENSIONS D x L (mm)	$\tan \delta$ 120 Hz	R_{ESR} 120 Hz / 20 °C (Ω)	I_R 120 Hz / 105 °C (mA)	WEIGHT (g)	CATALOG NUMBER
25	22	6.3 x 5.8	0.14	8.44	38	0.30	MALSECV00AD222EARK
	33	6.3 x 5.8	0.14	5.63	48	0.30	MALSECV00AD233EARK
	47	8 x 6.2	0.16	4.52	79	0.55	MALSECV00AE247EARK
	100	8 x 10	0.16	2.12	181	1.00	MALSECV00AF310EARK
	330	10 x 10	0.16	0.64	372	1.21	MALSECV00AG333EARK
	470	10 x 10	0.16	0.45	450	1.21	MALSECV00AG347EARK
	680	12.5 x 13.5	0.16	0.31	500	2.00	MALSECV00AH368EARK
35	10	5 x 5.3	0.12	15.92	24	0.17	MALSECV00BC210FARK
	22	6.3 x 5.8	0.12	7.23	42	0.30	MALSECV00AD222FARK
	33	8 x 6.2	0.13	5.22	76	0.55	MALSECV00AE233FARK
	47	8 x 10	0.13	3.67	124	1.00	MALSECV00AF247FARK
	220	10 x 10	0.13	0.78	450	1.21	MALSECV00AG322FARK
	330	12.5 x 13.5	0.13	0.52	500	2.00	MALSECV00AH333FARK
	470	12.5 x 13.5	0.13	0.37	600	2.00	MALSECV00AH347FARK
50	10	6.3 x 5.8	0.10	13.26	30	0.30	MALSECV00AD210HARK
	22	8 x 6.2	0.12	7.23	67	0.55	MALSECV00AE222HARK
	33	8 x 10	0.12	4.82	133	1.00	MALSECV00AF233HARK
	47	10 x 10	0.12	3.39	180	1.21	MALSECV00AG247HARK
	100	10 x 10	0.12	1.59	310	1.21	MALSECV00AG310HARK
	220	12.5 x 13.5	0.12	0.72	480	2.00	MALSECV00AH322HARK

REFLOW SOLDERING CONDITIONS FOR SMD ALUMINUM ELECTROLYTIC CAPACITORS



PROFILE FEATURE

	SOLDERING CONDITION		
	Ø 4 TO Ø 10	Ø 12.5	Ø 16
Average ramp-up rate (T_L to T_P)	3 °C/s max.	3 °C/s max.	
Preheat			
Temperature min. (T_s min.)	150 °C	150 °C	
Temperature max. (T_s max.)	200 °C	200 °C	
Time (T_s min. to T_s max.)	60 s to 150 s	40 s to 120 s	40 s to 100 s
T_s max. to T_L			
Ramp-up rate	3 °C/s max.	3 °C/s max.	
Time maintained above temperature (T_L)	217 °C	217 °C	
Time (t_L)	60 s to 90 s	40 s to 60 s	
Peak / classification temperature (T_P)	250 °C	240 °C	230 °C
Time within 5 °C of actual peak temperature (T_P)	10 s max.	10 s max.	
Ramp-down rate	3 °C/s max.	3 °C/s max.	
Time 25 °C to peak temperature	8 min max.	8 min max.	

**RESISTANCE TO SOLDERING HEAT**

Leakage current	Less than specified value
Capacitance value	Within $\pm 10\%$ of initial value
$\tan \delta$	Less than specified value

LOW TEMPERATURE BEHAVIOR (at 120 Hz)

IMPEDANCE RATIO (Z) T2/(Z) T1	RATED VOLTAGE (V)					
T2/T1	6.3	10	16	25	35	50
-25 °C / +20 °C	3	3	2	2	2	2
-40 °C / +20 °C	8	5	4	3	3	3

ADDITIONAL ELECTRICAL DATA

PARAMETER	CONDITIONS	VALUE
Current		
Leakage current (test conditions: U_R , 20 °C)	After 2 min at U_R	$I_{L2} \leq 0.01 \times C_R \times U_R$ or $3 \mu A$ for $U_R \leq 100 V$ (whichever is greater)
Resistance		
Equivalent series resistance (ESR)	Calculated from $\tan \delta_{max.}$	$ESR = \tan \delta / 2 \pi f C_R$

MULTIPLIER OF RIPPLE CURRENT (I_R) AS A FUNCTION OF FREQUENCY

FREQUENCY (Hz)	I_R MULTIPLIER FOR $U_R \leq 100 V$
50	0.70
120	1.00
300	1.17
1000	1.36
$\geq 10\,000$	1.50

TEST PROCEDURES AND REQUIREMENTS

TEST	PROCEDURE (quick reference)	REQUIREMENTS
Load life	$T_{amb} = 105\text{ °C}$ U_R and I_R applied After 2000 h	$\Delta C/C: \pm 20\%$ of initial value $I_L \leq \text{spec. limit}$ $\tan \delta \leq 2 \times \text{spec. limit}$
Shelf life	No voltage applied After 1000 h After test: U_R to be applied for 30 min 24 h to 48 h before measurement	$\Delta C/C: \pm 20\%$ of initial value $I_L \leq \text{spec. limit}$ $\tan \delta \leq 2 \times \text{spec. limit}$

Statements about product lifetime are based on calculations and internal testing. They should only be interpreted as estimations. Also due to external factors, the lifetime in the field application may deviate from the calculated lifetime. In general, nothing stated herein shall be construed as a guarantee of durability.



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.