




4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT

BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

CE

16

P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

PART NUMBER	L (METERS)	MPO CONNECTOR LOSS (dB)	MPO CONNECTOR LOSS (dB)
1938981-1	1.000-1.305	0.75	0.50
1938981-2	2.000-2.305	0.75	0.50
1938981-3	3.000-3.305	0.75	0.50
1938981-4	4.000-4.610	0.76	0.51
1938981-5	5.000-5.610	0.76	0.51
1938981-6	6.000-6.610	0.76	0.51
1938981-7	7.000-7.610	0.76	0.51
1938981-8	8.000-8.610	0.76	0.51
1938981-9	9.000-9.610	0.76	0.51
1-1938981-0	10.000-10.610	0.77	0.52
1-1938981-1	11.000-11.610	0.77	0.52
1-1938981-2	12.000-12.610	0.77	0.52
1-1938981-3	13.000-13.610	0.77	0.52
1-1938981-4	14.000-14.610	0.77	0.52
1-1938981-5	15.000-15.610	0.77	0.52
1-1938981-6	16.000-16.610	0.77	0.52
1-1938981-7	17.000-17.610	0.78	0.53
1-1938981-8	18.000-18.610	0.78	0.53
1-1938981-9	19.000-19.610	0.78	0.53
2-1938981-0	20.000-20.610	0.78	0.53
2-1938981-1	21.000-21.610	0.78	0.53
2-1938981-2	22.000-22.610	0.78	0.53
2-1938981-3	23.000-23.610	0.78	0.53
2-1938981-4	24.000-24.610	0.79	0.54
2-1938981-5	25.000-25.610	0.79	0.54
2-1938981-6	26.000-26.914	0.79	0.54
2-1938981-7	27000-27.914	0.79	0.54
2-1938981-8	28.000-28.914	0.79	0.54
2-1938981-9	29.000-29.914	0.79	0.54
3-1938981-0	30.000-30.914	0.80	0.55
3-1938981-1	31.000-31.914	0.80	0.55
3-1938981-2	32.000-32.914	0.80	0.55
3-1938981-3	33.000-33.914	0.80	0.55
3-1938981-4	34.000-34.914	0.80	0.55
3-1938981-5	35.000-35.914	0.80	0.55
3-1938981-6	36.000-36.914	0.80	0.55
3-1938981-7	37.000-37.914	0.81	0.56
3-1938981-8	38.000-38.914	0.81	0.56
3-1938981-9	39.000-39.914	0.81	0.56
4-1938981-0	40.000-40.914	0.81	0.56
4-1938981-1	41.000-41.914	0.81	0.56
4-1938981-2	42.000-42.914	0.81	0.56
4-1938981-3	43.000-43.914	0.81	0.56
4-1938981-4	44.000-44.914	0.82	0.57
4-1938981-5	45.000-45.914	0.82	0.57
4-1938981-6	46.000-46.914	0.82	0.57
4-1938981-7	47.000-47.914	0.82	0.57
4-1938981-8	48.000-48.914	0.82	0.57
4-1938981-9	49.000-49.914	0.82	0.57
5-1938981-0	50.000-51.000	0.83	0.58

PART NUMBER	L (METERS)	MPO CONNECTOR LOSS (dB)	MPO CONNECTOR LOSS (dB)
5-1938981-1	51.000-52.020	0.83	0.58
5-1938981-2	52.000-53.040	0.83	0.58
5-1938981-3	53.000-54.060	0.83	0.58
5-1938981-4	54.000-55.080	0.83	0.58
5-1938981-5	55.000-56.100	0.83	0.58
5-1938981-6	56.000-57.120	0.83	0.58
5-1938981-7	57.000-58.140	0.84	0.59
5-1938981-8	58.000-59.160	0.84	0.59
5-1938981-9	59.000-60.180	0.84	0.59
6-1938981-0	60.000-61.200	0.84	0.59
6-1938981-1	61.000-62.220	0.84	0.59
6-1938981-2	62.000-63.240	0.84	0.59
6-1938981-3	63.000-64.260	0.84	0.59
6-1938981-4	64.000-65.280	0.85	0.60
6-1938981-5	65.000-66.300	0.85	0.60
6-1938981-6	66.000-67.320	0.85	0.60
6-1938981-7	67.000-68.340	0.85	0.60
6-1938981-8	68.000-69.360	0.85	0.60
6-1938981-9	69.000-70.380	0.85	0.60
7-1938981-0	70.000-71.400	0.86	0.61

1

MAXIMUM INSERTION LOSS:
MPO: 0.75dB PLUS ATTENUATION, SEE CHART
LC: 0.50 dB PLUS CABLE ATTENUATION, SEE CHART
TEST CABLE ASSEMBLIES AT 1300nm WAVELENGTH ONLY.

2.

PRODUCT AND PROCESSING MUST MEET REQUIREMENTS
OF TYCO ELECTRONICS STANDARD 230-702.

3.

A COPY OF TEST DATA IS PLACED INSIDE OR WITH
THE UNIT PACKAGE.

4

WHITE MARK ON CONNECTOR BODY INDICATES FIBER 1 SIDE.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
METERS

MATERIAL
—

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± -
FINISH —

DWN
J.W.DAVIS
02FEB07

CHK
D.FENNELL
02FEB07

APVD
D.BAECHTLE
02FEB07

PRODUCT SPEC
—

APPLICATION SPEC
—

WEIGHT
—

CUSTOMER DRAWING

tyco

Electronics

Tyco Electronics Corporation
Harrisburg Pa, 17105-3608

NAME
CABLE ASSEMBLY, 62.5/125um,
12 FIBER CLT, OFNP, MPO YELLOW SECURE
TO LC SIMPLEX YELLOW SECURE

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=1938981

RESTRICTED TO
—

SCALE
NTS

SHEET
2 of 2

REV
A

1938981

B

A

AMP 3307-7 REV 31MAR2000

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity Divested:](#)

[3-1375191-0](#)